



Heyco® Snap Bushings

Mounting Diameter: 0.250" to 0.750"


- Converts raw-edged holes to smooth, neat, insulated holes.
- Locking fingers snap into holes with fingertip pressure.
- Withstands a push back force of 35 pounds.
- Insulates and mechanically protects electrical and telecommunications cables, tubing, hose, rope, and utility lines.
- Available in multiple sizes for use in .250" (6,4 mm) to 6.00" (152,4 mm) diameter holes.
- We offer the following brass-colored parts for lamp and lighting applications (Please consult Heyco for lead times):
 Part No. 2012, SB 312-3 Brass
 Part No. 2033, SB 375-4 Brass
 Part No. 2041, SB 437-4 Brass

PANEL DIMENSIONS				PART NO.		DESCRIPTION	PART DIMENSIONS					
Maximum Thickness	Mounting Hole Diameter			Black	White		A Inside Diameter		B Head Diameter		C Overall Height	
	in.	mm.	in.				mm.	in.	mm.	in.	mm.	in.
.040	1,0	.250	6,4	2003*	2004*	SB 250-040	.125	3,2	.312	7,9	.312	7,9
.062	1,6	.250	6,4	2000*	2001*	SB 250-2	.125	3,2	.312	7,9	.312	7,9
.062	1,6	.312	7,9	2010*	2011*	SB 312-3	.187	4,8	.375	9,5	.312	7,9
.125	3,2	.375	9,5	2020	2021	SB 375-3	.187	4,8	.468	11,9	.406	10,3
.125	3,2	.375	9,5	2030	2031	SB 375-4	.250	6,4	.468	11,9	.406	10,3
.172	4,4	.375	9,5	2017*	2018*	SB 375-281	.281	7,1	.468	11,9	.406	10,3
.125	3,2	.437	11,1	2038	2039	SB 437-4	.270	6,8	.531	13,5	.406	10,3
.125	3,2	.437	11,1	2043	2044	SB 437-5	.312	7,9	.531	13,5	.406	10,3
.125	3,2	.437	11,1	2042	2037	SB 437-243	.243	6,2	.531	13,5	.406	10,3
.125	3,2	.500	12,7	2058	2059	SB 500-4	.250	6,4	.570	14,5	.406	10,3
.125	3,2	.500	12,7	2049	2050	SB 500-5	.312	7,9	.570	14,5	.406	10,3
.125	3,2	.500	12,7	2053	2054	SB 500-6	.391	9,9	.570	14,5	.406	10,3
.125	3,2	.562	14,3	2060	2061	SB 562-5	.312	7,9	.656	16,7	.406	10,3
.125	3,2	.562	14,3	2063	2064	SB 562-6	.391	9,9	.656	16,7	.406	10,3
.125	3,2	.562	14,3	2066	2067	SB 562-7	.437	11,1	.656	16,7	.406	10,3
.125	3,2	.625	15,9	2075	2078	SB 625-4	.250	6,4	.718	18,2	.406	10,3
.125	3,2	.625	15,9	2070	2071	SB 625-7	.437	11,1	.718	18,2	.406	10,3
.125	3,2	.625	15,9	2073	2074	SB 625-8	.500	12,7	.718	18,2	.406	10,3
.250	7,1	.625	15,9	2830*	2831*	SB 625-500	.500	12,7	.703	17,9	.531	13,5
.125	3,2	.687	17,4	2083	2084	SB 687-8	.500	12,7	.781	19,8	.406	10,3
.125	3,2	.687	17,4	2086	2087	SB 687-9	.562	14,3	.781	19,8	.406	10,3
.125	3,2	.750	19,1	2090	2091	SB 750-6	.391	9,9	.850	21,6	.406	10,3
.125	3,2	.750	19,1	2092	2099	SB 750-8	.500	12,7	.850	21,6	.406	10,3
.125	3,2	.750	19,1	2093	2094	SB 750-9	.562	14,3	.850	21,6	.406	10,3
.125	3,2	.750	19,1	2096	2097	SB 750-10	.609	15,5	.850	21,6	.406	10,3
.250	6,4	.750	19,1	2840*	2841*	SB 750-625	.625	15,9	.828	21,0	.531	13,5



Standard color black. Consult Heyco for white and other colors.

*Depicts single panel design.


Locking fingers in fractional increment up to the maximum panel thickness.



SINGLE PANEL DESIGN*



MULTIPLE PANEL DESIGN



Quick Specs

Material
Certifications

6/6 Nylon
Recognized under the Component Program of Underwriters' Laboratories, File E15331

CS Certified by Canadian Standards Association, File LR8919

Flammability Rating

94V-2

Material Temperature Index 257°F (125°C)—Maximum temperature on part not to exceed 221°F (105°C)