




Heyco® Knock-Out Seals

- Plug electrical knock-outs.
- Molded in silver gray color to resemble galvanized steel.
- Install quickly with fingertip pressure (no tool required).
- Economical.
- Multiple trade sizes fit 1/2" to 2" knock-out holes.
- Lock firmly in boxes up to 1/8" thick, except for Part Number 4002 (KOS 2) and Thick Panel Knock-Out Seals (KOST's) which lock firmly in boxes up to 1/4" thick.
- Locking fingers in fractional increments up to the maximum panel thickness.
- Approximate Head Thickness: .062" (1,6 mm). Thickness may vary.
- To adapt a Knock-Out to accept a Heyco Strain Relief, see Heyco Knock-Out Adapters on page 4-29.

PANEL DIMENSIONS				TRADE SIZE	PART NO. Silver Gray	DESCRIPTION	PART DIMENSIONS			
Maximum Thickness		Mounting Hole Diameter					A Head Diameter		B Overall Height	
in.	mm.	in.	mm.			in.	mm.	in.	mm.	
.13	3,2	.875	22,2	1/2	3997	KOS 1/2	1.02	25,8	.45	11,5
		1.093	27,8	3/4	3998	KOS 3/4	1.22	31,0		
		1.375	34,9	1	3999	KOS 1	1.50	38,1		
		1.750	44,5	1-1/4	4000	KOS 1-1/4	1.91	48,4		
		2.000	50,8	1-1/2	4001	KOS 1-1/2	2.16	54,9		
.25	6,4	2.500	63,5	2	4002	KOS 2	2.73	69,3	.75	19,1

Standard color silver gray.



Heyco® Thick Panel Knock-Out Seals



PANEL DIMENSIONS				TRADE SIZE	PART NO. Silver Gray	DESCRIPTION	PART DIMENSIONS			
Maximum Thickness		Mounting Hole Diameter					A Head Diameter		B Overall Height	
in.	mm.	in.	mm.			in.	mm.	in.	mm.	
.25	6,4	.875	22,2	1/2	3991	KOST 1/2	1.02	25,8	.56	14,3
		1.093	27,8	3/4	3992	KOST 3/4	1.22	31,0		
		1.375	34,9	1	3993	KOST 1	1.50	38,1		
		1.750	44,5	1-1/4	3994	KOST 1-1/4	1.91	48,4		
.25	6,4	2.000	50,8	1-1/2	3995	KOST 1-1/2	2.16	54,9	.58	14,7
.25	6,4	2.500	63,5	2	4002	KOS 2	2.73	69,3	.75	19,1

Standard color silver gray.

Quick Specs

Material
Certifications

6/6 Nylon
 Recognized under the Component Program of Underwriters' Laboratories, File E51579
 Certified by Canadian Standards Association, File 8919

Flammability Rating

94V-2

Material Temperature Index

275°F (125°C)–Maximum temperature on part not to exceed 221°F (105°C)