

## SEALED LEAD-ACID BATTERIES (Cont.)



Fig. 1



Fig. 2



Fig. 3



Fig. 4



Fig. 5



Fig. 6



Fig. 7


Part No.	Figure No.	Nominal Voltage (V)	Amp Hours	Dimensions								Weight per Piece		Carton Quantity	Terminal Type
				Length		Width		Height		Total Height		lbs	kgs		
				in	mm	in	mm	in	mm	in	mm				
GC1.2-6F1	1	6	1.2	3.82	97.03	.94	23.88	2.03	51.56	2.26	57.40	0.30	0.66	30	F1
GC7-6F1	3	6	7.0	5.94	150.88	1.34	34.04	3.70	93.98	3.94	100.08	1.34	2.94	8	F1
GC200-6B	N/A	6	210.0	12.05	306.07	6.61	167.89	8.62	218.95	8.86	225.04	33.00	72.60	1	B
GC3.2-8F1	2	8	3.2	5.28	134.11	1.44	36.58	2.48	62.99	2.72	69.09	0.96	2.11	10	F1
GC0.8-12WL	N/A	12	.8	3.78	96.1	.98	24.89	2.44	61.98	2.44	61.98	.37	.80	20	WL
GC2.3-12F1	4	12	2.5	7.01	178.05	1.38	35.05	2.36	59.94	2.60	66.04	1.03	2.27	20	F1
GC4-12F1	5	12	4.0	3.54	89.92	2.76	70.10	3.98	101.09	4.21	106.93	1.66	3.65	10	F1
GC4.5-12F1	5	12	4.6	3.54	89.92	2.76	70.10	3.98	101.09	4.21	106.93	1.66	3.65	10	F1
GC5-12F1	5	12	5.4	3.54	89.92	2.76	70.10	3.98	101.09	4.21	106.93	1.66	3.65	10	F1
GC7-12F1	7	12	7.0	5.94	150.88	2.56	65.02	3.72	94.49	3.94	100.08	2.54	5.59	5	F1
GC7-12F2	6	12	7.0	5.94	150.88	2.56	65.02	3.72	94.49	3.94	100.08	2.54	5.59	5	F2
GC7-12F1-FR	7	12	7.0	5.94	150.88	2.56	65.02	3.72	94.49	3.94	100.08	2.54	5.59	5	F1
GC10-12F2	6	12	10.5	5.94	150.88	3.86	98.04	3.74	95.00	3.98	101.09	3.40	7.48	5	F2
GC12-12F2	6	12	12.0	5.94	150.88	3.86	98.04	3.74	95.00	3.98	101.09	3.90	8.58	4	F2
GC18-12F2	N/A	12	18.0	7.15	181.61	3.03	76.96	6.59	167.39	6.59	167.39	5.70	12.54	2	F2
GC18-12NB	N/A	12	18.0	7.15	181.61	3.03	76.96	6.59	167.39	6.59	167.39	5.70	12.54	2	NB
GC26-12F2	N/A	12	26.0	6.56	166.62	6.89	175.01	4.92	124.97	4.92	124.97	8.80	19.36	1	F2
GC26-12NB	N/A	12	26.0	6.56	166.62	6.89	175.01	4.92	124.97	4.92	124.97	8.80	19.36	1	NB
GC35-12NB	N/A	12	37.0	7.68	195.07	5.12	130.05	6.46	164.08	7.09	180.09	11.70	25.74	1	NB
GC38-12NB	N/A	12	38.0	7.76	197.10	6.50	165.10	6.69	169.93	6.69	169.93	13.60	29.92	1	NB
GC55-12NB	N/A	12	56.0	8.98	228.09	5.43	137.92	8.19	208.03	8.98	228.09	17.70	38.94	1	NB

## TERMINAL TYPES


Our Industrial Battery Part Numbers are easy to understand. This chart breaks down the Industrial Battery Part Numbers.

GC Family	7 - Amp Hours	12 - Voltage	F1 Terminal Type
Family - GC Electronics	<u>Amp Hours</u>	<u>Voltage</u>	<u>Terminal Types</u>
	0.8 /20 hr	6 = 6 Volts	F1 = 0.187 Quick Disconnect Tabs
	1.2 /20 hr	8 = 8 Volts	F2 = 0.250 Quick Disconnect Tabs
	1.4 /20 hr	12 = 12 Volts	B = Threaded Insert Bolt
	26 /20 hr		NB = Terminal Post with Nut and Bolt
	2.3 /20 hr		WL = Wire Leads
	35 /20 hr		

**F1 = 0.187" (4.7625mm) Spade**  
0.187" (4.75mm) x 0.032" (0.8mm)  
quick disconnect tabs



**F2 = 0.250" (6.35mm) Spade**  
0.250" (6.35mm) x 0.032" (0.8mm)  
quick disconnect tabs



**NB = Terminal Post with Nut & Bolt**

**WL = Wire Leads**

Options

FR = Flame Retardant