


## TRANSZORB® Transient Voltage Suppressors



DO-204AC (DO-15)

PRIMARY CHARACTERISTICS	
$V_{WM}$	5.0 V to 170 V
$P_{PPM}$	500 W
$P_D$	3.0 W
$I_{FSM}$ (uni-directional only)	70 A
$T_J$ max.	175 °C

### DEVICES FOR BI-DIRECTION APPLICATIONS

For bi-directional types, use C or CA suffix (e.g. SA5.0C, SA170CA).

Electrical characteristics apply in both directions.

### FEATURES

- Glass passivated chip junction
- Available in uni-directional and bi-directional
- 500 W peak pulse power capability with a 10/1000  $\mu$ s waveform, repetitive rate (duty cycle): 0.01 %
- Excellent clamping capability
- Very fast response time
- Low incremental surge resistance
- Solder dip 260 °C, 40 s
- Component in accordance to RoHS 2002/95/EC and WEEE 2002/96/EC



### TYPICAL APPLICATIONS

Use in sensitive electronics protection against voltage transients induced by inductive load switching and lighting on ICs, MOSFET, signal lines of sensor units for consumer, computer, industrial and telecommunication.

### MECHANICAL DATA

**Case:** DO-204AC, molded epoxy over passivated chip  
Molding compound meets UL 94 V-0 flammability rating

Base P/N-E3 - RoHS compliant, commercial grade  
Base P/NHE3 - RoHS compliant, high reliability/automotive grade (AEC Q101 qualified)

**Terminals:** Matte tin plated leads, solderable per J-STD-002 and JESD22-B102

E3 suffix meets JESD 201 class 1A whisker test, HE3 suffix meets JESD 201 class 2 whisker test

**Polarity:** For uni-directional types the color band denotes cathode end, no marking on bi-directional types

MAXIMUM RATINGS ( $T_A = 25$ °C unless otherwise noted)			
PARAMETER	SYMBOL	VALUE	UNIT
Peak pulse power dissipation with a 10/1000 $\mu$ s waveform <sup>(1)</sup> (Fig. 1)	$P_{PPM}$	500	W
Peak pulse current with a 10/1000 $\mu$ s waveform <sup>(1)</sup>	$I_{PPM}$	See next table	A
Power dissipation on infinite heatsink at $T_A = 75$ °C (Fig. 5)	$P_D$	3.0	W
Peak forward surge current, 10 ms single half sine-wave uni-directional only	$I_{FSM}$	70	A
Maximum instantaneous forward voltage at 35 A for uni-directional only <sup>(2)</sup>	$V_F$	3.5	V
Operating junction and storage temperature range	$T_J, T_{STG}$	- 55 to + 175	°C

#### Notes:

(1) Non-repetitive current pulse, per Fig. 3 and derated above  $T_A = 25$  °C per Fig. 2

(2) 8.3 ms single half sine-wave or equivalent square wave, duty cycle = 4 per minute maximum

<b>ELECTRICAL CHARACTERISTICS</b> ( $T_A = 25\text{ }^\circ\text{C}$ unless otherwise noted)								
DEVICE TYPE	BREAKDOWN VOLTAGE $V_{BR}$ AT $I_T$ <sup>(1)</sup> (V)		TEST CURRENT $I_T$ (mA)	STAND-OFF VOLTAGE $V_{WM}$ (V)	MAXIMUM REVERSE LEAKAGE AT $V_{WM}$ $I_D$ <sup>(3)</sup> ( $\mu\text{A}$ )	MAXIMUM PEAK PULSE CURRENT $I_{PPM}$ <sup>(2)</sup> (A)	MAXIMUM CLAMPING VOLTAGE AT $I_{PPM}$ $V_C$ (V)	MAXIMUM TEMPERATURE COEFFICIENT OF $V_{BR}$ (mV/ $^\circ\text{C}$ )
	MIN.	MAX.						
SA5.0	6.40	7.30	10	5.0	600	52.1	9.6	5.0
SA5.0A <sup>(4)</sup>	6.4	7.07	10	5.0	600	54.3	9.2	5.0
SA6.0	6.67	8.15	10	6.0	600	43.9	11.4	5.0
SA6.0A	6.67	7.37	10	6.0	600	48.5	10.3	5.0
SA6.5	7.22	8.82	10	6.5	400	40.7	12.3	5.0
SA6.5A	7.22	7.98	10	6.5	400	44.7	11.2	5.0
SA7.0	7.78	9.51	10	7.0	150	37.6	13.3	6.0
SA7.0A	7.78	8.60	10	7.0	150	41.7	12.0	6.0
SA7.5	8.33	10.2	1.0	7.5	50	35.0	14.3	7.0
SA7.5A	8.33	9.21	1.0	7.5	50	38.8	12.9	7.0
SA8.0	8.89	10.9	1.0	8.0	25	33.3	15.0	7.0
SA8.0A	8.89	9.83	1.0	8.0	25	36.8	13.6	7.0
SA8.5	9.44	11.5	1.0	8.5	10	31.4	15.9	8.0
SA8.5A	9.44	10.4	1.0	8.5	10	34.7	14.4	8.0
SA9.0	10.0	12.2	1.0	9.0	5.0	29.6	16.9	9.0
SA9.0A	10.0	11.1	1.0	9.0	5.0	32.5	15.4	9.0
SA10	11.1	13.6	1.0	10	1.0	26.6	18.8	10
SA10A	11.1	12.3	1.0	10	1.0	29.4	17.0	10
SA11	12.2	14.9	1.0	11	1.0	24.9	20.1	11
SA11A	12.2	13.5	1.0	11	1.0	27.5	18.2	11
SA12	13.3	16.3	1.0	12	1.0	22.7	22.0	12
SA12A	13.3	14.7	1.0	12	1.0	25.1	19.9	12
SA13	14.4	17.6	1.0	13	1.0	21.0	23.8	13
SA13A	14.4	15.9	1.0	13	1.0	23.3	21.5	13
SA14	15.6	19.1	1.0	14	1.0	19.4	25.8	14
SA14A	15.6	17.2	1.0	14	1.0	21.6	23.2	14
SA15	16.7	20.4	1.0	15	1.0	18.6	26.9	16
SA15A	16.7	18.5	1.0	15	1.0	20.5	24.4	16
SA16	17.8	21.8	1.0	16	1.0	17.4	28.8	19
SA16A	17.8	19.7	1.0	16	1.0	19.2	26.0	17
SA17	18.9	23.1	1.0	17	1.0	16.4	30.5	20
SA17A	18.9	20.9	1.0	17	1.0	18.1	27.6	19
SA18	20.0	24.4	1.0	18	1.0	15.5	32.2	21
SA18A	20.0	22.1	1.0	18	1.0	17.1	29.2	20
SA20	22.2	27.1	1.0	20	1.0	14.0	35.8	25
SA20A	22.2	24.5	1.0	20	1.0	15.4	32.4	23
SA22	24.4	29.8	1.0	22	1.0	22.7	39.4	28
SA22A	24.4	26.9	1.0	22	1.0	14.1	35.5	25
SA24	26.7	32.6	1.0	24	1.0	11.6	43.0	31
SA24A	26.7	29.5	1.0	24	1.0	12.9	38.9	28
SA26	28.9	35.3	1.0	26	1.0	10.7	46.6	31
SA26A	28.9	31.9	1.0	26	1.0	11.9	42.1	30
SA28	31.1	38.0	1.0	28	1.0	10.0	50.1	35
SA28A	31.1	34.4	1.0	28	1.0	11.0	45.4	31
SA30	33.3	40.7	1.0	30	1.0	9.3	53.5	39
SA30A	33.3	36.8	1.0	30	1.0	10.0	48.4	36
SA33	36.7	44.9	1.0	33	1.0	8.5	59.0	42
SA33A	36.7	40.6	1.0	33	1.0	9.4	53.3	39
SA36	40.0	48.9	1.0	36	1.0	7.8	64.3	46
SA36A	40.0	44.2	1.0	36	1.0	8.6	58.1	41



<b>ELECTRICAL CHARACTERISTICS</b> ( $T_A = 25\text{ }^\circ\text{C}$ unless otherwise noted)								
DEVICE TYPE	BREAKDOWN VOLTAGE $V_{BR}$ AT $I_T$ <sup>(1)</sup> (V)		TEST CURRENT $I_T$ (mA)	STAND-OFF VOLTAGE $V_{WM}$ (V)	MAXIMUM REVERSE LEAKAGE AT $V_{WM}$ $I_D$ <sup>(3)</sup> ( $\mu\text{A}$ )	MAXIMUM PEAK PULSE CURRENT $I_{PPM}$ <sup>(2)</sup> (A)	MAXIMUM CLAMPING VOLTAGE AT $I_{PPM}$ $V_C$ (V)	MAXIMUM TEMPERATURE COEFFICIENT OF $V_{BR}$ ( $\text{mV}/^\circ\text{C}$ )
	MIN.	MAX.						
SA40	44.4	54.3	1.0	40	1.0	7.0	71.4	51
SA40A	44.4	49.1	1.0	40	1.0	7.8	64.5	46
SA43	47.8	58.4	1.0	43	1.0	6.5	76.7	55
SA43A	47.8	52.8	1.0	43	1.0	7.2	69.4	50
SA45	50.0	61.1	1.0	45	1.0	6.2	80.3	58
SA45A	50.0	55.3	1.0	45	1.0	6.9	72.7	52
SA48	53.3	65.2	1.0	48	1.0	5.8	85.5	63
SA48A	53.3	58.9	1.0	48	1.0	6.5	77.4	56
SA51	56.7	69.3	1.0	51	1.0	5.5	91.1	66
SA51A	56.7	62.7	1.0	51	1.0	6.1	82.4	61
SA54	60.0	73.3	1.0	54	1.0	5.2	96.3	71
SA54A	60.0	66.3	1.0	54	1.0	5.7	87.1	65
SA58	64.4	78.7	1.0	58	1.0	4.9	103	78
SA58A	64.4	71.2	1.0	58	1.0	5.3	93.6	70
SA60	66.7	81.5	1.0	60	1.0	4.7	107	80
SA60A	66.7	73.7	1.0	60	1.0	5.2	96.8	71
SA64	71.1	86.9	1.0	64	1.0	4.4	114	86
SA64A	71.1	78.6	1.0	64	1.0	4.9	103	76
SA70	77.8	95.1	1.0	70	1.0	4.0	125	94
SA70A	77.8	86.0	1.0	70	1.0	4.4	113	85
SA75	83.3	102	1.0	75	1.0	3.7	134	101
SA75A	83.3	92.1	1.0	75	1.0	4.1	121	91
SA78	86.7	106	1.0	78	1.0	3.6	139	105
SA78A	86.7	95.8	1.0	78	1.0	4.0	126	95
SA85	94.4	115	1.0	85	1.0	3.3	151	114
SA85A	94.4	104	1.0	85	1.0	3.6	137	103
SA90	100	122	1.0	90	1.0	3.1	160	121
SA90A	100	111	1.0	90	1.0	3.4	146	110
SA100	111	136	1.0	100	1.0	2.8	179	135
SA100A	111	123	1.0	100	1.0	3.1	162	123
SA110	122	149	1.0	110	1.0	2.6	196	148
SA110A	122	135	1.0	110	1.0	2.8	177	133
SA120	133	163	1.0	120	1.0	2.3	214	162
SA120A	133	147	1.0	120	1.0	2.6	193	146
SA130	144	176	1.0	130	1.0	2.2	230	175
SA130A	144	159	1.0	130	1.0	2.4	209	158
SA150	167	204	1.0	150	1.0	1.9	268	203
SA150A	167	185	1.0	150	1.0	2.1	243	184
SA160	178	218	1.0	160	1.0	1.7	257	217
SA160A	178	197	1.0	160	1.0	1.9	259	196
SA170	189	231	1.0	170	1.0	1.6	304	230
SA170A	189	209	1.0	170	1.0	1.8	275	208

**Notes:**

- (1) Pulse test:  $t_p \leq 50\text{ ms}$
- (2) Surge current waveform per Fig. 3 and derate per Fig. 2
- (3) For bi-directional types with  $V_{WM}$  of 10 V and less, the  $I_D$  limit is doubled
- (4) For the bi-directional SA5.0CA, the maximum  $V_{BR}$  is 7.25 V
- (5) All terms and symbols are consistent with ANSI/IEEE C62.35

ORDERING INFORMATION (Example)				
PREFERRED P/N	UNIT WEIGHT (g)	PREFERRED PACKAGE CODE	BASE QUANTITY	DELIVERY MODE
SA5.0A-E3/54	0.432	54	4000	13" diameter paper tape and reel
SA5.0AHE3/54 <sup>(1)</sup>	0.432	54	4000	13" diameter paper tape and reel

**Note:**

(1) Automotive grade AEC Q101 qualified

**RATINGS AND CHARACTERISTICS CURVES**

( $T_A = 25\text{ }^\circ\text{C}$  unless otherwise noted)




Figure 1. Peak Pulse Power Rating Curve




Figure 3. Pulse Waveform




Figure 2. Pulse Derating Curve




Figure 4. Maximum Non-Repetitive Forward Surge Current Uni-Directional Only




Figure 5. Steady State Power Derating Curve




Figure 8. Incremental Clamping Voltage Curve Uni-Directional




Figure 6. Capacitance




Figure 9. Incremental Clamping Voltage Curve Bi-Directional




Figure 7. Incremental Clamping Voltage Curve Uni-Directional




Figure 10. Incremental Clamping Voltage Curve Bi-Directional




Figure 11. Typical Instantaneous Forward Voltage





Figure 12. Breakdown Voltage Temperature Coefficient Curve

**PACKAGE OUTLINE DIMENSIONS** in inches (millimeters)

**DO-204AC (DO-15)**





## Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and/or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk and agree to fully indemnify and hold Vishay and its distributors harmless from and against any and all claims, liabilities, expenses and damages arising or resulting in connection with such use or sale, including attorneys fees, even if such claim alleges that Vishay or its distributor was negligent regarding the design or manufacture of the part. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.

## Material Category Policy

**Vishay Intertechnology, Inc. hereby certifies that all its products that are identified as RoHS-Compliant fulfill the definitions and restrictions defined under Directive 2011/65/EU of The European Parliament and of the Council of June 8, 2011 on the restriction of the use of certain hazardous substances in electrical and electronic equipment (EEE) - recast, unless otherwise specified as non-compliant.**

**Please note that some Vishay documentation may still make reference to RoHS Directive 2002/95/EC. We confirm that all the products identified as being compliant to Directive 2002/95/EC conform to Directive 2011/65/EU.**