



Active

PRODUCT DRAWING
English

3D PDF

> See All Documentation

TE CONNECTIVITY (TE)
KCS01X024EACA=CONTACTOR,CURRENT SENSE

Kilovac

KCS01X024EACA
TE Internal Number: 1618408-3

EU RoHS Compliant
EU ELV Compliant

Contact Arrangement: **1 Form X, SPST-NO DM**

Wire Size (AWG) **26**

Contact Current Rating (A) **100**

Coil Voltage (Max) (VDC) **28**

Coil Resistance (Ω) **218**
> See All Features

North America

DISTRIBUTOR	QUANTITY	DATE AS OF
MASTER ELECTRONICS CORP. 1-888-473-5297	25	2017/06/06
DIGI-KEY ELECTRONICS 1-800-344-4539	18	2017/06/06
NEWARK ELEMENT14 1-800-463-9275	2	2017/06/05

SAVE TO LIST

FIND SIMILAR PRODUCTS



Products

Industries & Solutions

Search



Resources
Sign In

Please review product documents or [contact us](#) for the latest agency approval information. Please Note: Use the Product Drawing for all design activity.

Product Type Features

Terminal Configuration	2 x M5 x .8
Contactor Type	Sealed
Product Category	Electromechanical Relays
Model	KCS Series
Product Type	Contactor
Product Classification	Relays - Contactors
Arc Cover	Without

Configuration Features

Auxiliary Switch Contact Arrangement	None
--------------------------------------	-------------

Electrical Characteristics

Coil Voltage (Max) (VDC)	28
Coil Resistance (Ω)	218
Coil Voltage Rating (VDC)	18 – 28
Contact Switching Voltage (Max) (VDC)	600
Actuating System	DC

Contact Features

About TE Connectivity For Partners Customer Support **CALL US** **LIVE CHAT** United States

Our Company
Events
TE News Center
Careers
Investors
Corporate Responsibility
Terms and Conditions of Sale

Distributors
Suppliers

Email or Call Us
Find Authorized Distributors
What's New on TE.com
Product FAQs
Share Feedback

Select Country & Language
United States (EN)
Germany (DE)
China (中文)
Japan (日本語)
Find Your Country

Terms of Use | Privacy | Cookie Policy | Accessibility | Site Map

© 2017 TE Connectivity Corporation. All Rights Reserved



Coil Wire Length **381 mm [15 in]**

Packaging Features

Packaging Method	Individual
------------------	-------------------

Other

Torque (in-lbs)	30 – 40 in-lbs
-----------------	-----------------------

Compatible Products

> Contact Product Support

Feedback