


| | | |
|----------|--------|-----------|
| DASH NO. | M CODE | MADE FROM |
|----------|--------|-----------|



NOTES:

- FOR USE WITH RG-58/U CABLE GROUP.
- FOR CABLING INSTRUCTIONS SEE CP-1002
- MATERIALS:
 INSULATOR: TEFLON, ASTM-D4894
 GASKET: SILICONE RUBBER, A-A-59588
 SPRING WASHER: BER. COP, ASTM-B-196
 ALL OTHER METAL PARTS: BRASS, ASTM-B-16
- FINISHES:
 CENTER CONTACT: GOLD PLATE, ASTM-B488
 .00050 MIN. GOLD, .00050 MIN. NICKEL, COPPER STRIKE TYPE II, CLASS 1.25
 ALL METAL PARTS: SILVER PLATE, ASTM-B700
 .000200 TO .000300 SILVER, .00020 MIN. COPPER UNDERPLATE
- ELECTRICAL CHARACTERISTICS:
 OPERATING VOLTAGE: 3500 VAC
 5000 VDC

UNLESS OTHERWISE SPECIFIED

- ALL DIMENSIONS IN INCHES [MILLIMETERS].
- TOLERANCES:
 .XXX ±.004 .XX ±.010
 [.XXX ±.10] [.XX ±.25]
 FRACTIONS: X/Y ±.010 [.25] ANGLES: ± 1'

★ CRITICAL DIMENSIONS

PART NO. KV-59-04

| REVISIONS | |
|-----------|--------------------------------------|
| ISSUE | CHANGES |
| 9 | CN 37290 C REDRAWN PG 03/21/97 |
| 10 | CN 38577 E TML 05/30/02 |
| M | ER9130 DRK 06/20/08 |

CUSTOMER SALES DRAWING

SCALE 4:1

APPROX SURFACE AREA

USED ON

REF:

PLUG, MHV

| | |
|------------|---------------|
| DRAWN JEP | DATE 06-07-83 |
| DESIGN MJB | DATE 06-07-83 |
| APPR. | DATE |

KINGS
by WINCHESTER

Winchester Electronics
62 Barnes Industrial
Road North
Wallingford, CT 06492

B
SIZE

SDKV-59-04