



### INDEX


### PAGE

#### Network Wiring

Advantages . . . . .	P-2
Structured Wiring Layout . . . . .	P-3
netSELECT® Network Enclosures . . . . .	P-4
netSELECT® Network Modules and Accessories . . . . .	P-5
Universal Consolidation Blocks, Patch Panels, Patch Cords and Plugs . . . . .	P-7
Wall Mounted Enclosures and Accessories . . . . .	P-8
Cable Management Racks . . . . .	P-10
Power Strips . . . . .	P-12

#### Data Communications and Audio Video

Voice/Data Jacks . . . . .	P-13
F-Type Connectors . . . . .	P-14
Audio/Video Connectors . . . . .	P-15
RCA Connectors . . . . .	P-16
Multimedia Face Plates . . . . .	P-18
iSTATION™ Face Plates . . . . .	P-19
Outlet Frames and Plates . . . . .	P-20
HDMI Products . . . . .	P-21
iSTATION™ HD Connectors, and VGA Horizontal Runs . . . . .	P-22
iSTATION™ Front-Loading Frames and Modules . . . . .	P-23
iSTATION™ Audio/Video Modules . . . . .	P-24
iSTATION™ Surface Mount Boxes . . . . .	P-26
Telephone Surface Mount Wall Jacks . . . . .	P-27
Molded-In Voice/Data/Video . . . . .	P-28
Molded-In Plates . . . . .	P-30
Telephone Wall Jacks . . . . .	P-32
Labeling Solutions . . . . .	P-33
Tools and Accessories . . . . .	P-34
Standard UTP Wiring Conventions . . . . .	P-36





netSELECT® is an innovative network solution that's perfect for any home or small office. The netSELECT® System satisfies the need for a dependable, flexible system that can accommodate all of today's fast-changing voice, data and video requirements. Built-in flexibility makes it easy to upgrade and keep pace with evolving technologies.



### Easy for Installers

An easy-to-hang cabinet featuring surface or recess mounts between 16-inch studs on center, 2 x 4 inch minimum. netSELECT® modular components snap into the box horizontally or vertically, optimizing space. A blank module provides flexibility for installers to use their own choice of manufacturer's active components. Also included: A reversible and lockable hinged door, ample cable entrance locations and a complete offering of jacks, plates and other work station accessories.

### Easy for Users

Built in flexibility to upgrade and keep pace with evolving technologies. An easy-to-read label helps you to keep track of the system's infrastructure. The white powder coat finish provides a clean, durable chassis to house all components.


### Features and Benefits

- Share single analog, cable or DSL internet connection
- Local file access
- Shared peripherals
- Multiple telephone distribution
- Call handling (PBX)
- Video distribution
- Play games that allow multi-users
- Support home automation systems

# Network Wiring Structured Wiring Layout



Today's Communications Entail a Lot More Than Just Talking.  
netSELECT® Keeps You Connected—Internet, Voice, Data and Entertainment



Communications




Entertainment  
Gaming/Video



Internet/Networking





- Flush or surface mount enclosure (hardware provided)
- Hinged cover can be mounted to swing from either side
- Integral trim ring on hinged door
- Horizontal and vertical module mounting holes
- Unique 89D bracket mounting holes
- Integral cable management slots and tie-wraps
- Material: 20-18 gauge steel
- Finish: white; powder coat

### NETWORK ENCLOSURES



**NSOBX10**

Dimensions: 14.38"W x 10"H x 3.96"D  
 Knockouts:  
 Top: four 1½" NPT or completely open combo  
 Bottom: four 1½" NPT or completely open combo  
 Side: 1½" NPT

#### 10" Network Enclosure

##### for MDU and Modular Applications

	Catalog Number
10" Enclosure with hinged cover	<b>NSOBX10</b>
10" Enclosure with panel cover	<b>NSOBX10BC</b>
10" Enclosure box only	<b>NSOBX10B</b>
Hinged door	<b>NSOBX10D</b>
Panel cover	<b>NSOBX10C</b>
Blank plate for custom KO patterns	<b>NSOPLT</b>



**NSOBOX28**

28" Enclosure  
 Dimensions: 14.38"W x 28"H x 3.96"D  
 Knockouts:  
 Top: five 1½" NPT  
 Bottom: two power kit knockouts  
 Back: four 1" NPT

48" Enclosure  
 Dimensions: 14.38"W x 48"H x 3.96"D  
 Knockouts:  
 Top: five 1½" NPT  
 Bottom: two power kit knockouts  
 Back: none

#### 28" and 48" Network Enclosures

#### Catalog Number

28" Enclosure with hinged cover	<b>NSOBOX28</b>
28" Enclosure with panel cover	<b>NSOBOX28BC</b>
28" Enclosure box only	<b>NSOBOX28B</b>
Hinged door	<b>NSOBOX28D</b>
Vented door	<b>NSOBOX28DL</b>
Panel cover	<b>NSOBOX28C</b>
2"D Extension bracket with ventilation and WiFi KOs	<b>NSOBOX28X2</b>
48" Enclosure with hinged cover	<b>NSOBOX48</b>



**NSOBOX14**

Dimensions: 14.38"W x 14"H x 3.96"D  
 Knockouts:  
 Top: two 1" dia. and three 1½" NPT combo  
 Bottom: one 1" Dia. and one 1½" NPT combo; 1 power kit knockout  
 Back: two 1" NPT

#### 14" Network Enclosure

#### Catalog Number

14" Enclosure with hinged cover	<b>NSOBOX14</b>
14" Enclosure with panel cover	<b>NSOBOX14BC</b>
14" Enclosure box only	<b>NSOBOX14B</b>
Hinged door	<b>NSOBOX14D</b>
Vented door	<b>NSOBOX14DL</b>
Panel cover	<b>NSOBOX14C</b>
2"D Extension bracket with ventilation and WiFi KOs	<b>NSOBOX14X2</b>

#### Pre-Configured Network Enclosure 14"H with Hinged Cover

Basic home network kit includes:  
 1 box with hinged cover (NSOBOX14);  
 1 primary 8-port telephone module (NSOPTM8); 1 4-way coaxial splitter module (NSOVDM4)



**NSOBNK14**

#### Power Kits

#### Catalog Number

Standard power kit; includes duplex receptacle 15A 125V; NEMA 5-15R; electrical steel box and wallplate	<b>NSOKP*</b>
Surge suppression power kit; includes duplex receptacle 15A 125V; NEMA 5-15R; 240 Joules/15,000A protection per mode; electrical steel box and wallplate	<b>NSOKPS*</b>



#### Lock Kit, Chromed Steel

#### FLOCK1\*

Includes two keys; eliminates unwanted tampering



#### WiFi Antenna Kit

#### NSOKA\*

Attaches to extension brackets; 7dB gain for better coverage

Note: \*Not UL or cULus listed.





**NSOTVM6**

- Dimensions: 6.47"W x 2.95"H; except NSOMTM24 6.47"W x 6.00"H
- Meets FCC part 68 standard
- Finish: black; powder coat
- Material: 18 gauge steel or high impact plastic
- Snaps horizontally or vertically into enclosure
- Telephone and data modules are TIA-568A wired

### NETWORK MODULES

Combo Module, 6-Port	Catalog Number
Telephone and video	<b>NSOTVM6</b>
Telephone, video and cat. 5e	<b>NSOTVDM6</b>
Category 5e data upgrade kit	<b>NSODK6</b>

6-port telephone panel and 6-port coaxial splitter with optional 6-port cat. 5e panel; provides voice, video, and data distribution; for use with NSOBOX10 and NS790xx plates to quickly establish a comprehensive network



**NSOTVDM6**

Data Module, 8-Port	Catalog Number
Category 5e data module; supports up to gigabit ethernet with front 110 punch-down terminations	<b>NSODM8</b>
Category 6 data module; supports enhanced transmission speeds beyond gigabit ethernet	<b>NSODM8C6</b>



**NSODM8**

Primary Telephone Module, 8-Port	Catalog Number
Supports 8 phone outlets with up to 4 incoming lines for voice; RJ31X interface jack for security system connection; RJ45 jack interfaces with optional NSOETM8 telephone expansion module for additional extensions	<b>NSOPTM8</b>



Multiport Patchable Telecom Module	Catalog Number
Terminates lines via modular plug to accommodate flexibility, by changing plug locations; reconfigure where phone lines go at the panel level; includes nine RJ45 jumper cords	<b>NSOMTM24</b>



Expansion Telephone Module, 8-Port	Catalog Number
Adds additional 8 phone outlets with up to 4 incoming lines when used with the primary telephone module; RJ45 jumper cord to connect with NSOPTM8 primary telephone module	<b>NSOETM8</b>



Combination Module, 6-Port Telephone and 1-Port Cat. 5e Data	Catalog Number
Provides basic telephone and data delivery in a small package; allows data lines to be converted to voice, with the move of a patch cord	<b>NSO6P1DM</b>



Blank Module Plate	Catalog Number
Allows mounting of active components (i.e., switches, routers) or other devices (66 blocks, audio components) onto a modular platform; can be custom drilled or used with two self-adhesive VELCRO® strips included to mount components onto module	<b>NSOBM</b>



VELCRO® is a registered trademark of Velcro Industries B.V.

Specifications are subject to change without notice.

[www.bryant-electric.com](http://www.bryant-electric.com)

**BRYANT®**

### AUDIO/VIDEO MODULES AND ACCESSORIES

4-Way Coaxial Splitter Modules	Catalog Number
1 Ghz; basic unit	<b>NSOVM4</b>
2.3 Ghz; enhanced capability	<b>NSOVM42G</b>



**NSOVM4**

6-Way Coaxial Splitter Modules	Catalog Number
1 Ghz; basic unit	<b>NSOVM6</b>
2.3 Ghz; enhanced capability	<b>NSOVM62G</b>



**NSOVM6**

8-Way Coaxial Splitter Modules	Catalog Number
1 Ghz; basic unit	<b>NSOVM8</b>
2.3 Ghz; enhanced capability	<b>NSOVM82G</b>



**NSOVM8**

8 Room Audio Module	Catalog Number
Distributes audio from an amplifier to matching volume controllers; supports up to eight rooms of audio; power handling – 200W RMS@20° C per channel; requires impedance matching volume controls	<b>NSOAM8</b>



Gold Speaker Post Connectors and Plugs	Ring Color	Catalog Number
Speaker post connector; office white housing	Black	<b>SFSPGBK*</b>
	Red	<b>SFSPGR*</b>
Speaker banana plugs; gold; screw termination; 10-packs	Black	<b>SPPBK10*</b>
	Red	<b>SPPR10*</b>

Note: \*Not UL Listed.



**SFSPGR**



**SPPBK10**

Fixed Video Amplifier Module, 10dB	Catalog Number
Provides video signal amplification for incoming cable feeds recommended for use when more than four outputs are installed or when signal level is low; provides 10dB forward path gain and supports current digital cable systems and modems with a passive return; includes RG59 cable jumper to connect amplifier to passive video splitter	<b>NSOVAMP</b>



Panel Bracket Adapter	Catalog Number
For use with adapter panels shown below and FSP series modules; snap mounts into structured cabling enclosures	<b>NSOFSB</b>



F-Connector Adapter Panel	Catalog Number
Six populated coaxial connectors	<b>FSPFP6X</b>



Modular Adapter Panel	Catalog Number
Six blank openings for Bryant jacks and modular connectors	<b>FSPHD6X</b>



Slide Stereo Volume Controller	Catalog Number
Decorator styling; includes both ivory and white slides and frames; power handling – 70W RMS@20° C; impedance matching for up to eight pairs of speakers	<b>NSOSAVC</b>



Rotary Stereo Volume Controller	Catalog Number
Decorator styling; includes both ivory and white knobs and frames; power handling – 70W RMS@20° C; impedance matching for up to eight pairs of speakers	<b>NSORAVC</b>





- Meets ANSI/TIA category 6 and category 5e standards
- cULus Listed
- Consolidation blocks mount in or on the wall for telephone, data and AV systems



**NS5E12U**



**NS612U**



**NS5E24U**



**NS5E48U**



**NS624U**





**NS648U**

### UNIVERSAL NETSELECT® PATCH PANELS

Description	Catalog Number
Category 5e 12-port universal consolidation block; 89D bracket mount	<b>NS5E12U</b>
Category 6 12-port universal consolidation block; 89D bracket mount	<b>NS612U</b>
Category 5e universal patch panel; 24-port - 1.75 inch H (1 rack unit)	<b>NS5E24U</b>
48-port - 3.50 inch H (2 rack units)	<b>NS5E48U</b>
Category 6 universal patch panel 24-port - 1.75 inch H (1 rack unit)	<b>NS624U</b>
48-port - 3.50 inch H (2 rack units)	<b>NS648U</b>

- Meets and exceeds ANSI/TIA - Category 6 or Category 5e standards
- UL and cUL Listed

### UNIVERSAL PATCH CORDS, CATEGORY 6 AND CATEGORY 5e

Description	Color	1-Foot	3-Foot	5-Foot	7-Foot	10-Foot	15-Foot	20-Foot	25-Foot
Category 5e Patch Cord 	Blue	<b>SC5EB01</b>	<b>SC5EB03</b>	<b>SC5EB05</b>	<b>SC5EB07</b>	<b>SC5EB10</b>	<b>SC5EB15</b>	<b>SC5EB20</b>	<b>SC5EB25</b>
	Gray	<b>SC5EGY01</b>	<b>SC5EGY03</b>	<b>SC5EGY05</b>	<b>SC5EGY07</b>	<b>SC5EGY10</b>	<b>SC5EGY15</b>	<b>SC5EGY20</b>	<b>SC5EGY25</b>
	Yellow	<b>SC5EY01</b>	<b>SC5EY03</b>	<b>SC5EY05</b>	<b>SC5EY07</b>	<b>SC5EY10</b>	<b>SC5EY15</b>	<b>SC5EY20</b>	<b>SC5EY25</b>
	Red	<b>SC5ER01</b>	<b>SC5ER03</b>	<b>SC5ER05</b>	<b>SC5ER07</b>	<b>SC5ER10</b>	<b>SC5ER15</b>	<b>SC5ER20</b>	<b>SC5ER25</b>
Category 6 Patch Cord 	Blue	<b>SC6B01</b>	<b>SC6B03</b>	<b>SC6B05</b>	<b>SC6B07</b>	<b>SC6B10</b>	<b>SC6B15</b>	<b>SC6B20</b>	<b>SC6B25</b>
	Gray	<b>SC6GY01</b>	<b>SC6GY03</b>	<b>SC6GY05</b>	<b>SC6GY07</b>	<b>SC6GY10</b>	<b>SC6GY15</b>	<b>SC6GY20</b>	<b>SC6GY25</b>
	Yellow	<b>SC6Y01</b>	<b>SC6Y03</b>	<b>SC6Y05</b>	<b>SC6Y07</b>	<b>SC6Y10</b>	<b>SC6Y15</b>	<b>SC6Y20</b>	<b>SC6Y25</b>
	Red	<b>SC6R01</b>	<b>SC6R03</b>	<b>SC6R05</b>	<b>SC6R07</b>	<b>SC6R10</b>	<b>SC6R15</b>	<b>SC6R20</b>	<b>SC6R25</b>

#### Snap-On Plugs

- All plug contacts 50 micro-inch gold-plated
- IDC wire contacts
- Plastic: 94V-0 rated
- For voice applications
- For solid cable



**BRFTP4P**

#### SNAP-ON MODULAR PLUG

Description	AWG	Catalog Number
Snap-on; 8-position modular plug	24 to 26	<b>BRFTP4P</b>



RE4B



REKF



REKFF



REKRSJ20

REKR24



REKH



REKHS

## RE-BOX® WALL MOUNT ENCLOSURES

### PRE-CONFIGURED VERSION

Delivery: 1 base/rear section with welded 19-inch brackets for 2 hubs; 1 front door with 2 locks (NSQ tool); 1 set 19-inch extension brackets for 2 additional hubs (RE4xx only); 1 set 19-inch bottom hinge brackets for patch panels

Switch Capacity	Max. Hub Depth	Height	Width	Depth	Color	Catalog Number
2U	14.0" (356)	32.0" (818)	24.2" (615)	7.0" (178)	Light gray	<b>RE2</b>
2U	14.0" (356)	32.0" (818)	24.2" (615)	7.0" (178)	Black	<b>RE2B</b>
5U	14.0" (356)	32.0" (818)	24.2" (615)	10.0" (254)	Light gray	<b>RE4</b>
5U	14.0" (356)	32.0" (818)	24.2" (615)	10.0" (254)	Black	<b>RE4B</b>
5U	22.0" (559)	42.0" (1067)	24.2" (615)	10.0" (254)	Light gray	<b>RE4X</b>
5U	22.0" (559)	42.0" (1067)	24.2" (615)	10.0" (254)	Black	<b>RE4XB</b>

### USER-CONFIGURABLE VERSION

Delivery: 1 base/rear section and 1 front door with 2 locks (NSQ tool) (IDF24 has only 1 lock)

RWU	Height	Width	Depth	Color	Catalog Number
2U	24.0" (600)	24.2" (615)	7.0" (178)	Light Gray	<b>IDF24L*</b>
2U	24.0" (600)	24.2" (615)	10.0" (254)	Light Gray	<b>IDF24</b>
4U	32.0" (813)	24.2" (615)	10.0" (254)	Light Gray	<b>IDF32</b>
6U	42.0" (1067)	24.2" (615)	10.0" (254)	Light Gray	<b>IDF42</b>

Note: IDF24L and IDF24 do not use the same base section; knock-out patterns are different.  
See page P-9 for key lock kits.  
\*Front door includes Cat60 key locks.

## RE-BOX® WALL MOUNT ENCLOSURE ACCESSORIES

Description	Size	Catalog Number
Door conversion kit (RE2 to RE4); light gray	—	<b>REKU</b>
Door conversion kit (RE2 to RE4); black	—	<b>REKUB</b>
Fan kit; 57CFM (order 1 per RE2, 2 per RE4, RE4X, IDF)	—	<b>REKF</b>
Fan plate, blank	4.0" fan	<b>H1KB</b>
Fan	125V/7A	<b>REKEF</b>
Fan filter kit	—	<b>REKFF</b>
Filler panel	3.5"H	<b>MCCBP350</b>
Joining kits	Top-to-bottom Side-by-side (IDF24, IDF24L) Side-by-side (RE2, RE4, IDF32) Side-by-side (RE4X, IDF42)	<b>REKTJ</b> <b>REKSJ20</b> <b>REKSJ30</b> <b>REKSJ40</b>
Padlock hasp kit	—	<b>REKH</b>
For mounting NSO modules (see pages P-5 and P-6)	—	<b>REKHS</b>
Recessed mounting kit	24.0" 32.0" 42.0"	<b>REKR24</b> <b>REKR32</b> <b>REKR42</b>
Reverse hinge kit	—	<b>REKI</b>
Sound dampening kit	—	<b>REKS</b>





### QUADCAB® WALL MOUNT ENCLOSURE

Cabinet Depth	Door Style	Color*	Catalog Number
20.0"	Window	Black	<b>HSQXX</b>
26.0"	Window	Black	<b>HSQXX26</b>
36.0"	Window	Black	<b>HSQXX36</b>
20.0"	Solid	Black	<b>HSQXXS</b>
26.0"	Solid	Black	<b>HSQXXS26</b>
36.0"	Solid	Black	<b>HSQXXS36</b>


Note: **XX** = Height in inches. '24' = 24"/12 Rack Units; '36' = 36"/19 Rack Units; '48' = 48"/26 Rack Units.

\*For Office White, add "W" to the end of the catalog number.

Delivery: 1 rear section (arrives disassembled, facilitating installation); 1 front door; 2 19-inch mounting angles; 1 center section with 2 CH751 locks; 2 top/bottom cover plates; 2 hinge pins; 2 security cotter pins.



**REKZ**



**REKFP**

**HIDRUBCKIT**



**REKP**



**REKGB**



**REKMT10**



**CTK**

### RE-BOX® AND QUADCAB® WALL MOUNT ENCLOSURE ACCESSORIES

Description	Size/Style	Catalog Number
¼" plywood backboard	20.0" x 19.0"	<b>REKBB20</b>
	30.0" x 19.0"	<b>REKBB30</b>
	40.0" x 19.0"	<b>REKBB40</b>
110/66 block mounting rails	—	<b>REK110</b>
DIN rail utility box	—	<b>DRUBTVSS15</b>
DIN rail communications kit	—	<b>HIDRUBCKIT</b>
Equipment mounting bracket	8.75"	<b>REKZ</b>
	5.25"	<b>REKZL</b>
Fiber optic bracket	—	<b>REKFP</b>
Filler panel	3.5"H	<b>MCCBP350</b>
Gasket kit - padded grommet	30'	<b>HWKGT</b>
Gasket kit - adhesive backed foam	10'	<b>REKG</b>
Ground kit	—	<b>REKGB</b>
Ground strap kit; economy	—	<b>REKEGS</b>
Key lock kits:	CH751	<b>CKL751</b>
	333	<b>CKL333</b>
	Bellcore 716	<b>CKL716</b>
	Cat60	<b>CKLCAT60</b>
	Cat70	<b>CKLCAT70</b>
Patch panel mounting bracket	7.0"	<b>REK19</b>
	3.5"	<b>REK19L</b>
Power kit; 20A	—	<b>REKP</b>
Thermostat	—	<b>CTK</b>



**HPW84RR19**

## EQUIPMENT RACKS Inches (mm)

Rack Height	Rack Units	Mounting Width	Finish*	Catalog Number
48.0" (1219)	24	19.0" (483)	Black	<b>HPW48RR19</b>
48.0" (1219)	24	23.0" (584)	Black	<b>HPW48RR23</b>
68.5" (1676)	36	19.0" (483)	Black	<b>HPW66RR19</b>
84.0" (2134)	45	19.0" (483)	Black	<b>HPW84RR19</b>
84.0" (2134)	45	23.0" (584)	Black	<b>HPW84RR23</b>
89.7" (2286)	48	19.0" (483)	Black	<b>HPW90RR19</b>
89.7" (2286)	48	23.0" (584)	Black	<b>HPW90RR23</b>
96.0" (2438)	51	19.0" (483)	Black	<b>HPW96RR19</b>
96.0" (2438)	51	23.0" (584)	Black	<b>HPW96RR23</b>

Note: Shipped unassembled.

\*For aluminum mill finish rack, add "ML" to end of catalog number.

## 19" EQUIPMENT RACKS WITH 6" WIDE 'Z' CHANNELS Feet (m)

Rack Height	Rack Units	Finish	Cover Style	Catalog Number
7.0' (2.13)	45	Black	Hinged	<b>CS1976H</b>
7.0' (2.13)	45	Black	Clip on	<b>CS1976</b>
7.0' (2.13)	45	Aluminum	Clip on	<b>CS1976A</b>

Note: Delivery: 1 rack - 7'H (HPW84RR19); 2 vertical organizers (VS76/VS76A).



**HPW84RR19ML**

## 19" EQUIPMENT RACKS WITH 3.25" WIDE 'C' CHANNELS Feet (m)

Rack Height	Rack Units	Finish	Cover Style	Catalog Number
7.0' (2.13)	45	Black	Hinged	<b>CS1973H</b>
7.0' (2.13)	45	Black	Clip on	<b>CS1973</b>
7.0' (2.13)	45	Aluminum	Clip on	<b>CS1973A</b>

Note: Delivery: 1 rack - 7'H (HPW84RR19); 2 vertical organizers (VS73/VS73A); 4 covers (VCC3/VCC3A).



VS76H

## VERTICAL CHANNELS FOR 7' RACK Feet (m)

Rack Height	Hinged Cover Color	Catalog Number	
		6"W	3.25"W
7' (2.134)	Black	VS76H	VS73H

## 6" 'Z' CHANNEL WITH COVER Feet (m)

Rack Height	Catalog Number	
	Black	Aluminum
7' (2.134) or 7.5' (2.29)	VS76	VS76A
8' (2.44)	VS86	VS86A

## 3/4" 'C' CHANNEL Feet (m)

Rack Height	Catalog Number	
	Black	Aluminum
7' (2.13)	VS73	VS73A

## METAL ORGANIZERS, 19" WIDE Inches (mm)



HC219CC3N

Rack Units	Panel Height	Front Ring Depth	Rear Ring Depth	Catalog Number
1U	1.75" (44.5)	3.5" (88.9)	6.0" (152.4)	HC119GC36*
1U	1.75" (44.5)	3.5" (88.9)	—	HC119MS3N
2U	3.5" (88.9)	3.5" (88.9)	—	HC219CE3N
2U	3.5" (88.9)	6.0" (152.4)	—	HC219CE6N
2U	3.5" (88.9)	3.5" (88.9)	4.6" (116.8)	HC219CC3N
2U	3.5" (88.9)	3.5" (88.9)	—	HC219MS3N
3U	5.25" (133.4)	6.0" (152.4)	—	HC319CE6N

Note: \*Includes rear wire frame and rear cover—no pass-through holes.

## PLASTIC FINGER DUCT ORGANIZERS Inches (mm)



HC119CC3P

Rack Units	Panel Height	Front Duct Depth	Rear Duct Depth	Catalog Number
2U	3.5" (88.9)	3.0" (76.2)	5.0" (127.0)	HC219CC3P
2U	3.5" (88.9)	3.0" (76.2)	—	HC219CE3P
1U	1.75" (44.5)	3.0" (76.2)	5.0" (127.0)	HC119CC3P
1U	1.75" (44.5)	3.0" (76.2)	—	HC119CE3P



HPWPWR

### POWER STRIPS, 19" RACK MOUNT

All units utilize 1U of rack space and include circuit breakers (except PR10720); 15A units feature 10-foot cable with NEMA 5-15P plug; 20A units feature 10-foot cable with NEMA 5-20P plug; delivery: 1 strip, 1 kit mounting hardware

Electrical Specification	Receptacle Type	Outlets		Mounting Style	Surge Protected	Transformer Spaced	Current Switch	Current Monitor	Catalog Number
		Front	Rear						
15A/120V	NEMA 5-15R	0	10	Flush	No	No	Yes	No	HPWPWR
15A/120V	NEMA 5-15R	0	10	Flush	Yes*	No	Yes	No	MCCPSS19
15A/120V	NEMA 5-15R	4	4	Recess	Yes*	Yes	No	No	MCCPSS19TS
20A/120V	NEMA 5-20R	0	10	Flush	No	No	No	No	PR10120
20/16A, 120/250V	IEC 320-C13	10	0	Flush	No	No	Yes	No	PR10720**
15A/120V	NEMA 5-15R	0	6	Flush	No	No	No	No	PR0615
20A/120V	NEMA 5-20R	0	10	Flush	No	No	Yes	Yes	PR1020
60A/250V	IEC 320-C19	0	3	Adjustable	No	N/A	CB/Switch	No	PR0360***

Note: \*Joule rating = 720J. \*\*PR10720 includes an IEC 320 (C-20) inlet for power input; vertical mount brackets are also included. \*\*\*PR0360 features 10' cable with IEC 60A 2P/3W plug.



MCCPSS19TS

### POWER STRIPS, VERTICAL MOUNT

All units include circuit breakers and full length mounting bracket; feature 10-foot cable (except PR20820I); delivery: 1 strip; 1 kit mounting hardware; universal mounting brackets

Electrical Specification	Receptacle Type	Outlets Front	Type	Plug Circuits	Number of Protected	Surge Switch	Current Monitor	Catalog Number
15A/120V	NEMA 5-15R	10	NEMA 5-15P	1	No	No	No	PR104
20A/120V	NEMA 5-20R	10	NEMA 5-20P	1	No	No	No	PR10420
15A/120V	NEMA 5-15R	20	NEMA 5-15P	1	No	No	No	PR206
20A/120V	NEMA 5-20R	20	NEMA 5-20P	1	No	No	No	PR20620
20A/120V	NEMA 5-20R	20	NEMA 5-20P	1	No	Yes	Yes	PR20820DRTL
30A/120V	NEMA 5-20R	20	NEMA L5-30P	1	No	No	No	PR20830
20/16A/circuit 120V	NEMA 5-20R	20	NEMA 5-20P	2	No	No	No	PR20820A*
20/16A-120/250V	IEC 320C-13	20	IEC 320 (C-20)	1	No	No	No	PR20820I**
30/24A-250V	IEC 320C-13	24	NEMA L6-30P	1	No	No	No	PR24

Note: \*PR20820A features (2) 20A circuits each fed by 10-foot cable with NEMA 5-20 plug. \*\*PR20820I includes an IEC 320 (C-20) inlet for power input.



PR20620

### MOUNTING BRACKETS FOR POWER STRIPS

Power Strip Style	Description	Catalog Number
19" Rack mount	Adjustable mounting brackets; allows numerous recess or flush mount	PRAMB*
19" Rack mount	Panel mount brackets; ideal for zero 'U' mounting applications by effectively allowing the unit to be hung from a cross beam or flat surface	PRPMB*
Vertical mount	'L' brackets – turned 'in' for rack/rail mounting; turned 'out' to extend mounting options an additional 8 inches	PRSLB4*
Vertical mount	Left, right, front or back rail mounting; may be installed in conjunction with other equipment mounted in the same 'U' space	PREZB*

Note: \*Not UL recognized.



PRAMB

### MOUNTING BRACKETS OPTIONS

Type	Catalog Number	Integral Fixed Brackets	Pre-Assembled Brackets Included	Optional Brackets Available
19" Rack Mount	HPWPWR, MCCPSS19, PR10120, PR0615, PR1020	Flush Mount	N/A	N/A
	MCCPSS19TS	N/A	Recess Mount	PRAMB, PRPMB
	PR10720	N/A	Flush Mount and PRSLB4	PREZB
	PR0360	N/A	PRAMB	PRPMB
Vertical Mount	PR104, PR10420, PR206, PR20620, PR20820A, PR20820I, PR20820DRTL, PR24, PR20830	N/A	Full Length	PRSLB4, PREZB




PRSLB4



netSELECT® Voice/Data Jacks provide for a wide range of applications ranging from high performance data demands of Cat. 6 and Cat. 5e, to simple voice grade USOC jacks.

- Easy to terminate angled wiring towers
- Meets FCC part 68
- Meets and exceeds ANSI/TIA - Category 6 and Category 5e standards
- UL Listed and CSA Certified

Customize your jack selections and look.



## MODULAR JACKS



NSJ6W



NSJ5EW



NSJ6W

Description	Color	Catalog Number	Bag of 25 Catalog Number
Category 6 jacks	Almond	NSJ6AL	NSJ6AL25
	Black	NSJ6BK	NSJ6BK25
	Blue	NSJ6B	NSJ6B25
	Gray	NSJ6GY	NSJ6GY25
	Green	NSJ6GN	NSJ6GN25
	Ivory	NSJ6I	NSJ6I25
	Light Almond	NSJ6LA	NSJ6LA25
	Orange	NSJ6OR	NSJ6OR25
	Red	NSJ6R	NSJ6R25
	White	NSJ6W	NSJ6W25
	Yellow	NSJ6Y	NSJ6Y25
	Category 5e jacks	Almond	NSJ5EAL
Black		NSJ5EBK	NSJ5EBK25
Blue		NSJ5EB	NSJ5EB25
Gray		NSJ5EGY	NSJ5EGY25
Green		NSJ5EGN	NSJ5EGN25
Ivory		NSJ5EI	NSJ5EI25
Light Almond		NSJ5ELA	NSJ5ELA25
Orange		NSJ5EOR	NSJ5EOR25
Red		NSJ5ER	NSJ5ER25
White		NSJ5EW	NSJ5EW25
Yellow		NSJ5EY	NSJ5EY25
Category USOC jacks		Almond	NSJUAL
	Black	NSJUBK	—
	Blue	NSJUB	—
	Gray	NSJUGY	—
	Green	NSJUGN	—
	Ivory	NSJUI	—
	Light Almond	NSJULA	—
	Orange	NSJUOR	—
	Red	NSJUR	—
	White	NSJUW	—
	Yellow	NSJUY	—

Note: For a complete list of A/V and fiber modular connectors see pages P-14 to P-17.



**SFFGEI**



**SFGFEI**



**NSF70I**



**SFRFGEI**



**FRG625**



**SFSV110BK**



**SFBOW**



**SFBGOW**

## F-TYPE CONNECTORS

Description	Color	Catalog Number	
		Standard Bulkhead	Recessed
Gold F-type coupler bulkhead; female to female	Almond	<b>SFFGAL</b>	<b>SFGRFAL</b>
	Black	<b>SFFGBK</b>	<b>SFGRFBK</b>
	Gray	<b>SFFGGY</b>	<b>SFGRFGY</b>
	Ivory	<b>SFFGEI</b>	<b>SFGRFEI</b>
	Light Almond	<b>SFFGLA</b>	<b>SFGRFLA</b>
	Office White	<b>SFFGOW</b>	<b>SFGRFOW</b>
	White	<b>SFFGW</b>	<b>SFGRFW</b>
Nickel F-type coupler bulkhead; female to female	Almond	<b>NSF70AL</b>	—
	Black	<b>NSF70BK</b>	—
	Gray	<b>NSF70GY</b>	—
	Ivory	<b>NSF70I</b>	—
	Light Almond	<b>NSF70LA</b>	—
	Office White	<b>NSF70OW</b>	—
Nickel F-type coupler bulkhead; male to female; bag of 25		<b>NSC9025*</b>	—
Gold F-type to RCA bulkhead; female to female	Black	<b>SFRFGBK*</b>	—
	Gray	<b>SFRFGGY*</b>	—
	Ivory	<b>SFRFGEI*</b>	—
	Office White	<b>SFRFGOW*</b>	—
	White	<b>SFRFGW*</b>	—

Note: \*Not UL Listed.

## RG6 AND RG59 COMPRESSION CONNECTORS

Termination Type	Cable Type	Number of Pieces	Catalog Number
Compression	RG6/RG6 Quad Shield	25	<b>FRG625*</b>
Compression	RG59	25	<b>FRG5925*</b>
Crimp	RG6	25	<b>FRG6C25*</b>

Note: \*Not UL Listed.

See page P-35 for compression tool.

## S-VIDEO CONNECTORS

Description	Color	Catalog Number
S-video; 110 punch-down	Black	<b>SFSV110BK</b>
S-video; female to female coupler	Black	<b>SFSVBK</b>

## BNC CONNECTORS

Description	Color	Catalog Number
Nickle finish; BNC connector	Black	<b>SFBBK</b>
	Gray	<b>SFBGY</b>
	Ivory	<b>SFBEI</b>
	Light Almond	<b>SFBLA</b>
	Office White	<b>SFBOW</b>
	White	<b>SFBW</b>
Gold finish; BNC connector	Black	<b>SFBGBK</b>
	Gray	<b>SFBGGY</b>
	Ivory	<b>SFBGEI</b>
	Light Almond	<b>SFBGLA</b>
	Office White	<b>SFBGOW</b>
	White	<b>SFBGW</b>



SFSPGR



SPPBK10



SF35FF



SF35ST



SFC5EBK



SFC5EW



SF5ECOGY



SFUSBABB



SFUSBAAB

## GOLD SPEAKER POST CONNECTORS AND PLUGS

Description	Ring Color	Catalog Number
Speaker post connector; office white housing	Black	SFSPGBK*
	Red	SFSPGR*
Speaker post/banana plugs	Black	SPPBK10*
	Red	SPPR10*

Note: \*Not UL Listed.

## 3.5MM STEREO JACKS

Description	Housing Color	Catalog Number
3.5mm F/F coupler	Black	SF35FFBK*
	Gray	SF35FFGY*
	Ivory	SF35FFEI*
	Light Almond	SF35FFLA*
	Office White	SF35FFOW*
	White	SF35FFW*
3.5mm stereo jack	Black	SF35SJBK*
	Gray	SF35SJGY*
	Ivory	SF35SJEI*
	Light Almond	SF35SJLA*
	Office White	SF35SJ*
	White	SF35SJW*
3.5mm screw term	Black	SF35STBK*
	Gray	SF35STGY*
	Ivory	SF35STEI*
	Light Almond	SF35STLA*
	Office White	SF35STOW*
	White	SF35STW*

Note: \*Not UL Listed.

## INLINE COUPLERS

Description	Color	Catalog Number
Wiring: T568A/B	Black	SFC5EBK*
	White	SFC5EW*
Crossover	Gray	SF5ECOGY*

Note: \*Not UL Listed.

## USB CONNECTORS

Description	Color	Catalog Number
Format: A-to-B	Blue	SFUSBABB
	Office White	SFUSBABOW
	White	SFUSBABW
Format: A-to-A	Blue	SFUSBAAB
	Office White	SFUSBAAOW
	White	SFUSBAAW



## RCA CONNECTORS



SFRC110R

Description	Housing Color	Catalog Number	
		Standard Bulkhead	Recessed
RCA 110 punch-down; black housing	Blue	SFRC110B	—
	Green	SFRC110GN	—
	Red	SFRC110R	—
	White	SFRC110W	—
	Yellow	SFRC110Y	—



SFRCRFFEI



SFRCRREI

RCA gold pass through; female to female; red interior	Almond	SFRCRFFAL	SFRCRRAL
	Black	SFRCRFFBK	SFRCRRBK
	Gray	SFRCRFFGY	SFRCRRGY
	Ivory	SFRCRFFEI	SFRCRREI
	Light Almond	SFRCRFFLA	SFRCRRLA
	Office White	SFRCRFF	SFRCRR
	White	SFRCRFFW	SFRCRRW



SFRCWFFEI



SFRCWREI

RCA gold pass through; female to female; white interior	Almond	SFRCWFFAL	SFRCWRAL
	Black	SFRCWFFBK	SFRCWRBK
	Gray	SFRCWFFGY	SFRCWRGY
	Ivory	SFRCWFFEI	SFRCWREI
	Light Almond	SFRCWFFLA	SFRCWRLA
	Office White	SFRCWFF	SFRCWR
	White	SFRCWFFW	SFRCWRW



SFRCYFFEI



SFRCYREI

RCA gold pass through; female to female; yellow interior	Almond	SFRCYFFAL	SFRCYRAL
	Black	SFRCYFFBK	SFRCYRBK
	Gray	SFRCYFFGY	SFRCYRGY
	Ivory	SFRCYFFEI	SFRCYREI
	Light Almond	SFRCYFFLA	SFRCYRLA
	Office White	SFRCYFF	SFRCYR
	White	SFRCYFFW	SFRCYRW



SFRCBFFEI



SFRCBREI

RCA gold pass through; female to female; blue interior	Almond	SFRCBFFAL	SFRCBRAL
	Black	SFRCBFFBK	SFRCBRBK
	Gray	SFRCBFFGY	SFRCBRGY
	Ivory	SFRCBFFEI	SFRCBREI
	Light Almond	SFRCBFFLA	SFRCBRLA
	Office White	SFRCBFFOW	SFRCBROW
	White	SFRCBFFW	SFRCBRW



SFRCGFFEI



SFRCGREI

RCA gold pass through; female to female; green interior	Almond	SFRCGNFFAL	SFRCGNRAL
	Black	SFRCGNFFBK	SFRCGNRBK
	Gray	SFRCGNFFGY	SFRCGNRGY
	Ivory	SFRCGNFFEI	SFRCGNREI
	Light Almond	SFRCGNFFLA	SFRCGNRLA
	Office White	SFRCGNFFOW	SFRCGNROW
	White	SFRCGNFFW	SFRCGNRW



SFRCBKFFEI



SFRCBKREI

RCA gold pass through; female to female; black interior	Almond	SFRCBKFFAL	SFRCBKRAL
	Black	SFRCBKFFBK	SFRCBKRBK
	Gray	SFRCBKFFGY	SFRCBKRGY
	Ivory	SFRCBKFFEI	SFRCBKREI
	Light Almond	SFRCBKFFLA	SFRCBKRLA
	Office White	SFRCBKFF	SFRCBKR
	White	SFRCBKFFW	SFRCBKRW



SFRCORFFEI



SFRCORREI

RCA gold pass through; female to female; orange interior	Almond	SFRCORFFAL	SFRCORRAL
	Black	SFRCORFFBK	SFRCORRBK
	Gray	SFRCORFFGY	SFRCORRGY
	Ivory	SFRCORFFEI	SFRCORREI
	Light Almond	SFRCORFFLA	SFRCORRLA
	Office White	SFRCORFFOW	SFRCORROW
	White	SFRCORFFW	SFRCORRW





**SFRCCR**



**SFRCW**



**SFRCY**



**SFRCBOW**



**SFRCGNOW**



**SFRCBKOW**



**SFRCOROW**



**SFB10**



**SFSBEI10**

## RCA CONNECTORS

Description	Housing Color	Standard Bulkhead Catalog Number
Solder coupler termination; red interior	Almond	<b>SFRCRAL</b>
	Black	<b>SFRCRBK</b>
	Gray	<b>SFRCRGY</b>
	Ivory	<b>SFRCREI</b>
	Light Almond	<b>SFRCLLA</b>
	Office White	<b>SFRCCR</b>
	White	<b>SFRCRW</b>
Solder coupler termination; white interior	Almond	<b>SFRCWAL</b>
	Black	<b>SFRCWBK</b>
	Gray	<b>SFRCWGY</b>
	Ivory	<b>SFRCWEI</b>
	Light Almond	<b>SFRCWLA</b>
	Office White	<b>SFRCW</b>
	White	<b>SFRCWW</b>
Solder coupler termination; yellow interior	Almond	<b>SFRCYAL</b>
	Black	<b>SFRCYBK</b>
	Gray	<b>SFRCYGY</b>
	Ivory	<b>SFRCYEI</b>
	Light Almond	<b>SFRCYLA</b>
	Office White	<b>SFRCY</b>
	White	<b>SFRCYW</b>
Solder coupler termination; blue interior	Almond	<b>SFRCBAL</b>
	Black	<b>SFRCBBK</b>
	Gray	<b>SFRCBGY</b>
	Ivory	<b>SFRCBEI</b>
	Light Almond	<b>SFRCBLA</b>
	Office White	<b>SFRCBOW</b>
	White	<b>SFRCBW</b>
Solder coupler termination; green interior	Almond	<b>SFRCGNAL</b>
	Black	<b>SFRCGNBK</b>
	Gray	<b>SFRCGNGY</b>
	Ivory	<b>SFRCGNEI</b>
	Light Almond	<b>SFRCGNLA</b>
	Office White	<b>SFRCGNOW</b>
	White	<b>SFRCGNW</b>
Solder coupler termination; black interior	Almond	<b>SFRCBKAL</b>
	Black	<b>SFRCBKBK</b>
	Gray	<b>SFRCBKGY</b>
	Ivory	<b>SFRCBKEI</b>
	Light Almond	<b>SFRCBKLA</b>
	Office White	<b>SFRCBKOW</b>
	White	<b>SFRCBKW</b>
Solder coupler termination; orange interior	Almond	<b>SFRCORAL</b>
	Black	<b>SFRCORBK</b>
	Gray	<b>SFRCORGY</b>
	Ivory	<b>SFRCOREI</b>
	Light Almond	<b>SFRCORLA</b>
	Office White	<b>SFRCOROW</b>
	White	<b>SFRCORW</b>

## BLANK INSERTS

Description	Color	Catalog Number	Smooth Catalog Number
Blank insert; 10-pack (order 1 to receive a bag of 10 blanks)	Almond	<b>SFBAL10</b>	<b>SFSBAL10</b>
	Black	<b>SFBBK10</b>	<b>SFSBBK10</b>
	Gray	<b>SFBGY10</b>	<b>SFSBGY10</b>
	Ivory	<b>SFBEI10</b>	<b>SFSBEI10</b>
	Light Almond	<b>SFBLA10</b>	<b>SFSBLA10</b>
	Office White	<b>SFB10</b>	<b>SFSB10</b>
	White	<b>SFBW10</b>	<b>SFSBW10</b>



netSELECT® multimedia face plates offer a perfect match to electrical wallplates for a consistent smooth finish look.

- Accepts AV and Voice/Data connectors
- High impact-resistant thermoplastic plate
- UL Listed 1863 - Communication Circuit Accessory
- CSA Certified

### MULTIMEDIA FACE PLATES



**NSP111**



**NSP121**



**NSP131**



**NSP141**



**NSP161**



**NSP241**



**NSP261**

Description	Color	Catalog Number	
		Standard	Mid-Size
1-Gang; 1-port plate	Almond	<b>NSP11AL</b>	<b>NSP101AL</b>
	Black	<b>NSP11BK</b>	<b>NSP101BK</b>
	Gray	<b>NSP11GY</b>	<b>NSP101GY</b>
	Ivory	<b>NSP11I</b>	<b>NSP101I</b>
	Light Almond	<b>NSP11LA</b>	<b>NSP101LA</b>
	White	<b>NSP11W</b>	<b>NSP101W</b>
1-Gang; 2-port plate	Almond	<b>NSP12AL</b>	<b>NSP102AL</b>
	Black	<b>NSP12BK</b>	<b>NSP102BK</b>
	Gray	<b>NSP12GY</b>	<b>NSP102GY</b>
	Ivory	<b>NSP12I</b>	<b>NSP102I</b>
	Light Almond	<b>NSP12LA</b>	<b>NSP102LA</b>
	White	<b>NSP12W</b>	<b>NSP102W</b>
1-Gang; 3-port plate	Almond	<b>NSP13AL</b>	<b>NSP103AL</b>
	Black	<b>NSP13BK</b>	<b>NSP103BK</b>
	Gray	<b>NSP13GY</b>	<b>NSP103GY</b>
	Ivory	<b>NSP13I</b>	<b>NSP103I</b>
	Light Almond	<b>NSP13LA</b>	<b>NSP103LA</b>
	White	<b>NSP13W</b>	<b>NSP103W</b>
1-Gang; 4-port plate	Almond	<b>NSP14AL</b>	<b>NSP104AL</b>
	Black	<b>NSP14BK</b>	<b>NSP104BK</b>
	Gray	<b>NSP14GY</b>	<b>NSP104GY</b>
	Ivory	<b>NSP14I</b>	<b>NSP104I</b>
	Light Almond	<b>NSP14LA</b>	<b>NSP104LA</b>
	White	<b>NSP14W</b>	<b>NSP104W</b>
1-Gang; 6-port plate	Almond	<b>NSP16AL</b>	<b>NSP106AL</b>
	Black	<b>NSP16BK</b>	<b>NSP106BK</b>
	Gray	<b>NSP16GY</b>	<b>NSP106GY</b>
	Ivory	<b>NSP16I</b>	<b>NSP106I</b>
	Light Almond	<b>NSP16LA</b>	<b>NSP106LA</b>
	White	<b>NSP16W</b>	<b>NSP106W</b>
2-Gang; 4-port plate	Almond	<b>NSP24AL</b>	—
	Black	<b>NSP24BK</b>	—
	Gray	<b>NSP24GY</b>	—
	Ivory	<b>NSP24I</b>	—
	Light Almond	<b>NSP24LA</b>	—
	White	<b>NSP24W</b>	—
2-Gang; 6-port plate	Almond	<b>NSP26AL</b>	—
	Black	<b>NSP26BK</b>	—
	Gray	<b>NSP26GY</b>	—
	Ivory	<b>NSP26I</b>	—
	Light Almond	<b>NSP26LA</b>	—
	White	<b>NSP26W</b>	—




### IFP FACE PLATES, WITH LABEL FIELDS, 1- AND 2-GANG



Color	1-Gang 1-Port	2-Port	3-Port	4-Port	6-Port	2-Gang 6-Port	9-Port	12-Port
Almond	IFP11AL	IFP12AL	IFP13AL	IFP14AL	IFP16AL	IFP26AL	—	—
Black	IFP11BK	IFP12BK	IFP13BK	IFP14BK	IFP16BK	IFP26BK	IFP29BK	IFP212BK
Gray	IFP11GY	IFP12GY	IFP13GY	IFP14GY	IFP16GY	IFP26GY	IFP29GY	IFP212GY
Ivory	IFP11EI	IFP12EI	IFP13EI	IFP14EI	IFP16EI	IFP26EI	IFP29EI	IFP212EI
Light Almond*	IFP11LA	IFP12LA	IFP13LA	IFP14LA	IFP16LA	IFP26LA	IFP29LA	IFP212LA
Office White	IFP11OW	IFP12OW	IFP13OW	IFP14OW	IFP16OW	IFP26OW	IFP29OW	IFP212OW
White	IFP11W	IFP12W	IFP13W	IFP14W	IFP16W	IFP26W	IFP29W	IFP212W

Note: \*Light Almond plates match Office White non-metallic raceway, boxes, jacks and connectors.

### STAINLESS STEEL FACE PLATES WITHOUT LABEL FIELDS



1-Gang 1-Port	2-Port	3-Port	4-Port	6-Port	2-Gang 4-Port	6-Port	9-Port	12-Port
SSF11	SSF12	SSF13	SSF14	SSF16	SSF204	SSF206	SSF209	SSF212

### STAINLESS STEEL FACE PLATES WITH LABEL FIELDS



1-Gang	Catalog Number
1-Port	SSFL11
2-Port	SSFL12
3-Port	SSFL13
4-Port	SSFL14
6-Port	SSFL16

### DUPLEX AND DECORATOR PLATES WITH LABEL FIELDS



Color	Duplex Plate	Decorator Plate
Almond	IFP18AL	IFP126AL
Office White	IFP18OW	IFP126OW

### STANDARD DUPLEX AND DECORATOR PLATES WITH NO LABEL FIELDS



Color	1-Gang Duplex Plate	1-Gang Decorator Plate	2-Gang Decorator Plate
Almond	NP8AL	NP26AL	NP262AL
Black	NP8BK	NP26BK	NP262BK
Gray	NP8GY	NP26GY	NP262GY
Ivory	NP8I	NP26I	NP262I
Light Almond*	NP8LA	NP26LA	NP262LA
White	NP8W	NP26W	NP262W

Note: \*Light Almond plates match Office White non-metallic raceway, boxes, jacks and connectors.

### 630 WALL PHONE PLATES



Description	Jack Format	Includes	Catalog Number
Stainless steel; 1-gang wall phone plate	Flush	6-position USOC gray jack, RJ25	P630S1GJ6
	Flush	8-position Cat. 5e, gray jack, RJ45	P630S1GJ8
	Recessed	6-position USOC gray jack, RJ25	P630SR1GJ6
	Recessed	8-position Cat. 5e, gray jack, RJ45	P630SR1GJ8



## DECORATOR OUTLET FRAMES

Description	Color	Catalog Number			
		2-Port	3-Port	4-Port	6-Port
netSELECT® decorator unloaded frames provide a stylized look for that finishing touch; multimedia jacks insert into frame for custom configuration; high impact-resistant thermoplastic frame	Almond	<b>NS612AL</b>	<b>NS613AL</b>	<b>NS614AL</b>	<b>NS616AL</b>
	Black	<b>NS612BK</b>	<b>NS613BK</b>	<b>NS614BK</b>	<b>NS616BK</b>
	Gray	<b>NS612GY</b>	<b>NS613GY</b>	<b>NS614GY</b>	<b>NS616GY</b>
	Ivory	<b>NS612I</b>	<b>NS613I</b>	<b>NS614I</b>	<b>NS616I</b>
	Light Almond	<b>NS612LA</b>	<b>NS613LA</b>	<b>NS614LA</b>	<b>NS616LA</b>
	White	<b>NS612W</b>	<b>NS613W</b>	<b>NS614W</b>	<b>NS616W</b>



Description	Color	Catalog Number
1-Gang adapter; .40" (10.3 mm) dia. hole; for use with rotary dimmers or to pull through AV or telephone cable	Almond	<b>NS621AL</b>
	Ivory	<b>NS621I</b>
	Light Almond	<b>NS621LA</b>
	White	<b>NS621W</b>



Description	Color	Catalog Number
1-Gang adapter blank; to fill an extra decorator opening or to create customized openings	Almond	<b>NS620AL</b>
	Ivory	<b>NS620I</b>
	Light Almond	<b>NS620LA</b>
	White	<b>NS620W</b>
4-Port; T568B; loaded	Black	<b>SL5E4B</b>
4-Port; T568A; loaded	Black	<b>SL5E4A</b>

## DUPLEX OUTLET FRAMES



BR106B



Q106W

Description	Color	Catalog Number
2-Port duplex; unloaded	Almond	<b>BR106AL</b>
	Black	<b>BR106B</b>
	Gray	<b>BR106G</b>
	Ivory	<b>BR106E</b>
	Light Almond	<b>BR106LA</b>
	Office White	<b>BR106OW</b>
	White	<b>BR106W</b>
4-Port duplex; unloaded	Almond	<b>Q106AL</b>
	Black	<b>Q106B</b>
	Gray	<b>Q106G</b>
	Ivory	<b>Q106E</b>
	Light Almond	<b>Q106LA</b>
	Office White	<b>Q106OW</b>
	White	<b>Q106W</b>

## SECURE-IT™ PLATES



TPF1W

TWPF1GY


Secure-IT™ plates protect mated and unmated connections from physical damage and unauthorized tampering. Available in tamper-resistant and weatherproof versions.

Description	Color	Catalog Number
Tamper-resistant plates	Black	<b>TPF1BK</b>
	Gray	<b>TPF1GY</b>
	Office White	<b>TPF1OW</b>
	White	<b>TPF1W</b>
NEMA 3R weatherproof plates	Gray	<b>TWPF1GY</b>



netSELECT® HDMI Decorator Frames deliver uncompromising digital audio and video wherever you need it. Unleash the full potential of your high definition display and audio installations.

- Third party tested for 1080p resolutions
- UL Listed - Communications Circuit Accessory
- CSA Certified



NS801W



NS802W



HDPC06BK



HDMIC1



HDMIT1

### HDMI PRODUCTS

Description	Color	Catalog Number
1-Gang; 1-port HDMI; decorator frame; female to female	Almond	NS801AL
	Black	NS801BK
	Gray	NS801GY
	Ivory	NS801I
	Light Almond	NS801LA
	White	NS801W
1-Gang; 2-port HDMI; decorator frame; female to female	Almond	NS802AL
	Black	NS802BK
	Gray	NS802GY
	Ivory	NS802I
	Light Almond	NS802LA
	White	NS802W

### HDMI CORDS

Description	Feet	Catalog Number
HDMI device patch cords HDMI (24 AWG)	3 ft.	HDPC03BK
	6 ft.	HDPC06BK
Link cords (connector to device) HDMI (24 AWG)	xx ft.	HDLXXBK
Coupler cords (coupler to device) HDMI (24 AWG)	xx ft.	HDCXXBK
Horizontal cords (connector to connector) HDMI (24 AWG)	xx ft.	HDHXXBK

Note: **XX** = Length in feet. 10 = 10 ft., 15 = 15 ft., 20 = 20 ft., 25 = 25 ft., 30 = 30 ft., Black and Non-Plenum only.

### HDMI CONNECTORS

Description	Packaging	Catalog Number
HDMI feed thru coupler	Single	HDMIC1
	10-Pack	HDMIC10
HDMI feed thru 4.0" tail	Single	HDMIT1
	10-Pack	HDMIT10



**IMBDS1W**



**IMBDSA15W**



**ISFBDSW**



**9GC10**



**9ST10**



**15GC10**



**15ST10**



**15A6P1**



**15S6P1**



**15N6P1**



**15N6P1**



**15T6P1**

### HD (HIGH DEFINITION) 15-PIN/9-PIN CONNECTORS AND MODULES

Description	Color	Catalog Number
Flat blank HD15/9 or HDMI module; 1 unit; 10-pack	Almond	<b>IMBDS1AL</b>
	Black	<b>IMBDS1BK</b>
	Gray	<b>IMBDS1GY</b>
	Ivory	<b>IMBDS1EI</b>
	Light Almond	<b>IMBDS1OW</b>
	Office White	<b>IMBDS1W</b>
Angled blank HD15/9 or HDMI module; 1 unit; 10-pack	Almond	<b>IMBDSA15AL</b>
	Black	<b>IMBDSA15BK</b>
	Gray	<b>IMBDSA15GY</b>
	Ivory	<b>IMBDSA15EI</b>
	Light Almond	<b>IMBDSA15LW</b>
	Office White	<b>IMBDSA15OW</b>
	White	<b>IMBDSA15W</b>

### HD 9-PIN AND HD 15-PIN VGA-STYLE CONNECTORS

Description	Packaging	Catalog Number
HD 9-pin F/F coupler	10-Pack	<b>9GC10*</b>
HD 9-pin screw term	10-Pack	<b>9ST10</b>
HD 15-pin F/F coupler	10-Pack	<b>15GC10*</b>
HD 15-pin screw term	10-Pack	<b>15ST10</b>
HD 15-pin to 8-pin angled 45°	1-Pack	<b>15A6P1</b>
	10-Pack	<b>15A6P10</b>
HD 15-pin to 8-pin straight 180°	1-Pack	<b>15S6P1</b>
	10-Pack	<b>15S6P10</b>
HD 15-pin to 8-pin angled 90°	1-Pack	<b>15N6P1</b>
	10-Pack	<b>15N6P10</b>
HD 15-pin to 8-pin 8.0" tail; 1-pack	1-Pack	<b>15T6P1</b>

Note: \*Not UL Listed.

### PLUG-N-PLAY VGA HORIZONTAL RUNS\*

Description	Catalog Number
VGA; 8-pin; non-plenum; black	<b>VGA6XXBK</b>
VGA; 8-pin; plenum; black	<b>VGA6PXXBK</b>
VGA; 8-pin; 15-pin F; non-plenum; black	<b>VG15F6XXBK</b>
VGA; 8-pin; 15-pin M; non-plenum; black	<b>VG15M6XXBK</b>
VGA; 8-pin; 15-pin M; plenum; black	<b>VG15MP6XXBK</b>

Note: \*Maximum supported distance varies by application and resolution. Refer to X-END™ brochure for details.  
XX = Length: 05, 10, 15, 20, 25, 30, 35, 40, 45, 50, 55, 60, 65, 70, 75, 80, 85, 90, 95, 100.



### MODULAR FACE PLATE FRAMES

Description	Color	Catalog Number
Modular face plate frame; 1-gang	Almond	<b>IMF1AL</b>
	Black	<b>IMF1BK</b>
	Gray	<b>IMF1GY</b>
	Ivory	<b>IMF1EI</b>
	Office White	<b>IMF1OW</b>
	White	<b>IMF1W</b>
Modular face plate frame; 2-gang	Almond	<b>IMF2AL</b>
	Black	<b>IMF2BK</b>
	Gray	<b>IMF2GY</b>
	Ivory	<b>IMF2EI</b>
	Office White	<b>IMF2OW</b>
	White	<b>IMF2W</b>
Raceway bezel frame	Almond	<b>KPIMBZAL</b>
	Gray	<b>KPIMBZGY</b>
	Office White	<b>KPIMBZOW</b>

### UNLOADED MODULES

Description	Color	Flat Catalog No.	Angled Catalog No.		
Modular; 1-port; 1 unit (flat); 1.5 unit (angled)	Almond	<b>IM1K1AL</b>	<b>IM1KA15AL</b>		
	Black	<b>IM1K1BK</b>	<b>IM1KA15BK</b>		
	Gray	<b>IM1K1GY</b>	<b>IM1KA15GY</b>		
	Ivory	<b>IM1K1EI</b>	<b>IM1KA15EI</b>		
	Office White	<b>IM1K1OW</b>	<b>IM1KA15OW</b>		
	White	<b>IM1K1W</b>	<b>IM1KA15W</b>		
Modular; 2-port; 1 unit (flat); 1.5 unit (angled)	Almond	<b>IM2K1AL</b>	<b>IM2KA15AL</b>		
	Black	<b>IM2K1BK</b>	<b>IM2KA15BK</b>		
	Gray	<b>IM2K1GY</b>	<b>IM2KA15GY</b>		
	Ivory	<b>IM2K1EI</b>	<b>IM2KA15EI</b>		
	Office White	<b>IM2K1OW</b>	<b>IM2KA15OW</b>		
	White	<b>IM2K1W</b>	<b>IM2KA15W</b>		
Description	Color	1 Duplex Catalog No.	2 Duplex Catalog No.		
	SC angled; 1.5 unit (1 duplex); 2 unit (2 duplex)	Black	<b>IM1SCA15BK</b>	<b>IM2SCA15BK</b>	
		Gray	<b>IM1SCA15GY</b>	<b>IM2SCA15GY</b>	
		Ivory	<b>IM1SCA15EI</b>	<b>IM2SCA15EI</b>	
		Office White	<b>IM1SCA15OW</b>	<b>IM2SCA15OW</b>	
White	<b>IM1SCA15W</b>	<b>IM2SCA15W</b>			
Description	Color	1 Port Catalog No.	2 Port Catalog No.		
	Modular recessed angle; 1.5 unit	Black	<b>IM1IA15BK</b>	<b>IM2IA15BK</b>	
		Gray	<b>IM1IA15GY</b>	<b>IM2IA15GY</b>	
		Ivory	<b>IM1IA15EI</b>	<b>IM2IA15EI</b>	
		Office White	<b>IM1IA15OW</b>	<b>IM2IA15OW</b>	
White	<b>IM1IA15W</b>	<b>IM2IA15W</b>			
Description	Color	.5 Unit Catalog No.	1 Unit Catalog No.	1.5 Unit Catalog No.	
	Flat blank	Almond	<b>IMB05AL</b>	<b>IMB1AL</b>	<b>IMB15AL</b>
		Black	<b>IMB05BK</b>	<b>IMB1BK</b>	<b>IMB15BK</b>
		Gray	<b>IMB05GY</b>	<b>IMB1GY</b>	<b>IMB15GY</b>
		Ivory	<b>IMB05EI</b>	<b>IMB1EI</b>	<b>IMB15EI</b>
Office White		<b>IMB05OW</b>	<b>IMB1OW</b>	<b>IMB15OW</b>	
White	<b>IMB05W</b>	<b>IMB1W</b>	<b>IMB15W</b>		



### iSTATION™ AUDIO/VIDEO MODULES (10-PACK)



Description	AV blank 1.5 unit	XLR screw terminal	XLR solder-type	Speakon® connector; solder-type	USB feed-thru; A-to-B	¼" stereo jack; solder-type
Catalog No.	<b>IMAVB15OW*</b>	<b>XLRST10</b>	<b>XLR10</b>	<b>SC10</b>	<b>USB10</b>	<b>14S10</b>

Note: \*Color listed is Office White, for other colors, replace "OW" with: "AL" = Almond; "BK" = Black; "EI" = Ivory; "GY" = Gray; "W" = White.



### 110 AUDIO VIDEO MODULES Feet (m)



**IMCR1101W**

Description	Housing Color	Catalog Number
RCA component; video to 110 termination; 1 unit; 75' (19.1) max. HD Cat 5, 5e, 6 UTP	Almond	<b>IMCR1101AL</b>
	Black	<b>IMCR1101BK</b>
	Electric Ivory	<b>IMCR1101EI</b>
	Gray	<b>IMCR1101GY</b>
	Office White	<b>IMCR1101OW</b>
	White	<b>IMCR1101W</b>



**IMSR1101W**

S-video; stereo RCA audio to 110 termination; 1 unit; 100' (25.4) max. Cat 5, 5e, 6 UTP	Almond	<b>IMSR1101AL</b>
	Black	<b>IMSR1101BK</b>
	Electric Ivory	<b>IMSR1101EI</b>
	Gray	<b>IMSR1101GY</b>
	Office White	<b>IMSR1101OW</b>
	White	<b>IMSR1101W</b>



**IMSV351101W**

S-video; 3.5mm stereo audio jack to 110 termination; 1 unit; 100' (25.4) max. Cat 5, 5e, 6	Black	<b>IMSV351101BK</b>
	Electric Ivory	<b>IMSV351101EI</b>
	Gray	<b>IMSV351101GY</b>
	Office White	<b>IMSV351101OW</b>
	White	<b>IMSV351101W</b>



**IMR1101W**

RCA composite; video; stereo; audio to 110 termination; 1 unit; 100' (25.4) max. Cat 5, 5e, 6	Almond	<b>IMR1101AL</b>
	Black	<b>IMR1101BK</b>
	Electric Ivory	<b>IMR1101EI</b>
	Gray	<b>IMR1101GY</b>
	Office White	<b>IMR1101OW</b>
	White	<b>IMR1101W</b>



**IMAR1101W**

RCA stereo; audio 110 termination; 1 unit; 100' (25.4) max. Cat 5, 5e, 6	Almond	<b>IMAR1101AL</b>
	Black	<b>IMAR1101BK</b>
	Electric Ivory	<b>IMAR1101EI</b>
	Gray	<b>IMAR1101GY</b>
	Office White	<b>IMAR1101OW</b>
	White	<b>IMAR1101W</b>





### SOLDER AUDIO VIDEO MODULES



**IMCRS15OW**



**IMCRS1OW**



**IM3RS1OW**



**IMRSJ1OW**

Description	Housing Color	Catalog Number
RCA component; video; stereo audio or RGBHV; solder; 1.5 unit	Almond	<b>IMCRS15AL*</b>
	Black	<b>IMCRS15BK*</b>
	Electric Ivory	<b>IMCRS15EI*</b>
	Gray	<b>IMCRS15GY*</b>
	Office White	<b>IMCRS15OW*</b>
RCA component; video; solder; 1 unit	Almond	<b>IMCRS1AL*</b>
	Black	<b>IMCRS1BK*</b>
	Electric Ivory	<b>IMCRS1EI*</b>
	Gray	<b>IMCRS1GY*</b>
	Office White	<b>IMCRS1OW*</b>
RCA composite; video; stereo audio; solder; 1 unit	Almond	<b>IM3RS1AL</b>
	Black	<b>IM3RS1BK</b>
	Electric Ivory	<b>IM3RS1EI</b>
	Gray	<b>IM3RS1GY</b>
	Office White	<b>IM3RS1OW</b>
RCA composite; video; 3.5mm stereo audio jack; solder; 1 unit	Almond	<b>IMRSJ1AL</b>
	Black	<b>IMRSJ1BK</b>
	Electric Ivory	<b>IMRSJ1EI</b>
	Gray	<b>IMRSJ1GY</b>
	Office White	<b>IMRSJ1OW</b>
White	<b>IMRSJ1W</b>	

Note: \*Not UL Listed.

### GOLD FEED-THROUGH AUDIO VIDEO RCA COUPLERS



**IMCRF1OW**



**IM3RF1OW**

Description	Housing Color	Catalog Number
RCA component; video; gold; pass-through; F/F coupler; 1 unit	Almond	<b>IMCRF1AL*</b>
	Black	<b>IMCRF1BK*</b>
	Electric Ivory	<b>IMCRF1EI*</b>
	Gray	<b>IMCRF1GY*</b>
	Office White	<b>IMCRF1OW*</b>
RCA composite; video; audio; gold; pass-through; F/F coupler; 1 unit	Almond	<b>IM3RF1AL</b>
	Black	<b>IM3RF1BK</b>
	Electric Ivory	<b>IM3RF1EI</b>
	Gray	<b>IM3RF1GY</b>
	Office White	<b>IM3RF1OW</b>
White	<b>IM3RF1W</b>	

Note: \*Not UL Listed.

### GOLD SPEAKER POSTS MODULES AND BANANA PLUGS



**IMSP1OW**




**SPPBK10**

**SPPR10**

Description	Housing Color	Catalog Number
Speaker post; gold, black and red; screw termination	Almond	<b>IMSP1AL</b>
	Black	<b>IMSP1BK</b>
	Electric Ivory	<b>IMSP1EI</b>
	Gray	<b>IMSP1GY</b>
	Office White	<b>IMSP1OW</b>
Speaker banana plugs; gold; screw termination; 10-packs	Black	<b>SPPBK10*</b>
	Red	<b>SPPR10*</b>

Note: \*Not UL Listed.



- Low-profile design
- Accepts XJ jacks, audio video and fiber connectors
- Provided with double-sided tape and mounting screws for easy installation
- UL and cULus Listed
- Constructed with a high-impact resistant, flame-retardant polymer
- ANSI/TIA-606A compliant



ISM10W



ISM20W



ISM40W



ISM60W



ISM120W

### ISM SURFACE MOUNT BOXES, 1- AND 2-PORT

Ideal for open office, compact surface mount environments, and retrofits to support data, voice, and multimedia applications; can be mounted with supplied surface mounting screws or double-sided adhesive tape

Color	1-Port Catalog Number	2-Port Catalog Number
Ivory	ISM1EI	ISM2EI
Office White	ISM1OW	ISM2OW
White	ISM1W	ISM2W

### ISM SURFACE MOUNT BOXES, 4- AND 6-PORT

Ideal for open office MUTOA cabling, compact surface mount environments, and retrofits to support data, voice, and multimedia applications; features adjustable furniture latches to provide an additional mounting option to common ANSI/TIA/EIA standard furniture openings, and solutions requiring fiber; box bases feature fiber storage posts that can store one meter fiber cable after termination

Color	4-Port Catalog Number	6-Port Catalog Number
Ivory	ISM4EI	ISM6EI
Office White	ISM4OW	ISM6OW
White	ISM4W	ISM6W

### ISM SURFACE MOUNT BOXES, 12-PORT

Ideal for open office MUTOA cabling, large capacity surface mount applications and retrofits to support data, voice, and multimedia installations. Can be mounted with supplied surface mounting screws or double-sided adhesive tape and mounted to NEMA electric boxes or relay racks

Color	12-Port Catalog Number
Ivory	ISM12EI
Office White	ISM12OW
White	ISM12W

# Network Wiring

## Telephone Surface Mount Wall Jacks



Telephone surface mount jacks are available in 4- or 6-conductor configurations for voice. Alternatively, multimedia surface mount boxes can be custom loaded for computer and media use.

- High impact-resistant thermoplastic
- Mounts using screws or double sided tape (both included)
- Meets FCC part 68
- UL Listed 1863 - Communication Circuit Accessory
- CSA Certified

### TELEPHONE SURFACE MOUNT WALL JACKS



Description	Color	Catalog Number
Telephone surface mount jack; 6-position; 4-conductor; screw terminations	Ivory White	<b>NS760I</b> <b>NS760W</b>



Telephone surface mount jack; 6-position; 6-conductor; screw terminations	Ivory White	<b>NS761I</b> <b>NS761W</b>
---	----------------	--------------------------------



### MODULAR SURFACE HOUSINGS

Description	Color	Catalog Number
Multimedia 1-port surface mount box; jack not included	Ivory White	<b>ISM1EI*</b> <b>ISM1W*</b>



Multimedia 2-port surface mount box; jacks not included	Ivory White	<b>ISM2EI*</b> <b>ISM2W*</b>
---	----------------	---------------------------------

Note: \*cULus Listed 1863 - Communication Circuit Accessory.  
See pages P-13 to P-17 for modular jacks and A/V connectors.





Designed to complement decorator styling, these jacks offer voice and Cat. 5e devices to fit within a decorator wallplate. Create a look to match your voice/data, switch, and receptacle devices.

- High impact-resistant thermoplastic frame
- Meets FCC part 68
- UL Listed 1863 - Communication Circuit Accessory
- CSA Certified

### MOLDED-IN VOICE/LOW-SPEED DATA



**NS770I**

Description	Color	Catalog Number
Decorator frame; one RJ11 jack; 6-position; 4-conductor; screw terminations	Almond	<b>NS770AL</b>
	Black	<b>NS770BK</b>
	Brown	<b>NS770</b>
	Gray	<b>NS770GY</b>
	Ivory	<b>NS770I</b>
	Light Almond	<b>NS770LA</b>
	White	<b>NS770W</b>



**NS771I**

Decorator frame; one RJ11 jack; 6-position; 6-conductor; screw terminations	Almond	<b>NS771AL</b>
	Brown	<b>NS771</b>
	Ivory	<b>NS771I</b>
	Light Almond	<b>NS771LA</b>
	White	<b>NS771W</b>



**NS772I**

Decorator frame; duplex RJ11 jacks; 6-position; 6-conductor; screw terminations	Almond	<b>NS772AL</b>
	Ivory	<b>NS772I</b>
	Light Almond	<b>NS772LA</b>
	White	<b>NS772W</b>



**NS784I**

Decorator frame; one cat. 5e 110 punch-down; one RJ11 jack; 6-position; 4-conductor; screw terminations	Almond	<b>NS784AL</b>
	Black	<b>NS784BK</b>
	Brown	<b>NS784</b>
	Gray	<b>NS784GY</b>
	Ivory	<b>NS784I</b>
	Light Almond	<b>NS784LA</b>
	White	<b>NS784W</b>



Coaxial video and combination jacks complement multimedia needs in a 1-gang decorator opening.

- High impact-resistant thermoplastic frame
- Jacks meet FCC part 68
- UL Listed 1863 - Communication Circuit Accessory
- CSA Certified

### MOLDED-IN VOICE/LOW-SPEED DATA



**NS780I**

Description	Color	Catalog Number
Decorator frame; single F-type coupler bulkhead female to female	Almond	<b>NS780AL</b>
	Ivory	<b>NS780I</b>
	Light Almond	<b>NS780LA</b>
	White	<b>NS780W</b>



**NS782I**

Decorator frame; duplex F-type coupler bulkhead female to female	Almond	<b>NS782AL</b>
	Ivory	<b>NS782I</b>
	Light Almond	<b>NS782LA</b>
	White	<b>NS782W</b>



**NS783I**

Decorator frame; one RJ11 jack; 6-position; 4-conductor; one F-type coupler bulkhead female to female	Almond	<b>NS783AL</b>
	Ivory	<b>NS783I</b>
	Light Almond	<b>NS783LA</b>
	White	<b>NS783W</b>



**NS785I**

Decorator frame; one cat. 5e 110 punch-down; one F-type coupler bulkhead female to female	Almond	<b>NS785AL</b>
	Black	<b>NS785BK</b>
	Brown	<b>NS785</b>
	Gray	<b>NS785GY</b>
	Ivory	<b>NS785I</b>
	Light Almond	<b>NS785LA</b>
White	<b>NS785W</b>	



Designed for voice, these devices provide an economical alternative to wall phone outlet placement.

- High impact-resistant thermoplastic plate
- Convenient screw down terminals
- Meets FCC part 68
- UL Listed 1863 - Communication Circuit Accessory
- CSA Certified

## MOLDED-IN PLATES



**NS730I**



**NS732I**



**NS742I**



**NS744I**

Description	Color	Catalog Number	
		Standard	Mid-Size
1-Gang plate; one RJ11 jack; 6-position; 4-conductor; screw terminations	Almond	<b>NS730AL</b>	<b>NS735AL</b>
	Brown	<b>NS730</b>	<b>NS735</b>
	Ivory	<b>NS730I</b>	<b>NS735I</b>
	Light Almond	<b>NS730LA</b>	<b>NS735LA</b>
	White	<b>NS730W</b>	<b>NS735W</b>
1-Gang plate; one RJ11 jack; 6-position; 6-conductor; screw terminations	Almond	<b>NS732AL</b>	—
	Brown	<b>NS732</b>	—
	Ivory	<b>NS732I</b>	—
	Light Almond	<b>NS732LA</b>	—
	White	<b>NS732W</b>	—
1-Gang plate; duplex RJ11 jacks; 6-position; 4-conductor; screw terminations	Almond	<b>NS742AL</b>	—
	Ivory	<b>NS742I</b>	<b>NS745I</b>
	Light Almond	<b>NS742LA</b>	—
	White	<b>NS742W</b>	<b>NS745W</b>
1-Gang plate; duplex RJ11 jacks; 6-position; 6-conductor; screw terminations	Almond	<b>NS744AL</b>	—
	Ivory	<b>NS744I</b>	—
	Light Almond	—	—
	White	<b>NS744W</b>	—



Designed for voice CATV/satellite and data applications, these devices offer an economical alternative to snap fit style products.

- High impact-resistant thermoplastic frame
- Combination jack and coaxial minimize ganging requirements
- Meets FCC part 68
- UL Listed 1863 - Communication Circuit Accessory
- CSA Certified

## MOLDED-IN PLATES



**NS7471**

Description	Color	Catalog Number	
		Standard	Mid-Size
1-Gang plate; F-type coupler bulkhead female to female; one RJ11 jack; 6-position; 4-conductor	Almond	<b>NS747AL</b>	—
	Ivory	<b>NS747I</b>	—
	Light Almond	<b>NS747LA</b>	—
	White	<b>NS747W</b>	—



**NS748I**

1-Gang plate; F-type coupler bulkhead female to female; one RJ11 jack; 6-position; 6-conductor	Almond	<b>NS748AL</b>	<b>NS755AL</b>
	Ivory	<b>NS748I</b>	<b>NS755I</b>
	Light Almond	<b>NS748LA</b>	<b>NS755LA</b>
	White	<b>NS748W</b>	<b>NS755W</b>



**NS750I**

1-Gang plate; single F-type coupler bulkhead female to female	Almond	<b>NS750AL</b>	<b>NS751AL</b>
	Ivory	<b>NS750I</b>	<b>NS751I</b>
	Light Almond	<b>NS750LA</b>	<b>NS751LA</b>
	White	<b>NS750W</b>	<b>NS751W</b>



**NS752I**

1-Gang plate; duplex F-type coupler bulkhead female to female	Almond	<b>NS752AL</b>	—
	Ivory	<b>NS752I</b>	—
	Light Almond	<b>NS752LA</b>	—
	White	<b>NS752W</b>	—



**NS790I**






1-Gang plate; one cat. 5e 110 punch-down; one RJ11 jack; 6-position; 4-conductor; one F-type coupler bulkhead female to female	Almond	<b>NS790AL</b>	—
	Black	<b>NS790BK</b>	—
	Brown	<b>NS790</b>	—
	Gray	<b>NS790GY</b>	—
	Ivory	<b>NS790I</b>	—
	Light Almond	<b>NS790LA</b>	—
	White	<b>NS790W</b>	—



Designed for voice applications, these jacks provide an economical alternative to basic wall mount and performance needs.

- Available in high impact-resistant thermoplastic or stainless steel
- Meets FCC part 68
- UL Listed 1863 - Communication Circuit Accessory
- CSA Certified

## TELEPHONE WALL JACKS

	Description	Color	Catalog Number
 <p><b>NS721I</b></p>	Wall phone jack quick connect; 6-position; 4-conductor; punch-down termination tool included	Almond	<b>NS721AL</b>
		Ivory	<b>NS721I</b>
		Light Almond	—
		White	<b>NS721W</b>
 <p><b>NS722I</b></p>	Wall phone jack; 6-position; 4-conductor; screw terminations	Almond	<b>NS722AL</b>
		Ivory	<b>NS722I</b>
		Light Almond	—
		White	<b>NS722W</b>
 <p><b>NS725I</b></p>	Wall phone jack; 6-position; 6-conductor; screw terminations	Almond	<b>NS725AL</b>
		Ivory	<b>NS725I</b>
		Light Almond	<b>NS725LA</b>
		White	<b>NS725W</b>
 <p><b>NS723SS</b></p>	Wall phone jack quick connect; 6-position; 4-conductor; punch-down termination tool included	Stainless Steel	<b>NS723SS</b>
 <p><b>NS726SS</b></p>	Wall phone jack; 6-position; 4-conductor; screw terminations	Stainless Steel	<b>NS726SS</b>





- Meets TIA/EIA-606-A labeling administration standards
- Labor savings; installer can produce and print labels before installation
- Saving job files reduces potential for error and eliminates the time to re-enter information when changes and additions are required
- Makes closets and workstations look professional with clearly marked connections and leaves an impression of quality workmanship
- In ever-changing work environments, clearly marked connections will make moves, adds, and changes easier by eliminating mistakes and wasted time

## LABELING SOLUTIONS SOFTWARE

Description	Catalog Number
Software package for custom labeling; consult factory for download instructions	XPSOFT

## PATCH PANEL AND RACK LABELS Inches (mm)

Delivery: Package of 10; 8.5" x 11" (215.9 x 279.4) paper sheets

Description	Labels per sheet	Label Sheets Catalog Number	Extra Label Holders Catalog Number
Adhesive 8-port front label strips	20	XPLPPA10W	—
Paper 8-port front label strips (use with label holders supplied with panel)	18	XPLPP10W	XPHPP50
Paper ID labels for all panel sizes (use with vertical ID label holders on panels)	18	XPLPPID10W	XPHPPID1U10 (for 1U)
		—	XPHPPID2U10 (for 2U)
Rack and cabinet labels (use with XPHRC10)		XPLRC10W	XPHRC10

## MULTIMEDIA PANEL LABELS Inches (mm)

Delivery: Package of 10; 8.5" x 11" (215.9 x 279.4) paper sheets

Description	Labels per sheet	Label Sheets Catalog Number	Extra Label Holders Catalog Number
Paper 8-port front label strips (use with label holders supplied with panel)	18	XPLUDX2410W	XPHUDX2410

Note: Use XPLFOSEPAW labels for the UDX36 multimedia panel.



TX4P



TX4PP



TPD110



TBLH



TK3



TK8

## 1-PUNCH JACK TERMINATION TOOL

This tool should be used exclusively with netSELECT® jacks; used with the HXTA termination aid

Description	Catalog Number
1-Punch XJ tool with head; blades and HXTA termination aid	<b>TX4P</b>
1-Punch XJ replacement head (includes blades)	<b>TX4PH</b>
1-Punch XJ replacement blades	<b>TX4PHBL</b>
Hand Termination Aid "Jack Knuckles"	<b>HXTA</b>
Snap-X Termination Puck (Bag of 25)	<b>HXTP25</b>

## 1-PUNCH PANEL TERMINATION TOOL

Description	For use with	Catalog Number
1-Punch panel tool with head and blades	P6EXXU panel	<b>TX4PP</b>
1-Punch panel replacement head	P6EXXU panel	<b>TX4PPH</b>
1-Punch panel replacement blades	P6EXXU panel	<b>TX4PPBL</b>

## 110 PUNCH-DOWN TOOL

Comfortable, ergonomic grip with insulated, rubber-embedded handle; terminated 28-22AWG solid/stranded wire; high visibility colors; lanyard holes in the handle end; latching blade storage cover; adjustable high- and low-impact settings; twist and lock blades

Description	Catalog Number
Standard 110 punch-down tool	<b>TPD110</b>
1-pair NSJ; 110 blade	<b>TBLH</b>
Punch-down tool; 1-pair	<b>TPDH</b>
Replacement 110 blade	<b>TBL110</b>
Replacement 66 Blade	<b>TBL66</b>

## TOOL KITS

- Punch-down tool with 110 and 66 blades; rubber-embedded handle
- Durable; black; nylon belt pouch
- Belt pouch fits up to 2½" belt (slide on style)

## 3-PIECE TOOL KIT

Description	Catalog Number
Delivery: 1 punch-down tool with 110 and 66 blades; 1 pair of snips; and 1 belt pouch	<b>TK3</b>

## 8-PIECE TOOL KIT

Description	Catalog Number
Delivery: 1 punch-down tool with 110 and 66 blades; 1 pair of snips; 4-bit screwdriver; UTP/STP cable stripper/cutter; Maglite™; 1 belt pouch; and 1 Snap-X termination aid	<b>TK8</b>

Maglite™ is a trademark of Mag Instruments, Inc.



UCT



ECT



COMPTRG659



TCS3



NS4

## CRIMP TOOLS

- Universal frame accepts interchangeable dies to crimp different plugs
- Color-coded die-sets for different plug sizes
- Complete ratchet cycle release assures no-fault crimps

Description	Catalog Number
Crimp tool frame (die-sets sold separately).	UCT
Complete tool kit in hard, plastic case includes crimp tool; UTP cable stripper; 3 die-sets (RJ45, RJ22 and RJ11)	UCTKIT
RG6 compression connector (optional die-set not included in tool kit)	FRG6C25
RG59 compression connector (optional die-set not included in tool kit)	FRG5925
RJ11 die-set	CDTSR11
RJ22 die-set	CDTSR22
RJ45 die-set; non-snagless	CDTSR45
RJ45 die-set; snagless	CDTSR45S
RG6 and RG59 hex crimp die-set	CDTSRG659
Economy crimp tool – includes non-replaceable RJ11, RJ22 and RJ45 die-sets	ECT

## RG6 OR RG59 COMPRESSION TOOL

Use to terminate onto 75 ohm RG6 or RG59 coaxial cable.

Description	Catalog Number
RG6 and RG59 compression tool	COMPTRG659
Coaxial stripping tool	CSTRPR

Note: See page P-14 for compression connectors.

## COMMUNICATIONS CABLE STRIPPER/CUTTER Inches (mm)

- Strips round Cat. 5e and 6 UTP/STP
- Cuts cable
- Strips flat cables
- Compact size
- High-visibility for quick locating

Description	Catalog Number
Communications cable stripper/cutter; strips round Cat. 5e and Cat. 6 UTP/STP with diameters of 0.145" to 0.275" (3.7 to 7.0) ; cuts round UTP/STP cables up to 0.350" (8.9); adjusting screw for varied cable diameters to avoid scoring interior conductor insulation; high-visibility for quick locating; strips flat cables; non-metallic body	TCS3

## HAND HELD 110 TERMINATION TOOL

Description	Catalog Number
Designed as an economical alternative for low volume use where the installer press fits the conductors	NS4



### HORIZONTAL UTP CABLE AND PATCH CORDS


- Solid copper 4-pair 24 AWG UTP is specified for distribution cabling; stranded UTP is specified for patch cords for flexibility; shielded cable is not commonly used in the U.S.; splices bridge taps are not permitted
- Cable, connectors and patch cords shall be marked with the performance category; always match performance categories of cables and components throughout the infrastructure
- All cable, cords and connecting hardware shall meet performance requirements of ANSI/TIA/EIA-568-B.1 and 568-B.2; Bryant assures this compliance with all products and cable partners

#### COLOR CODING:

	white-blue/blue
	white-orange/orange
	white-green/green
	white-brown/brown


### RECOGNIZED CONNECTOR AND WIRING CONFIGURATIONS

- 8-position modular jack/plug
- 8-position modular panel/plug
- T568A wiring or T568B wiring options
- Cat. 5e or Cat. 6 recommended



### RJ 45 - TIA/EIA-568 CONVENTIONS

Two wiring standards were adopted; both configurations provide equivalent transmission performance



- Preferred method
- Directly compatible with 2-pair voice and Token Ring systems utilizing 6-position connectors



- Optional method
- AT&T's standard
- Directly compatible with AT&T phone systems

### LAN WIRING CONVENTIONS


Local Area Network standards designed to operate over UTP specify pin/pair assignments on modular connectors for various signal transmission protocols. While TIA/EIA-568A and 568B conventions support all of these designations, there are some cases where the user chooses to cable only the number of pairs required to support these applications.



- 10 Mbps Ethernet over UTP
- 100 Mbps Ethernet



- 4/16 Mbps Token Ring over copper



- 100 Mbps FDDI over copper (pending)



- 1000 Mbps/10Gb Ethernet over UTP
- Uses all four pairs