

Product Data Sheet



132X122 CH

Replace "X" with 1, 2 or 3 for number of poles

Power Stud Block

200 Amps, 600 Volts (AC/DC)

1,000V AC/DC CE (IEC 60947-7-1)



Wire Range:

Line side: 1/4 - 20 X 9/16 Stud

Load Side: 1/4 - 20 X 9/16 Stud

Insulator base adders and 1 pole product can be snapped together through integral dovetails to create variable pole power blocks.

This product is intended for use with Listed Crimp-type Lugs.

7.5 x 35 mm din rail or panel mountable

Electrical Ratings:

- 200A copper wire
- CE Rated Voltage (U_i): 1,000 V AC/DC per IEC 60947-7-1
- Material Group: IIIa
- Pollution Degree: 3
- UL/CSA Voltage Rating: 600 Volts AC/DC (UL 1059 Class C, User Group - General Industrial)
- Factory and Field Wiring

Mechanical Ratings:

- Maximum insulator base temperature: 125°C (257°F) UL RTI
- Flammability rating of insulator base: UL 94 V-0

* Use outside these ratings needs to be judged in the end-use application.

Materials:

- Bus bar: Copper, tin plated
- Insulator base: Glass filled polycarbonate (thermoplastic)
- Connector mounting screw: Brass, Tin plated
- Hinged cover: Glass filled polycarbonate (thermoplastic)
- Threaded Studs: Steel, zinc plated
- Nuts: Steel, Zinc plated (packed loose)
- Washers (flat and split): Steel, Zinc plated (packed loose)

Agency Approvals:

- UL Recognized, UL 1059 Terminal Block Standard, File No. XCFR2.E62806
- CSA Certified, CSA C22.2 No. 158, File No. LR19766
- CE compliant to IEC 60947-7-1
- RoHS Compliant

Wire Approvals:**Line and Load Torque:**


1/4 - 20 Stud: 61 in. lbs



- Panel mountable: #10 fastener, torque to 25-30 in. lb.

Accessories:

- End bracket for din rail mounting :MSK35
- Marker Strips. Printing available. Consult factory.
- Din Rail (35 x 7.5 mm, 2 m long, slotted): MN35-2



WWW.MARATHONSP.COM
1-419-352-8441