

HBL2425 -- Twist-Lock Flanged Inlet



3P4W, 20A 3PH 250V, L15-20R, White Nylon

Product Specifications

| | |
|--------------------------------------|---|
| Product Type | <p>Twist-Lock Devices</p> |
| Product Item | Flanged Inlet |
| Wiring Scheme | 3-Pole, 4-Wire Grounding |
| Amperage | 20A |
| Voltage | 3 Phase 250V AC |
| NEMA Configuration | L15-20P |
| Item Style | Standard |
| Device Color | White |
| Terminal Retainer Material | Clear polycarbonate |
| Blade Material | Brass |
| Terminal Clamp Material | .08" (2) steel-nickel plated |
| Terminal Screw Material | #10-32 Brass (white finish on neutral screw when used) Multi-drive |
| Ground Screw Material | #10-32 Brass (green finish) Multi-drive |
| Body Holding Screw Material | Steel, zinc plated Multi-drive |
| Body Contact Carrier Material | Natural White Nylon |
| Flanged Casing Material | Natural White Nylon |
| Mounting Screw Material | Nickel-plated Brass Round head screws |
| Ratings | Molded In or Stamped On |
| Catalog No | Permanently ink marked on product |
| Dielectric Voltage Withstand | 2,000V minimum |
| Current Interrupting | Certified for current interrupting at full rated current |
| Temperature Rise | Max 30C temperature rise at full rated current after 50 cycles of overload at 150% of rated current at a power factor of .75. |
| Terminal Accommodation | 20A #12 AWG |
| Terminal Identification | Terminals identified in accordance with UL 498 (X, Y, Z, White, Green) |
| Flammability | HB or better per UL 94 or CSA 22.2 No. 0.6 |
| Operating Temperatures | Maximum Continuous 75 C Minimum -40 C (w/o impact) |
| Listings | FED SPEC UL/CSA |
| UPC Number | 783585038247 |
| Weight in LBs | 0.25 |
| Link to Drawing Library | Click here for Library |
| Link to PDF Catalog | Click here for Catalog |



NEMA Configuration

