

HBL7526C -- Twist-Lock Flanged Receptacle



2P2W, 15A 125V, L1-15R, White Nylon

HBL7526C


Product Specifications

Product Type



Twist-Lock
Devices

| | |
|--------------------------------------|---|
| Product Item | Flanged Receptacle |
| Wiring Scheme | 2-Pole, 2-Wire Non-Grounding |
| Amperage | 15A |
| Voltage | 125V AC |
| NEMA Configuration | L1-15R |
| Item Style | Standard |
| Device Color | White |
| Terminal Retainer Material | Clear polycarbonate |
| Terminal Clamp Material | .062" cold rolled steel-nickel-plated |
| Terminal Screw Material | #8-32 Brass (white finish on neutral screw when used) |
| Body Contact Carrier Material | Natural White Nylon |
| Contact Spring Material | Brass |
| Spring Binding Plate Material | Brass |
| Flanged Casing Material | Natural White Nylon |
| Mounting Screw Material | Nickel-plated Brass Round head screws |
| Ground Contact Material | .032" Bronze |
| Ratings | Molded In or Stamped On |
| Catalog No | Permanently ink marked on product |
| Dielectric Voltage Withstand | 2,000V minimum |
| Current Interrupting | Certified for current interrupting at full rated current |
| Temperature Rise | Max 30C temperature rise at full rated current after 50 cycles of overload at 150% of rated current at a power factor of .75. |
| Terminal Accommodation | 15A #14 AWG |
| Terminal Identification | Terminals identified in accordance with UL 498 (X, Y, Z, White, Green) |
| Flammability | UL 94 VO for Receptacles and Inlets. HB or better for Plugs and Connectors. |
| Operating Temperatures | Maximum Continuous 75 C Minimum -40 C (w/o impact) |
| Listings | UL |
| UPC Number | 783585178059 |
| Weight in LBs | 0.15 |
| Link to Drawing Library | Click here for Library |
| Link to PDF Catalog | Click here for Catalog |



NEMA Configuration

