



NOTES:

1. FOR USE WITH BOEING BMS13-65 OH & ADAMS RUSSELL FC28Z CABLES.
2. FOR CABLING INSTRUCTIONS SEE 3-546-2.
3. FOR CRIMPING USE DIE KTH-2212.
4. INTERFACE PER MIL-STD-348, FIG. 313-1.
5. CENTER CONTACT (1-5990-1MA9) SUPPLIED UNASSEMBLED.
6. MARK PACKAGE: KINGS 125-91-9 YRWK (DATE CODE)
7. MATERIALS:
 INSULATOR: TEFLON, ASTM-D-1710
 K-GRIP SLEEVE: COM. BRONZE TUBE, ASTM B135
 OUTER CONTACT: BER. COPPER, ASTM-B-196
 GASKET: SILICONE RUBBER, A-A-59588
 C-RING: PHOSPHOR BRONZE, ASTM B103
 ALL OTHER METAL PARTS: BRASS, ASTM B16
8. FINISHES:
 CENTER CONTACT: .000050 MIN GOLD PER ASTM B488 OVER .000050 MIN NICKEL PER AMS-QQ-N-290(RoHS)
 ALL OTHER METAL PARTS: .000050 MIN NICKEL PLATE PER AMS-QQ-N-290 OVER .000050 MIN COPPER PER ASTM B734(RoHS)
9. ELECTRICAL CHARACTERISTICS:
 NOMINAL IMPEDANCE: 50 OHMS
 WORKING VOLTAGE: 500 VRMS
 FREQUENCY RANGE: DC TO 11 GHz
 VSWR: 1.30 MAX. .5-11 GHz
 INSERTION LOSS: DC TO 2.5 GHz, 0.045 dB MAX
 2.5 TO 5.0 GHz, 0.11 dB MAX
10. WEIGHT: 26.8 GRAMS (0.059 POUNDS)

UNLESS OTHERWISE SPECIFIED

1. ALL DIMENSIONS IN INCHES [MILLIMETERS].
 2. TOLERANCES:
 .XXX ±.004 .XX ±.010
 [.XXX ±.10] [.XX ±.25]
 FRACTIONS: X/Y ±.010 [.25] ANGLES: ± 1'
- ★ CRITICAL DIMENSIONS

125-91-9

REVISIONS	
ISSUE	CHANGES
0	ER 33826 JCA 04/06/92
1	CN 33985 E MJB 06/11/92
2	CN 38538 C JPK 04/09/02
3	CN 38540 E TML 04/15/02
4	CN 38716 E BDH 11/11/02
5	CN 39272 E TML 06/14/05
6	CN 39517 E HVN 07/07/06
7	ER 8354 RMS 05/27/08
J	ER 33571 COL 06/28/11

SALES DRAWING

THIS DRAWING, THE DESIGN AND DATA EMPLOYED IN THE DESIGN, TO WHATEVER END, AND THE METHOD OF MANUFACTURE, SHALL BE THE PROPERTY OF WINCHESTER ELECTRONICS CORPORATION AND SHALL NOT BE EMPLOYED, COPIED, OR DISCLOSED TO ANYONE IN ANY MANNER WITHOUT THE CONSENT OF WINCHESTER ELECTRONICS CORPORATION.

SCALE 4:1
 APPROX SURFACE AREA
 W.A.S.: E-1735B
 USED ON
 CAGE CODE:91836

PLUG, TNC

DRAWN	JCA	DATE	04/06/92
DESIGN	JT	DATE	04/07/92
APPR.		DATE	

WINCHESTER
 Winchester Electronics
 82 Borras Industrial
 Road North
 Winsted, CT 06492

SIZE **B**

125-91-9