

Fuseholders

For Micro™ Fuse or Pico® II Fuses

“Push-On” Retaining Nut Chassis Mount Type


QPL

Fuseholder will accept Littelfuse MICRO™ fuses and PICO® II fuses (rated to 5 amperes) with .025" diameter leads.


SPECIFICATIONS:

- Electrical:** Rated at 5 amperes for any voltage up to 125 volts.
- Mounting:** Maximum panel thickness is .09".
- Molded Parts:** Black Thermoset.
- Terminals:** Beryllium Copper, Silver-plated.
- Ambient Temperature:** -40°C to +125°C.
- Hardware:** “Push-On” retaining nut.

* Please refer to Fuseology section for information on proper fuseholder de-rating.



MOUNTING HOLE



FOR MICRO™ FUSE OR PICO® II FUSES

Vertical/Horizontal

P.C. Board Mount Type



Fuseholder will accept Littelfuse MICRO™ fuses and PICO® II fuses (rated to 5 amperes) with .025" diameter leads.

SPECIFICATIONS:

- Electrical:** Rated at 5 amperes for any voltage up to 125 volts.
- Molded Parts:** White Thermoplastic.
- Terminals:** Copper Alloy.
- Ambient Temperature:** -40°C to +100°C.

ORDERING INFORMATION:


| Catalog Number | Terminal Plating | Mounting |
|----------------|---------------------|------------|
| 281 005 | Silver ¹ | Vertical |
| 281 008 | Tin | Vertical |
| 281 007 | Silver ¹ | Horizontal |
| 281 010 | Tin | Horizontal |

¹UL Recognized.



* Please refer to Fuseology section for information on proper fuseholder de-rating.




281 000 Series Vertical




Circuit Board Mounting Detail



281 000 Series Horizontal



Circuit Board Mounting Detail (Component Side)



For LT-5™ and TR5® Fuses

P.C. Board Mount Type

See 560 Series holder for new designs and replacement.

SPECIFICATIONS:

- Electrical:** Rated at 5 amperes for any voltage up to 250 volts.
- Molded Parts:** Black Thermoplastic (UL94 V-O).
- Terminals:** Tin-plated brass/gold inside.

ORDERING INFORMATION:

Catalog Number: 021 000

* Please refer to Fuseology section for information on proper fuseholder de-rating.

OBSOLETE

