


REVISIONS	
ISSUE	CHANGES
7	CN 18684 C ATT 30 OCT 79

KA-91-10



NOTES:

1. MATERIALS: TEFLON MIL-P-1946B, BRASS QQ-B-620, BERYLLIUM COPPER QQ-C-530, COPPER WIRE QQ-W-330, SILKONE RUBBER ZZ-R-705 COLOR RED.
2. PLATING: SILVER PLATE QQ-S-365 .0002 MIN.
3. ELECTRICAL CHARACTERISTICS:  
 NOMINAL IMPEDANCE: 50 Ω.  
 WORKING VOLTAGE: 500 VOLTS RMS.  
 FREQUENCY RANGE DC TO 4GHz.  
 INSULATION RESISTANCE: 5000 MEGOHMS. MIN.  
 DIELECTRIC WITHSTANDING VOLTAGE: 1500 VOLTS RMS.

SCALE: 4:1

USED ON:	
REF:	
FINISH	
SPEC. / CER 10004	
MATL.	
SPEC.	
TNC (F) / BNC (M) ADAPTER	
DRAWN / SM	DATE / 15 NOV 77
APPR. / [Signature]	DATE / 15 NOV 77
KINGS ELECTRONICS 40 MARBLEDALE ROAD TUCKAHOE, N. Y. 10707	
KA-91-10	

UNLESS OTHERWISE SPECIFIED:

1. TOLERANCES: FRACTIONS & 2 PLACE DECIMALS ± .010  
3 PLACE DECIMALS ± .004 ANGLES ± 0° 30'
2. REMOVE ALL BURRS, BREAK SHARP EDGES .005 MAX.
3. NO FILLETS PERMITTED.
4. SURFACE ROUGHNESS 63 MICROINCHES RMS MAX.
5. ALL DIMENSIONS PRIOR TO PLATING.

U.S.

S-D