


# SD



**NOTES:**

1. FOR USE WITH RG-55A, 142, 142A, & 223/U CABLE.
2. FOR CRIMPING USE DIE KTH-2001.
3. FOR CABLING INSTRUCTIONS SEE CP-403.
4. MARK PACKAGE: KINGS KD-59-63  
YRWK (DATE CODE)
5. MATERIALS:  
INSULATOR: TEFLON, ASTM-D-1457  
GASKET: SIL. RUB., ZZ-R-765  
K-GRIP SLEEVE: COM. BRONZE TUBE, ALLOY 220  
OUTER CONTACT BER. COP., QQ-C-530  
SPRING WASHER BER. COP., QQ-C-533  
ALL OTHER METAL PARTS: BRASS, QQ-B-626
6. FINISHES:  
CENTER CONTACT: HARD GOLD PLT. PER MIL-G-45204  
ALL OTHER METAL PARTS: SILVER PLATE , QQ-S-365
7. ELECTRICAL CHARACTERISTICS:  
NOMINAL IMPEDANCE: 50 OHMS  
VOLTAGE RATING: 1000 VRMS  
FREQUENCY RANGE: DC TO 11 GHz

STAMP: KINGS KD-59-63  
YRWK (DATE CODE)

KD-59-63

**REVISIONS**

ISSUE	CHANGES
1	CN 115142 A JL 02/06/76
1	CN 19900 A MA 12/06/79
3	CN 37575 C REDRAWN MK 02/11/99
4	CN 38134 E HVN 12/06/00
5	CN 40052 C PMC 08/28/07

SCALE 4:1

APPROX SURFACE AREA

USED ON

REF:

**C-PLUG**

DRAWN	HFE	DATE	12/27/66
DESIGN	PETE	DATE	12/27/66
APPR.		DATE	

A Winchester Electronics Company

**KD-59-63**

# SD