



# Lineman Buckets & Accessories

Klein lineman buckets and accessories have been trusted and recognized for decades for their durability and dependability and are built for strength and to handle professional wear and tear.

For Professionals... Since 1857®



## Features:

**Rope handle** reinforced with leather for water resistance and strength.

**Durable, straight-wall and tapered-wall** buckets are made of heavy-duty canvas.

The No. canvas refers to the canvas weight. No. 1 being the thickest and No. 8 being the thinnest.

**High-density polyethylene top ring** for strength and chemical resistance.



## Leather-Bottom Buckets

*Additional Features:*

- No. 1 canvas.
- Leather reinforced bottom.
- Leather cuff extends 3" (76 mm) up the side.
- Inside pocket measures 8" x 8" (203 mm x 203 mm).
- Rope handle.



5104

Cat. No.	Top Diameter	Bottom Diameter	Height	Extra Features	Weight (lbs.)
5104	12" (305 mm)	12" (305 mm)	17" (432 mm)		2.71
5104S	12" (305 mm)	12" (305 mm)	17" (432 mm)	swivel snap (Cat. No. 2012)	2.93

## Straight-Wall Buckets

*Additional Features:*

- No. 6 canvas.
- Black molded polypropylene bottom.
- Rope handle.



5106

Cat. No.	Diameter	Height	Extra Features	Weight (lbs.)
5106	9" (229 mm)	14" (356 mm)		1.51
5106P	9" (229 mm)	14" (356 mm)	two 7" x 7" (178 mm x 178 mm) inside pockets	1.62
5106S	9" (229 mm)	14" (356 mm)	swivel snap (Cat. No. 2012)	1.80

## Wide-Opening Straight-Wall Buckets

*Additional Features:*

- No. 6 canvas.
- Black molded polypropylene bottom.
- Rope handle.

Cat. No.	Diameter	Height	Extra Features	Weight (lbs.)
5109	12" (305 mm)	15" (381 mm)		2.06
5109P	12" (305 mm)	15" (381 mm)	one 8" x 8" (203 mm x 203 mm) inside pocket	2.12
5109S	12" (305 mm)	15" (381 mm)	swivel snap (Cat. No. 2012)	2.35
5109PS	12" (305 mm)	15" (381 mm)	one 8" x 8" (203 mm x 203 mm) inside pocket and swivel snap (Cat. No. 2012)	2.40



5109

All dimensions are in inches and (millimeters).



## Canvas Buckets

### Tapered-Wall Buckets

Additional Features:

- No. 6 canvas.
- Black molded polypropylene bottom.
- Rope handle.



5113

Cat. No.	Top Diameter	Bottom Diameter	Height	Extra Features	Weight (lbs.)
5113	12" (305 mm)	9" (229 mm)	13" (330 mm)		1.55
5113S	12" (305 mm)	9" (229 mm)	13" (330 mm)	swivel snap (Cat. No. 2012)	1.84

### Heavy-Duty Tapered-Wall Bucket

Additional Features:

- Tough No. 4 canvas.
- Black molded polypropylene bottom.
- Rope handle.
- Riveted leather glove strap.
- Equipped with Cat. No. 2012 swivel snap hook.



5103S

Cat. No.	Top Diameter	Bottom Diameter	Height	Extra Features	Weight (lbs.)
5103S	12" (305 mm)	9" (229 mm)	12" (305 mm)	swivel snap (Cat. No. 2012)	1.95

### Heavy-Duty Tapered-Wall Buckets with Pockets

Additional Features:

- Tough No. 4 canvas.
- Black molded polypropylene bottom.
- Rope handle.
- Riveted leather glove strap.
- Equipped with Cat. No. 2012 swivel snap hook.

Cat. No.	Top Diameter	Bottom Diameter	Height	Outside Pockets	Extra Features	Weight (lbs.)
5171PS	12" (305 mm)	9" (229 mm)	12" (305 mm)	4 outside pockets	swivel snap (Cat. No. 2012)	2.20
5172PS	12" (305 mm)	9" (229 mm)	12" (305 mm)	15 inside pockets	swivel snap (Cat. No. 2012)	2.35



5171PS

5172PS

### Oval Bucket with 41 Pockets

Additional Features:

- No. 6 canvas.
- Black molded polypropylene bottom.
- Sisal-Rope handle.
- Equipped with Cat. No. 2012 swivel snap hook.
- Tripod suspension rope for greater stability.
- 26 pockets inside and 15 pockets outside.

Cat. No.	Length	Width	Height	Pockets	Extra Features	Weight (lbs.)
5152S	14" (356 mm)	7" (177 mm)	10" (254 mm)	26 inside pockets 15 outside pockets	swivel snap (Cat. No. 2012)	2.46



5152S

### Oval Bucket with 15 Interior Pockets

Additional Features:

- No. 6 canvas.
- Black molded polypropylene bottom.
- Sisal-Rope handle.
- Equipped with Cat. No. 2012 swivel snap hook.
- Tripod suspension for greater stability.

Cat. No.	Length	Width	Height	Pockets	Extra Features	Weight (lbs.)
5144S	14" (356 mm)	7" (177 mm)	10" (254 mm)	15 inside pockets	swivel snap (Cat. No. 2012)	2.17



5144S

All dimensions are in inches and (millimeters).



# Canvas Buckets

## Aerial-Basket Oval Bucket with 15 Interior Pockets

Additional Features:

- No. 6 canvas.
- Black molded polypropylene bottom.
- Two nylon 66 polymer hooks (Cat. No. 5144H) supplied with Cat. No. 5144.

Cat. No.	Length	Width	Height	Pockets	Extra Features	Weight (lbs.)
5144	14" (356 mm)	7" (177 mm)	10" (254 mm)	15 inside pockets	two hooks (Cat. No. 5144H)	2.01
5144B	14" (356 mm)	7" (177 mm)	10" (254 mm)	15 inside pockets		1.5



5144

## Hard Body Oval Buckets

- Fabric constructed of rugged denier polyester to resist wear and tear on the jobsite (Cat. No. 5144BHB14OS).
- Black molded polypropylene bottom with drain holes.
- Cat. No. 5144H hooks sold separately.



5144BHB



5144BHB14OS



5144BHHB

Cat. No.	Pockets	Handle	Color	Length	Height	Width	Weight (lbs)
5144BHB	15	No	orange	14" (356 mm)	10" (254 mm)	7" (178 mm)	2
5144BHHB	15	Yes	orange	14" (356 mm)	10" (254 mm)	7" (178 mm)	2
5144BHB14OS	29	Yes	black	14" (356 mm)	10" (254 mm)	7" (178 mm)	3

## Hard Body Oval Bucket with Knife Sheath

- Includes leather skinning knife sheath & 14 other interior pockets.
- Orange, non-conductive plastic exterior maintains bucket shape.
- Fabric constructed of rugged denier polyester to resist wear and tear on the jobsite.
- Black molded polypropylene bottom with drain holes.
- Cat. No. 5144H hooks sold separately.



5144HBS

Cat. No.	Interior Pockets	Handle	Color	Length	Height	Width	Weight (lbs)
5144HBS	15	Yes	orange	14" (356 mm)	10" (254 mm)	7" (178 mm)	2

All dimensions are in inches and (millimeters).





# Canvas Buckets

## Line-Hose Bag

- No. 6 canvas with Cicolac top ring and molded bottom.
- Large enough to accommodate several pieces of hose.
- Can also be used to raise protective rubber blankets that are rolled.
- Leather cuff extends 3" (76 mm) up the side.
- Polypropylene rope handle is reinforced with leather.



5110-48

Cat. No.	Diameter	Depth	Weight (lbs.)
5110-48	7" (178 mm)	48" (1219 mm)	1.91

## Canvas Electrode Bag

- Made of tough No. 4 canvas.
- Heat-resistant, hard leather bottom.
- Web loop for sliding over belt.



5471

Cat. No.	Diameter	Front Depth	Back Depth	Weight (lbs.)
5471	2-1/2" (64 mm)	12" (305 mm)	15-1/2" (394 mm)	.25



## Canvas Tapered-Bottom Bag

- No. 10 canvas.
- Two pockets are provided for small parts.
- Bottom is tapered so parts will stay in center.
- Equipped with a snap for hanging.

Cat. No.	Diameter	Depth	Weight (lbs.)
5143	6-1/2" (165 mm)	8" (203 mm)	.30



5143

All dimensions are in inches and (millimeters).



# Canvas Buckets

## Aerial Aprons

- Sewn-in magnet design won't catch on gloves (Cat. No. 51829M).
- Includes: ten hand tool pockets, two pouches, hammer loop and two drill bit holders.
- Two pouches reinforced with heavy duty rivets.
- Cat. No. 5144H hooks sold separately.



Sewn-in Magnet



51829

51829M

Cat. No.	Interior Pockets	Magnet	Color	Length	Height	Width	Weight (lbs)
51829	18	No	orange	24" (609 mm)	23" (584 mm)	-	4
51829M	18	Yes	orange	24" (609 mm)	23" (584 mm)	-	4

## Hooks

### Swivel Snap Hook

Additional Features:

- This is NOT an occupational protective hook. NOT for human support.
- Bronze swivel snap hook made for use on canvas buckets.
- Maximum safe load is 150 lbs. (68 kg).

Cat. No.	Length	Width	Weight (lbs.)
2012	4-3/8" (111 mm)	1-5/8" (41 mm)	.28



2012

### Hook for Aerial-Baskets

- All weather, durable, nylon 66 polymer.
- Most manufacturers' aerial basket trucks accommodate bucket hook.
- Replacement hook for both Cat. No. 5144 and Cat. No. 5169.

Cat. No.	Weight (lbs.)
5144H	.30



5144H

## Slings

### Pole Sling

- For use where a running loop wrap around pole is desired.
- Nylon web stitched with nylon thread.
- Copper rivets with burrs at the point of wear.
- NOT an occupational protective device. NOT for human support.
- Resistant to oil, creosote, and moisture.



5606

Cat. No.	Rated Capacity (Maximum Working Load)		Overall Length	Width	Weight (lbs.)
	Choke Hitch	Basket Hitch			
5606	3000 lbs (1350 kg)	4700 lbs (2115 kg)	39" (991 mm)	2" (51 mm)	1.33

All dimensions are in inches and (millimeters).

**⚠WARNING:** This is NOT an occupational protective device. NOT for human support.

