

Heavy Duty Terminal Blocks

1600 Series - Barrier Type

Specifications:

- 75 amps
- 600 volts AC/DC
- Base, phenolic, 150°C (UL RTI)
- Screws, #10-32 phil-slot, brass, nickel plated
- Connector, brass, nickel plated
- 21/32" (.656") line-to-line spacing
- Bare wire range #10-22 AWG CU
- Accepts lugs w/max width of .50"
- See on-line data sheets for additional information



1604 H



1606 STD

Standards:


- UL recognized file no. XCFR2.E62806
- CSA certified file no. LR19766
- CE compliant (IEC 60947-7-1)
- RoHS compliant

HEAVY DUTY
TERMINAL BLOCKS


# of Poles	Catalog #								Dimensions		Clear Cover	White Cover
									A	B		
2	1602 MCJ	1602 STD	1602 DJ	1602 DJSV	1602 ST	1602 SC	1602 H	2.44	1.78	CC 1602	CW 1602	
4	1604 MCJ	1604 STD	1604 DJ	1604 DJSV	1604 ST	1604 SC	1604 H	3.75	3.09	CC 1604	CW 1604	
6	1606 MCJ	1606 STD	1606 DJ	1606 DJSV	1606 ST	1606 SC	1606 H	5.06	4.41	CC 1606	CW 1606	
8	1608 MCJ	1608 STD	1608 DJ	1608 DJSV	1608 ST	1608 SC	1608 H	6.38	5.72	CC 1608	CW 1608	
12	1612 MCJ	1612 STD	1612 DJ	1612 DJSV	1612 ST	1612 SC	1612 H	9.00	8.34	CC 1612	CW 1612	

See page 116 for DIN Rail Adapter


mm = dim X 25.4




Standard Connector with Serrations for Anti-Rotation




Removable Connector with Brass Insert




Removable Connector with Brass Insert, Removable Cover




10-32 Stud, Removable Connector



Short Circuiting Bar with Brass Insert, 4 Shorting Pins per Block



Standard Connector with Hinge Cover



Multiple Circuit Jumper

