



Type B Overall Size (mm): 84x44 14pin through-hole bottom connection

INDEX



WHIP! Image next to part no. indicates cad file.

 Indicates an [Opto Express](#) part.

- [Product Table](#)
- [Part Number Suffix Table](#)
- [Absolute Maximum Ratings](#)
- [Technical Information](#)
- [Electrical Characteristics](#)
- [Options](#)
- [Order Samples](#)
- [Stock/Price Request](#)
- [Sales and Tech Support](#)
- [Drawings](#)


PRODUCT TREE

1. [Product Gallery](#)
2. [LCD Displays & Modules](#)
3. [Character Modules](#)
4. [16 Characters x 2 Lines](#)
5. [Type B Overall Size \(mm\): 84x44 14pin through-hole bottom connection](#)

Lumex drawings are in PDF format. If you don't have Adobe Acrobat, click on this icon to

[download a free copy](#)



Lumex Part Number	Overall Size with LED Backlight	Overall Size without Backlight	Viewing Area (WxH)	Character Height (WxH)	Dot Size (WxH)	Font	Duty
 LCM-S01602DSF/B WHIP!	84x44x12.7		66x16	2.96x5.56	0.56x0.66	5x8	1/16
LCM-S01602DSR/B WHIP!		84x44x8.8	66x16	2.96x5.56	0.56x0.66	5x8	1/16
LCM-S01602DTF/B WHIP!	84x44x12.7		66x16	2.96x5.56	0.56x0.66	5x8	1/16
LCM-S01602DTR/B WHIP!		84x44x8.8	66x16	2.96x5.56	0.56x0.66	5x8	1/16

Part Number Suffix Table

[\[top of page\]](#)

- DSR = STN, Reflective
- DSF = STN, Transflective (With Backlight)
- DTR = TN, Reflective
- DTF = TN, Transflective (With Backlight)

Absolute Maximum Ratings

[\[top of page\]](#)

Item	Symbol	Test Condition	Standard Value		Unit
			Min	Max	
Supply Voltage for Logic	V_{DD} - V_{SS}	$T_a=25^\circ\text{C}$	4.7	5.3	V
Supply Voltage for LCD Drive	V_{DD} - V_o	-	4.2@50° C	4.8@50° C	V
Input Voltage	V_I	$T_a=25^\circ\text{C}$	V_{SS}	V_{DD}	V
Operating Temperature	T_{opr}	LCM-S	0	50	$^\circ\text{C}$
		LCM-H	-20	70	$^\circ\text{C}$
Storage Temperature	T_{stg}	LCM-S	-20	70	$^\circ\text{C}$
		LCM-H	-30	85	$^\circ\text{C}$

Technical Information

[\[top of page\]](#)

- You can find comprehensive technical information in the [Lumex Tech Notes](#) section. Click [here](#) to get there!

Electrical Characteristics

[\[top of page\]](#)

Item	Symbol	Test Condition	Standard Value			Unit	
			Min.	Typ.	Max.		
Supply Voltage for Logic	V_{DD} - V_{SS}	-	-	5.0	-	V	
Supply Current for Logic	I_{DD}	$V_{DD}=5\text{V}$	-	2.0	3.0	mA	
Input Voltage	High	V_{IH}	-	2.2	-	V_{DD}	
	Low	V_{IL}	-	0	-	0.6	
Output Voltage	High	V_{OH}	-	2.4	-	V	
	Low	V_{OL}	-	-	0.4	V	
*LED Backlight	Voltage	V_f	$I_f=160\text{mA}$	-	4.2	4.6	V
	Current	I_f	-	-	160	-	mA
	Power Consumption	PD	-	-	656	-	mW
	Luminous	L	$I_f=160\text{mA}$	70	-	-	cd/m ²
	Color	-	-	-	-	-	nm
*Only Applies to Modules with Backlight $V_{DD}=4.7\text{V}$ to 5.3V , $T_A=25^\circ\text{C}$							

Options

[\[top of page\]](#)

- High Temperature Module Available

[Home](#) | [What's New](#) | [Product Gallery](#) | [Product Search](#) | [X-Ref Search Engine](#) | [Tech Notes](#) | [Sales and Tech Support](#) | [Corporate Info](#)

290 East Helen Road Palatine, IL 60067 Telephone: (847) 359-2790 Facsimile: (847) 359-8904 E-mail us at sales@lumex.com

© 1997-2001 Lumex, Inc.