




Date	SYM	REVISION RECORD	AUTH	DR.	CK.
10/24/14	С	REDRAWN AND UPDATED TO ROHS 2 COMPLIANT	T.B.	B.S.	
			·		







1. MATERIAL:

HOUSING: HIGH IMPACT NYLON 66, HALOGEN AND

PHOSPHOR FREE, UL94V-0, UL FILE NO. E48285

RIVETS: BRASS, NICKEL PLATED.

SPRING: 302 STAINLESS STEAL, NICKEL PLATED.

TEMPERATURE RANGE: -40°C TO +140°C

WIRES: 24AWG, 80°C, VW-1, TR-64, 300V, UL1007 E41396

RESISTANT TO SOLVENTS, COMMON OILS AND REFRIGERANTS

ROHS 2 COMPLIANT

MOUNTING INSTRUCTION:

USE 2-56 MACHINE SCREWS OR EYELETS 0.089" OD BY 0.15" FLANGE STIMPSON GS-3 SERIES OR EQUIVALENT. ALSO ADHESIVES AND DOUBLE SIDED TAPES WORK WELL.

INITED	CONNECTION	CULLWATIC
IIN I EK	CONNECTION	SCHEIMATIC

Tolerance (Inches)	Memory Protection Devices, Inc 200 Broad Hollow Road, Farmingdale, New York 11735						
Decimal			Scale	Drawn By	B.S.		
±.5 (.020)				Approved By	T.B.		
Fractional	Title 4AA BATTERY HOLDER WITH WIRE LEADS						
± .8 (.030)							
Angular	Date	e Drawing Number					
± 3°	10/24/14	Bł	H4AA-W				