



SPECIFICATIONS:

- * Holder material- Black, Nylon 66, UL File No. E44716, UL94V-0
- * Contacts: 0.020" thick PHOS-BRONZE, GOLD FLASH
- * Temperature range: -40°C to +280°C
- * Vibration Test: 10-50-10 Hz sweeped in 60 seconds

X,Y,Z direction: 1 hour each direction

- * Result: No dislodgement of the cell or damage No discontinuity over 10 micro-seconds
- * Shock Test: Half sine wave acceleration 150G. 6 ms

3 shock pulses each direction per axis, total of 18 pulses

- * Result: No evidence of physical damage
- * ROHS 2 COMPLIANT

Tolerance (Except as noted)	▮ MPD Mem	ory Prote	ction I	Devices, Inc
(Except as noted)		ale, New York 11735		
decimal			Scale	Drawn By B.S.
±.5 (.020)				Approved By T.B.
Fractional	Title			
± .8 (.030)	HIGH GRIP BATTERY HOLDER FOR CR2032 WITH PC PINS			
Angular	Date Drawing Number			
± 3°	4/25/14		BU2032-1-HD-G	