

ELECTRIC HEAT GUN



Voltage: 120V/60Hz
 Amperage: 12A
 Watt: 1440W
 2 fan speeds: Low & High
 2 heat settings: Approx. 850°F on Low, 1120°F on High
 Resetable thermostat protection

84-603-1 Bulk

WIRE GAUGE



Stainless steel Wire Gauge.
 36 AWG to 1 AWG, metric also.

87-110-0 Bulk
87-110-1 Pkg.

ROTARY TOOL KIT



87-211-1 shown
 with Flexible Shaft
 attached

Variable Speed 8000 - 30000 RPM
 CUL Approved
 C/w 42 Accessories Including:
 Flexible Shaft with 1/8" Chuck, 2 Drills, 4 Sanding Belts, 2
 Diamond Bures, 10 Grinding Stones, 6 Cut-off Wheels, 8
 Sanding Wheels, Collets, etc.

87-211-1 Pkg.

PCB MARKER (BLUE)




These markers feature valve-activated, ink-feed mechanisms, interchangeable felt-tips, and a sleek, lightweight plastic body. They write in bright, crisp markings.

Ink resists action of various etchants such as ferric chloride and ammoniated alkali.


87-501-0 Bulk **87-501-1** Pkg.

BREADBOARD STRIPS FOR PROTOTYPE DESIGN



Aluminum Plate 164x52x0.3mm
 Board 165.1x54.6x8.5mm
 ABS plastic with color printed
 1 Terminal strip, 630 tie-point
 2 Distribution strips, 200 tie-point

88-840-1 Pkg.



Aluminum plate 183x95x1.2mm
 Board 165.1x54.6x8.5cm
 ABS plastic with color printed
 1 Terminal strip, 630 tie-point
 2 Distribution strips, 200 tie-point
 3 Binding posts
 5 Cushions

88-841-1 Pkg.



Aluminum plate 215x130x1.2mm
 Board 165.1x109.3x8.5mm
 ABS plastic with color printed
 2 Terminal strips, 1260 tie-point
 4 Distribution strip, 400 tie-point
 3 Binding posts
 5 Cushions

88-842-1 Pkg.



Aluminum plate 230x175x1.2mm
 Board 174.8x165.1x8.5mm
 ABS plastic with color printed
 3 Terminal strips, 1890 tie-point
 5 Distribution strip, 500 tie-point
 4 Binding posts
 5 Cushions

88-843-1 Pkg.


BREADBOARD STRIPS FOR PROTOTYPE DESIGN cont'd



88-844-1 Pkg.

Aluminum plate 240x210x1.2mm Board
184.4x190x8.5mm ABS plastic with color printed
4 Terminal strips, 2520 tie-point
7 Distribution strip, 700 tie-point
4 Binding posts
5 Cushions

BREADBOARD KIT WITH JUMPER WIRES



88-850-1 Pkg.

Board 165.1x54.6x8.5cm. ABS plastic with color printed
1 Terminal strip, 630 tie-point
2 Distribution strips, 200 tie-point
70pc jumper wire kit included

350 PIECE JUMPER WIRE KIT FOR BREADBOARDS



88-852-1 Pkg.

350 PIECES Stripped, Bent, 22 AWG Jumper Wires
Includes 25 each of wires for jumping 1, 2, 3, 4, 5, 6, 7, 8, 9, 10, 20, 30, 40 and 50 nodes.

140 PIECE JUMPER WIRE KIT FOR BREADBOARDS



88-851-1 Pkg.

140 PIECES Stripped, Bent, 22 AWG Jumper Wires
Includes 5 each of wires for jumping 1, 2, 3, 4, 5, 6, 7, 8, 9, 10, 20, 30, 40 and 50 nodes.

TRIGGER TRANSFORMER for 90-152



170 volt input to 4KV output voltage. Suitable for the flash tube shown below.

90-150-0 Bulk **90-150-1** Pkg.


XENON FLASH TUBE



90-152-0 Bulk **90-152-1** Pkg.

Anode to Cathode voltage 300V(200min/400 max)
Maximum energy/flash rate 4WS (watt seconds)
Flash Rate 1/second (Min.)
Nominal Life (flashes) 10 million
Trigger Voltage 4KV
Tube length 32mm
Tube width 16mm
Lead length 40mm
Lead spacing 10mm

CdS PHOTOCELLS



	90-154-0	90-155-0
Peak Response(nm)	550nm	550nm
Min. Resistance(10 lux)	5K	11K
Max. Resistance(10 lux)	10K	20K
Min. Dark Resistance	500K	650K
Peak AC Voltage	100V	100V

	90-156-0	90-157-0
Peak Response(nm)	550nm	550nm
Min. Resistance(10 lux)	16K	30K
Max. Resistance(10 lux)	30K	60K
Min. Dark Resistance	700K	1.5M
Peak AC Voltage	150V	150V

Use -1 for Display Package

MODE ELECTRONICS LTD.
211 - 2999 UNDERHILL AVE.,
BURNABY, B.C., CANADA, V5A 3C2
Phone: 604-435-6633
Fax: 604-435-8890
Toll Free: 1-800-663-4992
Web Site: www.mode-elec.com