

SPECIFICATIONS:

- * UL Flamability Rating: UL 94-HB File No. E108370
- * Contacts: Phosphor Bronze C5191, Nickel Plated 80-150u

thickness

- * Vibration test: 10-50-10 hz sweeped in 60 seconds x,y,z direction: 1 hour each direction
- * Result: no dislodgement of the cell or damage no discontinuity over 10 milliseconds
- * Shock test: half sine wave acceleration 150g. 6 milliseconds 3 shock pulses each direction per axis, total of 18 pulses
- * Result: no evidence of physical damage
- * ROHS 2 COMPLIANT

Tolerance	MPD Memory Protection Devices, Inc 200 Broad Hollow Road, Farmingdale, New York 11735			
(Except as noted)				
decimal			Scale	Drawn By B.S.
±.5 (.020)				Approved By T.B.
Fractional	Title CR2032 PC PINS BATTERY RETAINER			
± .8 (.030)	WITH INSULATOR			
Angular	Date	Drawing Nu	mber	
± 3°	12/11/15 BHX1-2032-PC			

Date

SYM

REVISION RECORD

AUTH DR. CK.