

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0676430011](#)
Status: **Obsolete**
Description: Universal Serial Bus (USB) Shielded I/O Receptacle, Right Angle, Type A, Black Polyester, 0.76µm (30µ") Gold (Au) Plating, PCB Thickness 1.60mm (.063"), without Upper Flange
Replacement Part Number: [67643-0911](#)

Documents:
[Drawing \(PDF\)](#)

General

Product Family	I/O Connectors
Series	67643
Application	Wire-to-Board
Comments	Without Upper Flange Not for IR Reflow Process
Component Type	Receptacle
Product Name	USB
Replacement Part Number	67643-0911
Type	A


Physical

Boot Color	N/A
Circuits (Loaded)	4
Circuits (maximum)	4
Gender	Receptacle
Keying to Mating Part	Yes
Lock to Mating Part	Yes
Material - Plating Mating	Gold
Material - Plating Termination	Tin-Lead
Number of Rows	1
Orientation	Right Angle
PC Tail Length	2.60mm (.102")
PCB Locator	Yes
PCB Retention	Yes
PCB Thickness - Recommended	1.60mm (.063")
Packaging Type	Tray
Panel Mount	Yes
Pitch - Mating Interface	2.00mm (.079"), 2.50mm (.098")
Pitch - Termination Interface	2.00mm (.079"), 2.50mm (.098")
Plating min - Mating	0.762µm (30µ")
Polarized to Mating Part	Yes
Polarized to PCB	Yes
Ports	1
Surface Mount Compatible (SMC)	No
Temperature Range - Operating	0°C to +50°C
Termination Interface: Style	Through Hole
Waterproof / Dustproof	No

Electrical

Current - Maximum per Contact	1.5A
Shield Type	Full Shield
Shielded	Yes
Voltage - Maximum	30V (RMS)

Material Info



EU RoHS	China RoHS
Not RoHS Compliant	
REACH SVHC	
Not Reviewed	
Low-Halogen Status	
Not Reviewed	



Need more information on product environmental compliance?

Email productcompliance@molex.com
 For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series
[67643Series](#)

Mates With
 USB Type A Plug

Reference - Drawing Numbers

Product Specification

PS-67998-0000

This document was generated on 05/18/2011

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION