

Search This Product Catalog

By Keyword

- Architecture & Construction
 - Product Catalog for Architecture & Construction
 - 3M™ Access Network Solutions
 - 3M™ Aerosols, Films, Hot Melt, Liquids, & Pastes Solutions
 - 3M™ Bonding Tapes
 - 3M™ Corrosion Protection Products
 - 3M™ Electrical Products**
 - 3M™ Glass Bubbles
 - 3M™ Heat Tracing Solutions
 - 3M™ Industrial Abrasives
 - 3M™ Industrial Tapes
 - 3M™ Novec™ Fire Protection Fluid
 - 3M™ Occupational Health & Environmental Safety Products
 - 3M™ Packaging Solutions
 - 3M™ Protection Products
 - 3M™ Reclosable Fasteners
 - Volition™ Networks

Product Catalog for Architecture & Construction > 3M™ Electrical Products . . . 3M™ Scotchlok™ Standard Forks > 3M™ Scotchlok™ Standard Forks Vinyl Insulated Butted Seam >

3M™ Scotchlok™ Fork, Vinyl Insulated Butted Seam MVU10-10FX, 500 per case

[Printer-friendly format](#)

This terminal has a wire range of 12-10 AWG and a stud size of 10. Barrel Length is 0.25; Barrel I.D. equals 0.135; Maximum Insulation Diameter is 0.250

3M Id : 80-6101-3734-3
GTIN(UPC/EAN) : 0 00 54007 11327 0

Additional Information

The standard fork allows rapid connection of wire. They are usually used on free-standing studs, because of their wider tongues.

Learn More . . .

- [Standard Forks - Vinyl Insulated Butted Seam - Product Selection Guide \(PDF 44.1 K\)](#)
- [Terminal Stud Size Chart - Product Selection Guide \(PDF 14.9 K\)](#)

Please Note:

Adobe® Acrobat® Reader is required to view PDF documents.



Characteristics

Agency Approvals	UL and CSA
Barrel Inside Diameter	0.135 Inch
Barrel Length	0.25 Inch
Barrel Style	Butted
Clearance ©	0.29 Inch
Conductor Sizes	12 - 10 AWG
CSA File Number	LR22190
Dimension E	0.84 Inch
Insulation Material	Vinyl
Length (L)	1.03 Inch
Maximum Insulation Outer Diameter	0.25 Inch
Stud Size	10
Terminal Style	Standard
Terminal Type	Fork
Thickness	0.04 Inch
UL File Number	E23438
Width (W)	0.28 Inch