

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [0878330820](#)  
**Status:** **Active**  
**Overview:** [Milli-Grid™ Connector System](#)  
**Description:** [Milli-Grid™ Header, Right Angle, Shrouded, Lead-Free, 8 Circuits, 0.38µm Gold \(Au\) Plating, without PCB Locator, without Locking Window, Center Polarization Slot, Tube](#)

**Documents:**

[3D Model](#) [Packaging Specification PK-87831-001-001 \(PDF\)](#)  
[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)  
[Product Specification PS-87831-027-001 \(PDF\)](#)

**Agency Certification**

CSA LR19980  
 UL E29179

**General**

Product Family PCB Headers  
 Series [87833](#)  
 Application Signal, Wire-to-Board  
 Comments Contact Molex for application in automotive industry  
 Overview [Milli-Grid™ Connector System](#)  
 Product Name Milli-Grid™  
 UPC 822348186570

**Physical**

Breakaway No  
 Circuits (Loaded) 8  
 Circuits (maximum) 8  
 Color - Resin Black  
 Durability (mating cycles max) 100  
 First Mate / Last Break No  
 Flammability 94V-0  
 Glow-Wire Compliant No  
 Guide to Mating Part No  
 Keying to Mating Part None  
 Lock to Mating Part None  
 Material - Metal Phosphor Bronze  
 Material - Plating Mating Gold  
 Material - Plating Termination Tin  
 Material - Resin Nylon  
 Net Weight 0.485/g  
 Number of Rows 2  
 Orientation Right Angle  
 PC Tail Length 2.16mm  
 PCB Locator No  
 PCB Retention None  
 PCB Thickness - Recommended 1.60mm  
 Packaging Type Tube  
 Pitch - Mating Interface 2.00mm  
 Pitch - Termination Interface 2.00mm  
 Plating min - Mating 0.381µm  
 Plating min - Termination 1.905µm  
 Polarized to PCB No  
 Shrouded Fully  
 Stackable No  
 Surface Mount Compatible (SMC) Yes  
 Temperature Range - Operating -55°C to +105°C



Series image - Reference only

**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant**

**REACH SVHC**

Not Contained Per -  
 ED/30/2017 (7 July  
 2017)

**Halogen-Free**

**Status**

**Not Low-Halogen**

**Need more information on product  
 environmental compliance?**

Email [productcompliance@molex.com](mailto:productcompliance@molex.com)  
 Please visit the [Contact Us](#) section for any  
 non-product compliance questions.

China ROHS Green Image  
 ELV Not Relevant  
 RoHS Phthalates Not Contained

**Search Parts in this Series**

[87833 Series](#)

**Mates With**

Milli-Grid™ Vertical Through Hole  
 Receptacle [79107](#) , [78787](#) , Milli-Grid™  
 Flex-to-Board Vertical Receptacle [79108](#)  
 , Milli-Grid™ Vertical Surface Mount  
 Receptacle [79109](#) , [78788](#) , Milli-Grid™  
 Crimp Housing [51110](#) , Milli-Grid™ Cable-to-  
 Board Receptacle [87568](#)

Termination Interface: Style Through Hole

**Electrical**

Current - Maximum per Contact 2.0A

Voltage - Maximum 125V

**Solder Process Data**

Duration at Max. Process Temperature (seconds) 011

Lead-freeProcess Capability SMC&WAVE

Max. Cycles at Max. Process Temperature 001

Process Temperature max. C 265

**Material Info**

**Reference - Drawing Numbers**

Packaging Specification PK-87831-001-001

Product Specification PS-87831-027-001

Sales Drawing SD-87833-0001-001

This document was generated on 08/29/2017

**PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION**