

Datasheet for 76650-0039

General Information

Kit Part Number:	76650-0039
Connector Type:	Solderless Terminals
Solution:	Maintenance, Repair and Operation Connectors
Molex Family:	Solderless Terminals
Certificates:	N/A
Country of Origin:	Kit assembled in U.S.A

Specifications

Insulation:	Nylon, PVC
Insulation Type:	Nylon, PVC Insulated
Mounting Style:	Non-Mounted
Orientation:	Assorted Quick Disconnect Terminals
Product/Type:	Assorted Terminals
Stud/Tab Size:	# 6, #10, .250" (6.35mm), 1/4", 3/8" (9.52mm)
Tool Included:	Yes
Wire Gauge (AWG):	12-10, 16-14 , 22-14, 22-18

Product Highlights

Quick disconnects allow for quickly connecting or disconnecting a terminal. The front end of the terminal has a female-type receptacle which allows the terminal to slide onto and off of a male blade. Spades have the open tongue end used for rapid insertion on the mounting screw. The spade is usually used on free standing studs. Closed-end connectors are used in a variety of situations to "pigtail" or tie together 2 or more wires. Butt Splices allow two stripped wires to be inserted into each end and "butt" in the center, with the crimp securing both wires together.

Features and Benefits

- Color-coded insulator allows easy identification of terminal size and wire gauge.
- A wire stop stamped into the crimp barrel prevents insertion of over-stripped wires.
- Terminals funnel entrance is designed for increased crimping rates by speeding wire delivery into the crimp section and eliminating wire strand fold back.
- The spades open tongue end is for rapid insertion on the mounting screw / stud
- The basic ring tongue type is the safest and most reliable because it cannot be disconnected unless the screw is completely removed.

Applications

- MRO (Maintenance Repair and Operations)
- Consumer Applications
- Power Applications
- Motor Applications
- Powertrains
- Transportation
- Construction / Mining
- Energy / Power
- Production Equipment
- Instrumentation

<http://www.molexkits.com>

- Environmental Equipment and Controls
- Blower Motors

Bill of Materials

Molex Part No.	Description	Quantity
19054-0113	Insulated #10 Ring Tongue Terminal, 16-14 AWG	10
19017-0037	Insulated 6.35mm (.250") Female Quick Disconnect Terminal, 16-14 AWG	10
19023-0012	Insulated 6.35mm (.250") Male Quick Disconnect Terminal, 16-14 AWG	10
19054-0035	Insulated #6 Ring Tongue Terminal, 22-18 AWG	10
19054-0039	Insulated #10 Ring Tongue Terminal, 22-18 AWG	10
19054-0081	Insulated #6 Ring Tongue Terminal, 16-14 AWG	10
19070-0123	Insulated #10 Ring Tongue Terminal, 12-10 AWG	10
19119-0004	Insulated #6 Flanged Block Spade Terminal, 22-18 AWG	10
19130-0046	Insulated #10 Block Spade Terminal, 16-14 AWG	10
19154-0004	Insulated Butt Splice Connector, 22-18 AWG	10
19160-0009	Nylon Insulator, Closed-end Connector, 22-12 AWG, Clear	10
19130-0040	Insulated #6 Block Spade Terminal, 16-14 AWG	10
CT-4071-1R	Universal Hand Crimping Tool, 22-10 AWG	1
19130-0044	Insulated #6 Block Spade Terminal, 16-14 AWG	10

Recommended Molex Tool

Molex Part No.	Description
CT-4071-1R (included in kit)	No Additional Information
64001-0100 (not included in kit)	Click for more info