

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0747523501](#)
Status: **Active**
Overview: SFP+ Passive Cable Assembly
Description: SFP+ Passive Cable Assembly, 10Gbps, 26 AWG Cable, Pull-to-Release Plunger Style Latch, 5.0m Length

Documents:

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Packaging Specification PK-74752-3501 \(PDF\)](#)

Agency Certification

UL E72548

General

Product Family Cable Assemblies
 Series [74752](#)
 Assembly Configuration Dual Ended Connectors
 Comments Meets customer requirements for speeds up to 10 Gbps. Passive cables may require host pre-emphasis and equalization to reach at the longer lengths.
 Connector to Connector SFP Plus-to-SFP Plus
 Electrical Model Yes
 Overview [SFP+ Passive Cable Assembly](#)
 Product Name SFP Plus
 UPC 800756661438

Physical

Cable Length 5.0m
 Circuits (Loaded) TWO DIFFERENTIAL PAIR
 Gender Male-Male
 Lock to Mating Part Yes
 Material - Metal Beryllium Copper, Zinc Alloy
 Net Weight 259.000/g
 Packaging Type Bag
 Single Ended No
 Waterproof / Dustproof Yes
 Wire Insulation Diameter N/A
 Wire Size AWG 26
 Wire/Cable Type Twin-ax

Electrical

Impedance 100Ω
 Shield Type Full Shield
 Shielded Yes
 Voltage - Maximum 3.3V

Material Info

Reference - Drawing Numbers

Electrical Model Document EE-74752-1497
 Packaging Specification PK-74752-3501
 S-Parameter Model SP-74752-3501, SP-76931-3090
 Sales Drawing 747520001-000



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per - ED/30/2017 (7 July 2017)

Halogen-Free

Status

Not Low-Halogen

Need more information on product environmental compliance?

Email productcompliance@molex.com
 Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS

ELV

RoHS Phthalates

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[74752](#) Series

Mates With

[74441](#) SFP Plus (SFP+) Host Connector