




HONEYWELL PART NUMBER
11SM244
PRODUCT CODE TWW4400
JG-80518
FAA-PMA 


REV	DOCUMENT	CHANGED BY	CHECK
9	0093246	DJS 03OCT12	CMH



296±.010

.156±.010 DIA

 .088 ^{+0.002}/_{-.001} DIA HOLE



.046 SPHERICAL RADIUS


.092 DIA

.356±.010

.110 DIA

.020 MAX
PRETRAVEL

.33
OPERATING
POSITION

 .088 ^{+0.002}/_{-.001}

.302±.010

.094±.010

.187±.010

.098 ^{+0.002}/_{-.004} DIA

.375

.203±.010

.058 DIA HOLE IN TERMINALS

.781±.010



.250±.010

.090±.010


.342±.010



.260±.010


NOTE -

-  - MOUNTING HOLES WILL ACCEPT PINS OR SCREWS OF .087 MAX DIA ON .375±.002 CENTERS
- 2 - TERMINALS ARE PLATED FOR SOLDERING
- 3 - SWITCH WILL WITHSTAND TEMPERATURE OF 400° F
-  - FOR MANUFACTURING DETAIL SEE ASSEMBLY DRAWING 11SM244 FOR FAA-PMA

RELEASE NO.	SR - 9842
REPLACES	-

CHARACTERISTICS
OPERATING FORCE - - - - 3 - 5 OZ
RELEASE FORCE - - - - 1 OZ MIN
DIFFERENTIAL TRAVEL - - - .004 MAX
OVERTRAVEL - - - - .005 MIN 

ELECTRICAL DATA	
KEMA, CE	5A, 250V ~ T85 1E4 
UL	5A, 250 VAC 0.3A 125 VDC 
AVIATION	FAA - PMA

DESIGN UNITS: INCH
TOLERANCES UNLESS NOTED:
NO PLACE X ±
ONE PLACE .X ±
TWO PLACE .XX ±
THREE PLACE .XXX ±
FOUR PLACE .XXXX ±
ANGLES ±
THIRD ANGLE PROJECTION 

DRAWN	VK	27 NOV 07
CHECK	RJ	27 NOV 07
THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE PERMISSION OF HONEYWELL.		
INTERPRET PER ANSI Y14.5M-1982 OTHER HONEYWELL ENGINEERING STANDARDS MAY APPLY		
RASTER		

Honeywell			
TITLE SWITCH - BASIC			
SIZE	TYPE	DRAWING NAME	REV
B	I	11SM244	9
SCALE	NONE	WEIGHT .006 LB MAX	SHEET 1 OF 1