

Honeywell Sensing and Control

Search


[narrow your search](#)

Products

- Controls Monitoring and Lighting (354)
- Machine Safety (1684)
- Sensors (7016)
- Switches (9694)

Technology

- Electromechanical (9195)
- Magnetic (511)
- Microstructure (2298)
- Optical/Infrared (1077)
- Thick Film (1764)
- More...

Need Help?

[Click here to contact us](#)

3100U 00031431 Thermostats

[\(Home : Products\)](#)


3100 Series Hermetic Thermostats

Actual product appearance may vary.

[Sales & Service](#)
[Distributor Inventory](#)
[Overview](#) [Specs](#) [Documentation](#) [Application Notes](#)

Product Specifications

Functional Properties	Open on rise
Reset Type	Automatic
Amperage	3 A resistive max.
Voltage	120 Vac
Operating Temperature	-29 °C to 260 °C [-20 °F to 500 °F]
Environmental Exposure Range	-62 °C to 288 °C [-80 °F to 550 °F]
Open Temperature	4.4 °C [40 °F]
Close Temperature	-6.7 °C [20 °F]
Open Tolerance	2.8 °C [5 °F]
Close Tolerance	2.8 °C [5 °F]
Dielectric Strength	MIL-STD-202, Method 301; 1250 Vac 60 Hz - Terminal to Case
Insulation Resistance	MIL-STD-202, Method 302; 50 MOhm
Contact Resistance	MIL-STD-202, Method 307; 0.050 Ohm max.
Hermetic Seal	MIL-STD-202, Method 112; Cond. 1x10 ⁻⁵
Moisture Resistance	MIL-STD-202, Method 106
Housing Material	Steel housing hermetically sealed with glass-to-metal seal at terminal junction
Contact Material	Silver
Agency Approvals and Standards	UL
Mounting	B209 fixed bracket
Series Name	3100U