

Honeywell



SD3410-001

SD Series Silicon PhotoDarlington, TO-46 Metal, Flat Window Can Package

Representative photograph, actual product appearance may vary.

Due to regional agency approval requirements, some products may not be available in your area. Please contact your regional Honeywell office regarding your product of choice.

Features

- TO-46 metal can package
- Choice of flat window or lensed package
- 90 ° or 12 ° (nominal) acceptance angle option
- Wide operating temperature range [-55 °C to 125 °C]
- Wide sensitivity ranges
- Mechanically and spectrally matched to SE3450/5450, SE3455/5455 and SE3470/5470 infrared emitting diodes

Description

The SD3410/5410 series consists of an NPN silicon photodarlington mounted in a TO-46 metal can package. The SD3410 has flat window cans providing a wide acceptance angle, while the SD5410 has glass lensed cans providing a narrow acceptance angle. The TO-46 packages are ideally suited for operation in hostile environments.

Honeywell

SD3410-001


SD Series Silicon PhotoDarlington, TO-46 Metal, Flat Window Can Package

Product Specifications	
Product Type	IR Component
Angular Response (Degree)	90
Light Current Minimum	0.6 mA
Package Style	TO-46, Flat Window
Package Components	Metal
Rise and Fall Time	75 μs
Power Dissipation	150 mW
Operating Temperature Range	-55 °C to 125 °C [-67 °F to 257 °F]
Dark Current	250 nA
Collector-Emitter Breakdown Voltage	15 V
Emitter-Collector Breakdown Voltage	5 V
Collector-Emitter Saturation Voltage	1.1 V
Comment	The radiation source is a tungsten lamp operating at a color temperature of 2870°K.
Availability	Global
Product Name	Photodarlington

Honeywell

SD3410-001


SD Series Silicon PhotoDarlington, TO-46 Metal, Flat Window Can Package



Honeywell

SD3410-001

SD Series Silicon PhotoDarlington, TO-46 Metal, Flat Window Can Package



Honeywell

SD3410-001

SD Series Silicon PhotoDarlington, TO-46 Metal, Flat Window Can Package

 WARNING

PERSONAL INJURY

DO NOT USE these products as safety or emergency stop devices, or in any other application where failure of the product could result in personal injury.

Failure to comply with these instructions could result in death or serious injury.

 WARNING

MISUSE OF DOCUMENTATION

- The information presented in this product sheet (or catalog) is for reference only. DO NOT USE this document as product installation information.
- Complete installation, operation and maintenance information is provided in the instructions supplied with each product.

Failure to comply with these instructions could result in death or serious injury.

© Copyright Honeywell Inc.1998-2004 All rights reserved.