

Order Product and Get Support

- U.S. Authorized Distributors
- Global Sales & Service
- N. American Sales Reps
- Distributor Inventory
- Technical Assistance
- White Papers
- Literature Request
- RoHS Product List
- Customer Feedback

135-102DAF-J10



Actual product appearance may vary.

Glass encapsulated chip DO -35 type

Features

- Cost effective
- Rugged DO35 glass encapsulation
- High temperature capability
- Available on tape and reel

Potential Applications

- Consumer electronics
- PCB temperature sensing
- Communications
- Fire detection
- Computers
- Low-cost applications with a maximum temperature of 300 °C [615 °F]
- Automotive

Description

135 Series Thermistors are high-quality, hermetically-sealed, glass-encapsulated units in an axial lead package. They cover the full temperature range of -60 °C to 300 °C [-76 °F to 572 °F]. The uniform dimensions are often suited for automated assembly. The tinned copper-clad, steel leads are both solderable and weldable. These rugged sensors are designed for many applications which demand reliability at low cost. Available on tape and reel for automated assembly.

Supporting Documentation

None Available

Product Specifications	
Availability	Global
Nominal Resistance at 25 °C [77 °F]	1,000 Ohm
Tolerance	± 5.0%
Accuracy	25 °C [77 °F]
R- T Curve	10A
Operating Temperature Range	-60 °C to 300 °C [-76 °F to 572 °F]
Maximum Diameter	2,0 mm [0.080 in]
Termination Material	Tinned copper - clad steel
Lead length	28,6 mm [1.125 in]
Time Constant in Air	4.0 s
Dissipation Constant	2,5 m/W°C
Series Name	135

My Links

- [Login to iCOM](#)
- [Login as Rep/AD](#)
- [Login as Guest](#)
- [Login to Digital University](#)

Keyword Search

Search for product and support information.

All Sensing and Control

Product Search

Part number search:

Use (*) to expand search

[Specification Search](#)