




Home > Products > MICRO SWITCH™ Toggle Switches > TW > Product Page

Order Product and Get Support

- U.S. Authorized Distributors
- Global Sales & Service
- N. American Sales Reps
- Distributor Inventory
- Technical Assistance
- White Papers
- Literature Request
- Test and Measurement Catalog
- RoHS Product List
- Customer Feedback

2TW101-3



Actual product appearance may vary.

TW Series Toggle Switch, 2 pole, 2 position, Solder terminal, Standard Lever

Features

Save space and weight
 SPDT and DPDT circuitry
 Temperature range: -85° F to +160° F (-65° C to +71° C)
 Sealed bushing versions
 Choice of 1/4 in. or 15/32 in. bushing
 Color tab available on 15/32 in. bushing
 UL recognized

Potential Applications

Industrial machinery and equipment
 Military and commercial aviation
 Construction equipment
 Test instruments
 Agricultural machinery
 Process control
 Medical instrumentation

Description

MICRO SWITCH™ miniature toggle switches in two bushing sizes. Molded in terminals are plated for soldering. Momentary and maintained circuitry closures available. Special on-on-on circuitries are also available. Pull-to-unlock levers prevent accidental operation.

Supporting Documentation

- [Terminal Identification](#)
- [Panel Cutout](#)
- [Accessory: Nuts](#)
- [Engineering Drawing](#)

Product Specifications	
Circuitry/Operating action	<div style="display: flex; justify-content: space-around;"> <div style="text-align: center;"> <p>Keyway Position</p> </div> <div style="text-align: center;"> <p>Opposite Keyway Position</p> </div> </div>
Product Type	MICRO SWITCH™ Toggle Switch
Ampere/Voltage Range (Resistive Load)	0.1 A to 5.0 A at 0.5 Vac to 115 Vac, 0.1 A to 5.0 A at 0.5 Vdc to 28 Vdc
Circuitry	DPDT
Action	2 position
Mounting	Bushing 1/4 in
Termination	Solder
Lever Type	Standard
Comment	Fine silver contacts
Availability	Global
UNSPSC Code	30211908
UNSPSC Commodity	30211908 Toggle switches
Series Name	TW

My Links

[Login to iCOM](#)
[Login as Rep/AD](#)
[Login as Guest](#)
[Login to Digital University](#)

Keyword Search

Search for product and support information.

All Sensing and Control

Product Search

Part number search:

Use (*) to expand search

[Specification Search](#)