

# 85134

[Products](#) > [Controls and Monitors](#) > [Operator Controls](#) > [Hour Meters](#) > [dc Hour Meters](#) > [85000 Series](#) > **85134**

## Overview

**Honeywell Quartz Plus dc Hour Meter, round opening, three screw flange mounting with deluxe black bezel, 0.25 bent blade termination, 100K hours, 12 Vdc to 60 Vdc operating**  
[View More](#)



## Technical Specifications

Product Type	<b>Quartz + Hour Meter</b>	Function	<b>Hour Meter</b>
Appearance	<b>Round</b>	Mounting	<b>3 Screw</b>
Voltage	<b>12 Vdc to 60 Vdc</b>	Bezel	<b>Black</b>
Hours	<b>100K</b>	Run Indicator	<b>Yes</b>
Logo Top	<b>Honeywell Quartz</b>	Logo Bottom	<b>Hours</b>

[View More](#)

English ▾

## Documents

TITLE	DOCUMENT TYPE	LANGUAGE	SIZE
<b>85134_highres_photo</b>	Photo	English	3MB
<b>85134_lowres_photo</b>	Photo	English	253KB
<b>True Time Stamp - Hour Meters</b>	Case Study	English	345KB
<b>Hour Meters Line Guide</b>	Product Line Guide	English	571KB

[View More](#)

## Product Features

- Custom CMOS integrated circuit
- Indicates operating time in hours and tenths, plus has a running indicator
- Totally sealed
- Battery system voltages: 6, 12, 24, 36, 48 60, 72, and 80 Vdc
- UL, CSA

## Applications

- Lawn tractors
- Garden tractors
- Farm equipment
- Gen sets
- Construction equipment
- Utility vehicles
- Industrial equipment
- Recreational vehicles
- Golf carts
- Aircraft
- Medical equipment

- [view distributor inventory](#)
- [sample request](#)
- [email technical support](#)
- [start a chat we're online](#)
- [get support](#)
- [email sales](#)
- [find a distributor](#)
- [email this page](#)

- Office equipment


#### NAVIGATION LINKS

- [HOME](#)
- [PRODUCTS](#)
- [INDUSTRIES](#)
- [CONTACT US](#)
- [NEWS & EVENTS](#)
- [ABOUT US](#)

#### DISTRIBUTOR LINKS

- [DIGITAL U-HML](#)
- [ECOM LOGIN](#)
- [REQUEST ACCESS TO ECOM](#)
- [SALES/AD PORTAL LOGIN](#)
- [SALES/AD PORTAL ACCESS REQUEST](#)
- [SAMPLE REQUEST](#)
- [LEARNING HUB LOGIN](#)

#### LANGUAGE

English 

#### SITE INFORMATION

- [PRIVACY STATEMENT](#)
- [TERMS & CONDITIONS](#)
- [COPYRIGHT © 2017 HONEYWELL INTERNATIONAL INC.](#)

This site uses cookies to simplify and improve your usage and experience of this website. Cookies are small text files stored on the device you are using to access this website. If you ignore this message and continue without changing your browser settings, we will assume that you are consenting to our use of cookies. For further information on our use of cookies, please see [Privacy Statement](#).

[Don't show this message again](#)