

- PRODUCTS ▾
- DISTRIBUTOR INVENTORY
- INDUSTRIES ▾
- SUPPORT ▾
- NEWS & EVENTS ▾
- ABOUT US ▾

# 2CPSC1A1

[Products](#) > [Switches](#) > [Safety Switches](#) > [Cable-Pull Switches](#) > [2CPS Series](#) > **2CPSC1A1**

## Overview

MICRO SWITCH 2CPS Series Cable Pull Safety Switch, Cable, Maintained Both Sides, 2NC/2NO Direct Opening (Switch 2, Left: 1NC/1NO; Switch 2, Right: 1NC/1NO), 20 mm, Gold  
[View More](#)



## Technical Specifications

Product Type	Cable Pull Safety Switch	Actuator	Cable, Maintained Both Sides
Switch Type	2NC/2NO Direct Opening (Switch 1, Left: 1NC/1NO; Switch 2, Right: 1NC/1NO)	Contact Material	Gold-plated
Cable Length	N/A	Termination Type	20 mm
Ampere Rating	10 uA to 50 mA Low Energy	Voltage	250 Vac and 60 Vdc max.
Housing Material	Zinc Die-Cast	Series Name	2CPS

[View More](#)

View documents in:

## Documents

TITLE	DOCUMENT TYPE	LANGUAGE	SIZE
<b>CPS Series Cable Pull Safety Switch Datasheet</b>	Datasheet	English	2MB
<b>PK 80155: 2 CPS Series Cable Pull Safety Switch</b>	Installation Instructions and Approvals Documentation	English	1MB
<b>PK 80169: 2CPS Series Cable Pull Switch Without Broken Cable Detection</b>	Installation Instructions and Approvals Documentation	English	538KB
<b>PK 80170: CPS-BRACKET Mounting Bracket, Issue 3 (Multiple Languages)</b>	Installation Instructions and Approvals Documentation	English	519KB

[View More](#)

## Product Features

- Positive opening operation of normally closed contacts
- Choice of 2NC/2NO or 3NC/1NO contact configurations

- [view all 2CPSC1A1 literature](#)
- [view distributor inventory](#)
- [sample request](#)
- [email support](#)
- [get support](#)
- [email sales](#)
- [find a distributor](#)
- [email this page](#)

- Maximum cable length in a single direction is 76 m (250 ft) for a combined length of 152 m (500 ft) in dual directions
- Choice of three actuator configurations
- Removable contact block version available
- Large wiring cavity with straight-through wiring
- 24 Vdc or 120 Vac bright, multi-cluster LED status indicator light available
- Gold-plated contacts are standard
- Die-cast zinc housing
- Optional hardware packs available
- UL, CE, CSA, SIL 3 capable

## Applications

---

- Long conveyor systems found in warehouses and distribution centers
- Conveyor systems having a high amount of vibration
- Conveyor systems that experience wide temperature swings
- Long conveyor systems where easy through wiring, or highly visible trip status is required
- Perimeter guarding where hosedown conditions are present

### NAVIGATION LINKS

[HOME PAGE](#)

[PRODUCTS](#)

[DISTRIBUTOR INVENTORY](#)

[INDUSTRIES](#)

[SUPPORT](#)

[NEWS & EVENTS](#)

[ABOUT US](#)

### DISTRIBUTOR LINKS

[ECOM LOGIN](#)

[LEARN CENTER](#)

[REQUEST ACCESS TO ECOM](#)

[SALES/AD PORTAL LOGIN](#)

[SALES/AD PORTAL ACCESS REQUEST](#)

[SAMPLE REQUEST](#)

[SUPPLIER MICROSITE](#)

### LANGUAGE

English 

### SOCIAL MEDIA



### SITE INFORMATION

[PRIVACY STATEMENT](#)

[SITEMAP](#)

[TERMS & CONDITIONS](#)

COPYRIGHT © 2018 HONEYWELL INTERNATIONAL INC.