

Honeywell Sensing and Control

Search



4TP1-7 ( Home : Products : Switches » MICRO SWITCH™ Rocker Switches » Power-duty Rocker Switches » TP )

narrow your search

Products

- Controls Monitoring and Lighting (352)
- Machine Safety (1701)
- Sensors (6224)
- Switches (9749)
- Wireless (39)

Technology

- Control and Instrumentation (1052)
- Electromechanical (9301)
- Magnetic (541)
- Optical/Infrared (1042)
- Thick Film (1764)
- More...

new products

New Wireless Products

Go farther. Work smarter. Explore new possibilities. Just by cutting the cord and making the switch.



Wireless Web Site WGLA and WPMM XYR6000™


find out more

white papers

- Wireless Switches Offer Unlimited Benefit
- Basic Switches Are Not Created Equal
- Applying Precision Switches
- Sensors for Medical Devices
- New Ways to Measure Torque
- Choosing Safety Switches
- Specifying Hour Meters

Need help?

Click here to contact us



Actual product appearance may vary.

TP Series Rocker Switch, 4 pole, 3 position, Screw terminal, Flush Panel Mounting

Sales & Service

Distributor Inventory

Overview Specs Documentation Application Notes

Product Specifications

Product Type	MICRO SWITCH™ Rocker																					
Contact Type	Silver Cadmium Oxide Contacts																					
Circuitry	4PDT																					
Action	3 position																					
Circuitry/Operating action	<table border="0" style="margin-left: auto; margin-right: auto;"> <tr> <td style="text-align: center;"><b>Keyway</b></td> <td style="text-align: center;"><b>Center</b></td> <td style="text-align: center;"><b>Opposite</b></td> </tr> <tr> <td style="text-align: center;"><b>Momentary</b></td> <td style="text-align: center;"><b>Momentary</b></td> <td style="text-align: center;"><b>Momentary</b></td> </tr> <tr> <td style="text-align: center;"><b>Position</b></td> <td style="text-align: center;"><b>Position</b></td> <td style="text-align: center;"><b>Position</b></td> </tr> <tr> <td style="text-align: center;">             3 2 1         </td> <td style="text-align: center;">             3 2 1         </td> <td style="text-align: center;">             3 2 1         </td> </tr> <tr> <td style="text-align: center;">             6 5 4         </td> <td style="text-align: center;">             6 5 4         </td> <td style="text-align: center;">             6 5 4         </td> </tr> <tr> <td style="text-align: center;">             9 8 7         </td> <td style="text-align: center;">             9 8 7         </td> <td style="text-align: center;">             9 8 7         </td> </tr> <tr> <td style="text-align: center;">             12 11 10  <b>ON</b> </td> <td style="text-align: center;">             12 11 10  <b>OFF</b> </td> <td style="text-align: center;">             12 11 10  <b>ON</b> </td> </tr> </table>	<b>Keyway</b>	<b>Center</b>	<b>Opposite</b>	<b>Momentary</b>	<b>Momentary</b>	<b>Momentary</b>	<b>Position</b>	<b>Position</b>	<b>Position</b>	 3 2 1	 3 2 1	 3 2 1	 6 5 4	 6 5 4	 6 5 4	 9 8 7	 9 8 7	 9 8 7	 12 11 10 <b>ON</b>	 12 11 10 <b>OFF</b>	 12 11 10 <b>ON</b>
<b>Keyway</b>	<b>Center</b>	<b>Opposite</b>																				
<b>Momentary</b>	<b>Momentary</b>	<b>Momentary</b>																				
<b>Position</b>	<b>Position</b>	<b>Position</b>																				
 3 2 1	 3 2 1	 3 2 1																				
 6 5 4	 6 5 4	 6 5 4																				
 9 8 7	 9 8 7	 9 8 7																				
 12 11 10 <b>ON</b>	 12 11 10 <b>OFF</b>	 12 11 10 <b>ON</b>																				
Mounting	Flush Panel																					
Lamp Type	Translucent																					
Termination	Screw																					
Ampere/Voltage Range (Resistive Load)	0.75 A at 115 Vdc, 0.5 A at 250 Vdc, 0.5 A to 18 A at 0.5 Vdc to 28 Vdc, 0.5 A to 10 A at 0.5 Vac to 277 Vac																					
LED/Lamp/Neon Voltage	L192: 10 A-125, 250, 277 Vac; 1/4 Hp-125 Vac; 1/2 Hp-250, 277 Vac; 3 A-125 Vac "L"																					
Comment	Silver cadmium oxide contacts																					
Availability	Global																					
UNSPSC Code	302119																					
UNSPSC Commodity	302119 Switches and controls and relays																					
Series Name	TP																					

contacts

- Customer Service
- Technical Support
- Global Sales & Service
- View Site Demo
- Site Comments?

meet dr. larry

VIDEO - Dr. Larry Goldstein explains our newest and best technologies.



Meet Dr. Larry

my links

- Login to iCOM
- Login to Rep/AD Portal
- Login to Digital University

News Center

HONEYWELL ANNOUNCES ADDITION TO RELIALIGN™ RESIDENTIAL DOOR INTERLOCK SWITCHES THAT FEATURE RUGGED, PLASTIC HOUSING

HONEYWELL RELEASES UNLIMITED POTENTIAL WITH NEW LIMITLESS™ WIRELESS SWITCHES

HONEYWELL'S XYR6000 WIRELESS POSITION SENSOR ENABLES MONITORING IN HAZARDOUS AREAS AND REMOTE LOCATIONS

MICRO SWITCH Anniversary site