




Home > Products > PCB level Position Sensors (Miniature Plastic package) > SS400 > Product Page

Order Product and Get Support

- U.S. Authorized Distributors
- Global Sales & Service
- N. American Sales Reps
- Distributor Inventory
- Technical Assistance
- White Papers
- Literature Request
- RoHS Product List
- Customer Feedback

SS443A-SP



Actual product appearance may vary.

SS400 Series Unipolar Hall-Effect Digital Position Sensor; surface mount package; available in 1,000 per tape and reel

Features

Digital current sinking output
 Quad-Hall design virtually eliminates mechanical stress effects
 Temperature compensated magnetics
 Operate/release points can be customized
 High output current capability
 Operate/release points symmetrical around zero gauss (bipolar/latch)
 Package material: Plaskon 3300H
 Surface mount version available:
 SS400-S (with cut and formed leads)

Potential Applications

Speed and RPM sensor
 Brushless DC motor commutation
 Motor and fan control
 Magnetic encoding
 Tachometer, counter pickup
 Disc speed, tape rotation sensing
 Flow -rate sensing

Description

SS400 Series position sensors have a thermally balanced integrated circuit over full temperature range. The negative compensation slope is optimized to match the negative temperature coefficient of lower cost magnets. Bipolar, latching and unipolar magnetics are available.

Band gap regulation provides extremely stable operation over 3.8 Vdc to 30 Vdc supply voltage range.

NOTE: Interruption of power to a latching device may cause the output to change state when power is restored. If a magnetic field of sufficient strength is present, the sensor output will be in the condition dictated by the magnetic field.

Supporting Documentation

[▾ Dimensions](#)

[▾ Operate and Release Point](#)

[▾ Required Accessories—Magnets](#)

[▾ Tape and Reel Dimensions](#)

Product Specifications	
Product Type	Hall-Effect Digital Position Sensor IC
Package Quantity/Type	Available in 1,000/Tape and Reel
Package Style	Surface Mount
Supply Voltage	3.8 Vdc to 30.0 Vdc
Output Type	Sink
Termination Type	Surface Mount
Magnetic Actuation Type	Unipolar
Operating Temperature Range	-40 °C to 150 °C [-40 °F to 302 °F]
Storage Temperature	-65 °C to 160 °C [-85 °F to 320 °F]
Output Voltage	0.4 Vdc max.
Switching Time Rise (10 % to 90 %)	1.5 µs max.
Switching Time Fall (90 % to 10 %)	1.5 µs max.
Availability	Global
Supply Current (max. @ 25 °C)	10 mA
Output Current (max.)	20 mA
Operate Point @ 25 °C	18.0 mT [180 G] max.
Release Point @ 25 °C	7.5 mT [75 G] min.
Leakage Current max.	10 µA
Differential	0.5 mT [5 G] min.
Series Name	SS400

Keyword Search

Search for product and support information.

All Sensing and Control ▾

Product Search

Part number search:

Use (*) to expand search

Specification Search