

## Honeywell Sensing and Control

Search



**SSCMRNN1.6BA7A5**  
 ( Home : Products : Sensors » Silicon Pressure Sensors » Low Pressure Sensors » TruStability® SSC )

[contacts](#)

### narrow your search

#### Products

- Controls Monitoring and Lighting (286)
- Machine Safety (1727)
- Sensors (6158)
- Switches (9781)
- Wireless (45)

#### Technology

- Control and Instrumentation (890)
- Electromechanical (9303)
- Magnetic (538)
- Platinum thin film (56)
- Thick Film (1372)
- More...



TruStability® SSC Series-Standard Accuracy, ±2% total error band, digital I<sup>2</sup>C address: 0x78, SMT, RN: single radial barbed port, absolute, 0 bar to 1.6 bar, 5.0 Vdc, dry gases only, no special options

*Actual product appearance may vary.*

[Sales & Service](#)  
 [Distributor Inventory](#)

- Customer Service
- Technical Support
- Global Sales & Service
- View Site Demo
- Site Comments?

[meet dr. larry](#)

**VIDEO** - Dr. Larry Goldstein explains our newest and best technologies.



Meet Dr. Larry

[my links](#)

- [Login to iCOM](#)
- [Login to Rep/AD Portal](#)
- [Login to Digital University](#)

### new products

#### New Wireless Products

Go farther. Work smarter. Explore new possibilities. Just by cutting the cord and making the switch.



[Wireless Web Site WGLA and WPMM XYR6000™](#)

[find out more](#)

### white papers

- Wireless Switches Offer Unlimited Benefit
- Basic Switches Are Not Created Equal
- Applying Precision Switches Sensors for Medical Devices
- New Ways to Measure Torque
- Choosing Safety Switches
- Specifying Hour Meters

### Need help?

[Click here to contact us](#)

[Overview](#)  
 [Specs](#)  
 [Documentation](#)  
 [Application Notes](#)

#### Product Specifications

Measurement Type	Absolute
Signal Conditioning	Amplified
Pressure Range	0 bar to 1.6 bar
Overpressure	4 bar
Supply Voltage	5.0 Vdc
Supply Current	2 mA typ.
Temperature Compensation	Yes
Output Calibration	Yes
Response Time	1 ms max.
Port Style	RN: single radial barbed port
Package Type	SMT
Accuracy (Best Fit Straight Line)	±0.25%
Shock	MIL-STD-202F, Method 213B, Condition F
Vibration	MIL-STD-202F, Curve AK (20.7 g random)
Operating Temperature	-40 °C to 85 °C [-40 °F to 185 °F]
Compensated Temperature Range	-20 °C to 85 °C [-4 °F to 185 °F]
Storage Temperature	-40 °C to 85 °C [-40 °F to 185 °F]
Media Compatibility	Dry gases only
Comment	No special options
Availability	Global
Series Name	TruStability® SSC

### News Center

HONEYWELL INTRODUCES TRUSTABILITY® NSC SERIES, UNCOMPENSATED / UNAMPLIFIED BOARD MOUNT PRESSURE SENSORS

HONEYWELL EXPANDS ITS LIMITLESS™ PLATFORM WITH THE LAUNCH OF ITS GLOBALLY AVAILABLE INDUSTRIAL WIRELESS RECEIVER

HONEYWELL EXTENDS ITS TRUSTABILITY® PRESSURE SENSOR PRODUCT LINE WITH A SINGLE SIDE LIQUID MEDIA OPTION

**MICRO SWITCH Anniversary site**