


HONEYWELL PART NUMBER
22SM401
PRODUCT CODE TXT0100

REV	DOCUMENT	CHANGED BY	CHECK
5	0038112	KVS 04JUN08	ASD



NOTE-
 ▲-MOUNTING HOLES WILL ACCEPT PINS OR SCREWS OF .087 MAX DIA ON .375±.002 CENTERS
 2-TERMINALS ARE PLATED FOR SOLDERING
 3-DEADBREAK CONDITIONS
 (A) MAX AMOUNT PERMISSIBLE ----- .0002 IN
 (B) LOAD ----- 10 VAC , .035 AMP
 (C) PLUNGER RATE ----- .015 INCHES PER MIN

RELEASE NO. SR - 9701

REPLACES -

CHARACTERISTICS	
OPERATING FORCE	3 1/2 OZ MAX
RELEASE FORCE	1 OZ MIN
DIFFERENTIAL TRAVEL	.001 MAX
OVERTRAVEL	.005 MIN

ELECTRICAL DATA		
CONTACT ARRANGEMENT SPDT		
30 VOLTS DC RATING		
	SEA LEVEL	50,000 FT
INDUCTIVE	3 AMP	2.5 AMP
RESISTIVE	5 AMP	5 AMP
MAXIMUM INRUSH 24 AMP		
APPROVALS	KEMA, CE	5A, 250V ~ T85 1E4
	UL, CSA	5A, 250 VAC

DESIGN UNITS: INCH
TOLERANCES UNLESS NOTED:
NO PLACE X ±
ONE PLACE .X ±
TWO PLACE .XX ±
THREE PLACE .XXX ±
FOUR PLACE .XXXX ±
ANGLES ±
THIRD ANGLE PROJECTION

DRAWN	VK	19 OCT 07
CHECK	RJ	19 OCT 07
THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE PERMISSION OF HONEYWELL.		
INTERPRET PER ANSI Y14.5M-1982 OTHER HONEYWELL ENGINEERING STANDARDS MAY APPLY		
RASTER		

Honeywell			
TITLE SWITCH - BASIC			
SIZE	TYPE	DRAWING NAME	REV
B	I	22SM401	5
SCALE	-	WEIGHT .006 LB MAX	SHEET 1 OF 1