

2HM1-1

PAGE 1 OF 1
 RELEASE NO. SR10355

M

DRAWING NUMBER

14

ISSUE

REPLACES

PSR 04JUL07

CHECK

4, AUG '62

CHECK

4, AUG '62



CHECK

24 JUL 62

DRAWN

L S D

FO-80378



(3) NO. 22 WIRE LEAD PER MIL-W-22759/11 MARKED WITH CIRCUIT IDENT AND WIRE GAGE (C-22, NO-22, NC-22) PER MIL-W-5088

NOTES

- 1 MOUNTING HOLES WILL ACCEPT PINS OR SCREWS OF .087 MAX DIA ON .375 ± .002 CENTERS
- 2 FOR USE IN TEMPERATURE RANGE -85°F TO +250°F (DOWN TO -300°F IF WIRE LEADS ARE NOT FLEXED)
- 3 HERMETICALLY SEALED (METAL-TO-METAL, GLASS-TO-METAL)
- 4 ALL EXPOSED PARTS ARE OF CORROSION RESISTANT MATERIALS
- 5 WEIGHT OF SWITCH ONLY IS 0.22 OZ MAX WEIGHT OF CONDUCTOR GROUP ONLY IS 0.20 OZ MAX PER FOOT
- 6 DO NOT APPLY MORE THAN 1 1/2 INCH-LBS OF TORQUE WHEN TIGHTENING MOUNTING SCREWS

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF MINNEAPOLIS-HONEYWELL REGULATOR CO. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.

CHARACTERISTICS		ELECTRICAL DATA			SCALE 2 : 1
OPERATING FORCE	----- 7 OZ MAX	CONTACT ARRANGEMENT S P D T			DO NOT SCALE PRINT
RELEASE FORCE	----- 1 OZ MIN	LINE VOLTAGE	INDUCTIVE LOAD	RESISTIVE LOAD	UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES TOLERANCES ARE: ONE PLACE (.0) ±.030 TWO PLACE (.00) ±.015 THREE PLACE (.000) ±.005 ANGLES ±
DIFFERENTIAL TRAVEL	----- .006 MAX	28 VDC	3 AMP	5 AMP	
OVERTRAVEL	----- .003 MIN	115 VAC (400 CYCLE)	2 AMP	2 AMP	
					WEIGHT 5