

Honeywell Sensing and Control

Search



narrow your search

Products

- Controls Monitoring and Lighting (286)
- Machine Safety (1727)
- Sensors (6165)
- Switches (9781)
- Wireless (45)

Technology

- Control and Instrumentation (890)
- Electromechanical (9307)
- Magnetic (541)
- Platinum thin film (56)
- Thick Film (1372)
- More...

new products

New Wireless Products

Go farther. Work smarter. Explore new possibilities. Just by cutting the cord and making the switch.



[Wireless Web Site WGLA and WPMM XYR6000™](#)

[find out more](#)

white papers

- Wireless Switches Offer Unlimited Benefit
- Basic Switches Are Not Created Equal
- Applying Precision Switches
- Sensors for Medical Devices
- New Ways to Measure Torque
- Choosing Safety Switches
- Specifying Hour Meters

Need help?

[Click here to contact us](#)

CSNE151-204
(Home : Products : Sensors » Current Sensors » Closed Loop » CSN)



Actual product appearance may vary.

CSN Series closed loop current sensor, measures ac, dc or impulse current, 50 amp-turns nominal, ±90 amp-turns range, miniature housing, 2000 turn

[Sales & Service](#) [Distributor Inventory](#)

[Overview](#) [Specs](#) [Documentation](#) [Application Notes](#)

Product Specifications

Product Type	Closed Loop Linear
Sensed Current Type	ac or dc
Sensed Current Range	±90 A
Package Type	Series Connect PCB Mount
Output Type	Current
Continuous Current	±50 A
Operate Current	50 A RMS @ 25 °C
Supply Current	±12 mA + Output
Supply Voltage	±15.0 Vdc
Offset Current	< ±0.3 mA
Offset Current Drift	< ±0.6 mA
Coil Resistance	190 Ohm
Response Time	< 1 μs
Coil Turns	2000
Output Nominal	25 mA
Operating Temperature	-40 °C to 75 °C [-40 °F to 167 °F]
Storage Temperature	-40 °C to 90 °C [-40 °F to 194 °F]
Measuring Resistance	0 Ohm min., 250 Ohm max.
Housing Material	Glass-filled PBT (UL94-V0)
Mounting	PCB on 9 Pins
Pinout Style	4 Pin
Accuracy	±0.5 %
Availability	Global
Comment	Low cost miniature 50 A sensor.
UNSPSC Code	411121
UNSPSC Commodity	411121 Transducers
Series Name	CSN

contacts

- Customer Service
- Technical Support
- Global Sales & Service
- View Site Demo
- Site Comments?

meet dr. larry

VIDEO - Dr. Larry Goldstein explains our newest and best technologies.



Meet Dr. Larry

my links

- [Login to iCOM](#)
- [Login to Rep/AD Portal](#)
- [Login to Digital University](#)

News Center

Honeywell Introduces TruStability® NSC Series, Uncompensated / Unamplified Board Mount Pressure Sensors

HONEYWELL EXPANDS ITS LIMITLESS™ PLATFORM WITH THE LAUNCH OF ITS GLOBALLY AVAILABLE INDUSTRIAL WIRELESS RECEIVER

HONEYWELL EXTENDS ITS TRUSTABILITY® PRESSURE SENSOR PRODUCT LINE WITH A SINGLE SIDE LIQUID MEDIA OPTION

HONEYWELL ADDS NEW 100° AND 180° ARC CONFIGURATIONS TO ITS SMART POSITION SENSOR PORTFOLIO

HONEYWELL INTRODUCES ITS HAWK™ RESOLVERS 1-INCH SERIES, FULLY HOUSED CONFIGURATION

HONEYWELL INTRODUCES MICROPOWER OMNIPOLAR DIGITAL HALL-EFFECT SENSOR ICS WITH LOW SUPPLY VOLTAGE AND ULTRA LOW TYPICAL CURRENT

[MICRO SWITCH Anniversary site](#)