



HONEYWELL

HOA6972-N51

See full Datasheet below...

onlinecomponents.com

THE ONLINE DISTRIBUTOR OF ELECTRONIC COMPONENTS

BUY NOW



MASTERTM
ELECTRONICS

BUY NOW

masterelectronics.com & onlinecomponents.com
are **authorized** e-commerce distributors
of electronic components.

Honeywell Sensing and Control



Search

narrow your search

Products

- Controls Monitoring and Lighting (352)
- Machine Safety (1702)
- Sensors (6223)
- Switches (9750)
- Wireless (21)

Technology

- Capacitive (26)
- Electromechanical (9301)
- Microstructure (1486)
- NTC Thermistors (147)
- Thick Film (1764)
- More...

new products

New Wireless Products

Go farther. Work smarter. Explore new possibilities. Just by cutting the cord and making the switch.



Wireless Web Site
WGLA and WPMM
XYR6000™

[find out more](#)

white papers

- ▶ Wireless Switches Offer Unlimited Benefit
- ▶ Basic Switches Are Not Created Equal
- ▶ Applying Precision Switches
- ▶ Sensors for Medical Devices
- ▶ New Ways to Measure Torque
- ▶ Choosing Safety Switches
- ▶ Specifying Hour Meters

Need help?

[Click here to contact us](#)

HOA6972-N51 Optoschmitt Sensors (Transmissive) (Home : Products)



Actual product appearance may vary.

HOA096X/HOA097X Series IR Opaque Optoschmitt Sensor, Transistor Output, No Mounting Tab, Plastic Package

[Sales & Service](#)

[Distributor Inventory](#)

[Overview](#) [Specs](#) [Documentation](#) [Application Notes](#)

Product Specifications

Series Name	HOA696X/HOA697X
Product Type	IR Switch
Output	Totem-Pole
Output Logic	Inverter
Mounting Configuration	No Mounting Tab
Package Components	Plastic
Package Color	Black
Continuous Forward Current	50 mA
Forward Voltage	1.6 V
Reverse Breakdown Voltage	3 V
Reverse Current	10 µA
Maximum Trigger Current	15 mA
Housing Material	Polysulfone, Opaque
Power Dissipation	100 mW
Operating Temperature	-40 °C to 70 °C [-40 °F to 158 °F]
Hysteresis (H)	0.05
Operating Supply Voltage	4.5 V to 7.0 V
Supply Voltage	7.0 Vdc
High Level Output Voltage	2.4 V minimum
High Level Supply Current	15 mA
Low Level Output Voltage	0.4 V maximum
Low Level Supply Current	15 mA
Short Circuit Output Current	-20 mA to -100 mA
Output Rise Time	70 ns
Output Fall Time	70 ns
Propagation Delay ⁴⁴ ; Low-High ⁴⁴ ; High-Low	5.0 µs
Duration of Output Short Vcc or Ground	1.0 second
IREDD Trigger Current	15 mA
Comment	Output is HI when incident light intensity is above the turn-on threshold level.
Availability	Global
Sensor Aperture	1,52 mm x 0,25 mm [0.060 in x 0.010 in]
Slot Width	3,18 mm [0.125 in]

contacts

- ▶ Customer Service
- ▶ Technical Support
- ▶ Global Sales & Service
- ▶ View Site Demo
- ▶ Site Comments?

meet dr. larry

VIDEO - Dr. Larry Goldstein explains our newest and best technologies.



- ▶ Meet Dr. Larry

my links

- ▶ Login to iCOM
- ▶ Login as Rep/AD
- ▶ Login as Guest
- ▶ Login to Digital University

News Center

- ▶ HONEYWELL ANNOUNCES ADDITION TO RELIALIGN™ RESIDENTIAL DOOR INTERLOCK SWITCHES THAT FEATURE RUGGED, PLASTIC HOUSING
- ▶ HONEYWELL RELEASES UNLIMITED POTENTIAL WITH NEW LIMITLESS™ WIRELESS SWITCHES
- ▶ HONEYWELL'S XYR6000 WIRELESS POSITION SENSOR ENABLES MONITORING IN HAZARDOUS AREAS AND REMOTE LOCATIONS

MICRO SWITCH Anniversary site