DATA SHEET

NEC/TOKIO

MINIATURE SIGNAL RELAY EB2 SERIES

COMPACT AND LIGHT WEIGHT SURFACE MOUNTING TYPE

DESCRIPTION


The EB2 series is a version of the EA2 series, suitable for surface mounting. This series has three variations of high solder joint reliability type, and low profile type.

FEATURES

- O Compact and lightweight: 7.5 mm × 14.3 mm × 9.3 mm, 1.5 g
- O 2 form c contact arrangement
- O Low power consumption
- O Low magnetic interference
- Edw Integricus Interference
 Breakdown voltage: 1 000 VAC (surge voltage 1 500 V), FCC Part 68 conformable
 UL recognized (E73266), CSA certified (LR 46266)
- O Lineup in non-latch, single-coil latch and double-coil latch types
- O Lineup in minimum footprint (9.3 × 14.3), and high solder joint reliability (20 years) types
- O Lineup in low profile type (hight: 6.5 mm).

APPLICATIONS

Electronic switching systems, PBX, key telephone systems.



ATTENTION

DO NOT EXCEED MAXIMUM RATINGS.

Do not use relays under exceeding conditions such as over ambient temperature, over voltage and over current. Incorrect use could result in abnormal heating, damage to related parts or cause burning. **READ CAUTIONS IN THE SELECTION GUIDE.**

Read the cautions described in NEC/TOKIN's "Miniature Relays" when you choose relays for your application.

The information in this document is subject to change without notice.


Date Published May 2005 P Printed in Japan

© NEC TOKIN Corporation 2002

- •All specifications in this catalog and production status of products are subject to change without notice. Prior to the purchase, please contact NEC Tokin for updated product data.
- •Please request for a specification sheet for detailed product data prior to the purchase.
- •Before using the product in this catalog, please read "Precautions" and other safety precautions listed in the printed version catalog.




PART NUMBER SYSTEM




OUTLINE DRAWINGS AND DIMENSIONS


EB2-..NU EB2-..NUE Unit: mm (inch)




* Relay hight of NUE TYPE - 6.5 mm (0.26) MAX. (Initial)



PAD LAYOUTS (bottom view)




Unit: mm (inch)




Note. General tolerance: ±0.1 (±0.004)

PIN CONFIGURATIONS (bottom view)



(not energized position)



S : Coil polarity of set (operate) R : Coil polarity of reset (release)



- •All specifications in this catalog and production status of products are subject to change without notice. Prior to the purchase, please contact NEC Tokin for updated product data.
- ●Please request for a specification sheet for detailed product data prior to the purchase.
- ●Before using the product in this catalog, please read "Precautions" and other safety precautions listed in the printed version catalog.



MARKINGS (top view)

1 EB2-5NU NEC 3 JAPAN 3 9106 4

UL recognized CSA certified type

- 1 Part number
- ② Manufacturer
- 3 Country of origin
- 4 Date code
- (5) Index mark of relay direction (pin No.1, 10)
- 6 ÜL, CSA Marking

SAFETY STANDARD AND RATING

UL Recognized (UL508)* (CSA Certificated (CSA C22.2 No14)
File No E73266 File No LR46266

30 Vdc, 1 A (Resistive)
110 Vdc, 0.3 A (Resistive)
125 Vac, 0.5 A (Resistive)

* Spacing: UL114, UL478

PERFORMANCE CHARACTERISTICS

Contact Form		2 form c	
Contact rating	Maximum switching power	30 W (resistive)	62.5 VA (resistive)
	Maximum switching voltage	220 Vdc	250 Vac
	Maximum switching current	1 A	
	Maximum carrying current	2 A	
	Minimum carrying ratings	10 mV.dc, 10mA *1	
Initial contact resistance		75 mΩ max. (Initial)	
Contact material		Silver alloy with gold overlay	
Nominal operating Power	Non-latch type and double coil latch type	140 mW (3 to 12 V) 200 mW (24 V)	
	Single coil Latch type	100 mW (3 to 12 V) 150 mW (24 V)	
Minimum operating Power	Non-latch type and double coil latch type	113 mW (24 V)	
	Single coil latch type	56 mW (3 to 12 V) 85 mW (24 V)	
Operate time (excluding both	unce)	Approximately 2 ms without diode	
Release time (excluding bo	unce)	Approximately 1 ms without diode	
Insulation resistance		1000 MΩ at 500 Vdc	
	Between open contacts	1000 Vac (for one minute)	
Breakdown voltage	Between adjacent contacts	1500 V surge (10 × 160 µs *2)	
J	Between coil and contact	1000 Vac (for one minute) 1500 V surge (10 × 160 μ s * ²)	
Shock resistance		735 m / s² (misoperating) 980 m / s² (destructive failure)	
Vibration resistance		10 to 55 Hz at double amplitude of 3 mm (misoperating) 10 to 55 Hz, at double amplitude of 5 mm (destructive failure)	
Ambient temperature		-40°C to 85°C	
Coil temperature rise		18 degrees at nominal coil voltage	
Running specifications	Noload	1 × 10 ⁸ operations (Non-latch type) *3	
	1401000	1 × 10 ⁷ operations (latch type)	
Training specifications	Load	50 Vdc 0.1 A (resistive), 1 × 10 ⁶ operations at 85°C, 2 Hz 10 Vdc 10 mA (resistive), 1 × 10 ⁶ operations at 85°C, 2 Hz	
Weight		Approximately 1.5 grams	
		, , , , , , , , , , , , , , , , , , ,	

- *1 This value is a reference value in the resistance load.
- Minimum capacity changes depending on seitching frequency and environment temperature and the load.
- *2 Rise time : 10 μ s, decay time to half crest : 160 μ s
- *3 This shows a number of operation where it can be running by which a fatal defect is not caused, and a number of operation by which a steady characteristic is maintained is 1 × 10⁷ operations.



- •All specifications in this catalog and production status of products are subject to change without notice. Prior to the purchase, please contact NEC Tokin for updated product data.
- lacktriangle Please request for a specification sheet for detailed product data prior to the purchase.
- •Before using the product in this catalog, please read "Precautions" and other safety precautions listed in the printed version catalog.



Recommended relay drive conditions

Drive under conditions. If it is impossible, please inquire to NEC/TOKIN.

Nonlatch type	Voltage: within ±5% at nominal voltage	
	Square pulse (rise and fall time is rapidly) Pulse height: within ±5% at nominal voltage Pulse width: More than 10 ms	Ambient temperature -40 to +85°C



- •All specifications in this catalog and production status of products are subject to change without notice. Prior to the purchase, please contact NEC Tokin for updated product data.
- ●Please request for a specification sheet for detailed product data prior to the purchase.
- Before using the product in this catalog, please read "Precautions" and other safety precautions listed in the printed version catalog.



PRODUCT LINEUP

Non-latch Type

at 20°C

Nominal Coil	Coil	Must Operate	Must Release
Voltage	Resistance	Voltage	Voltage
(Vdc)	(Ω) ±10 %	(Vdc)	(Vdc)
3	64.3	2.25	0.3
4.5	145	3.38	0.45
5	178	3.75	0.5
6	257	4.5	0.6
9	579	6.75	0.9
12	1028	9	1.2
24	2880	18	2.4

Single-Coil Latch Type

at 20°C

Nominal Coil	Coil	Must Operate	Must Release
Voltage	Resistance	Voltage	Voltage
(Vdc)	(Ω) ±10 %	(Vdc)	(Vdc)
3	90	2.25	2.25
4.5	202.5	3.38	3.38
5	250	3.75	3.75
6	360	4.5	4.5
9	810	6.75	6.75
12	1440	9	9
24	3840	18	18

Double-Coil Latch Type ** (Can not be driven by revese po; arity for reverse operation.) at 20°C

Nominal Coil Voltage	Coil Resistance (Ω) ±10 %		Must Operate Voltage (Vdc)	Must Release Voltage (Vdc)
(Vdc)	S (12) 1	64.3	2.25	(vac)
	R	64.3	-	2.25
4.5	S	145	3.38	-
	R	145	-	3.38
5	S	178	3.75	=
	R	178	-	3.75
6	S	257	4.5	=
	R	257	-	4.5
9	S	579	6.75	=
	R	579	-	6.75
12	S	1028	9	-
	R	1028	-	9
24	S	2880	18	-
	R	2880	-	18

Note * Test by pulse voltage

The latch type relays should be initialized at appointed position before using, and should be enegized to specific polanity by a bone polabity to avoid wrong operation.

Any special coil requirement, please contact NEC/TOKIN for availability.

^{* *} S : Set coil (pin No.1... \oplus , pin No.5... \odot) R : Reset coil (pin No.10... \oplus , pin No.6... \odot)

[•]All specifications in this catalog and production status of products are subject to change without notice. Prior to the purchase, please contact NEC Tokin for updated product data.


Please request for a specification sheet for detailed product data prior to the purchase.


Before using the product in this catalog, please read "Precautions" and other safety precautions listed in the printed version catalog.

TYPICAL PERFORMANCE DATA

■COIL TEMPERATURE RISE


Temperature is measured by coil resistance.






SWITCHING CAPACITY

This is allowed maximum value. Inquiry for NEC/TOKIN under maximum value at continuous use.





■MAXIMUM COIL VOLTAGE

This is maximum value of permissible alteration. Inquiry for NEC/TOKIN at continuous use.



■APPLIED VOLTAGE VS. TIMING (Sample: EB2-5NU)






- •All specifications in this catalog and production status of products are subject to change without notice. Prior to the purchase, please contact NEC Tokin for updated product data.
- Please request for a specification sheet for detailed product data prior to the purchase.
- Before using the product in this catalog, please read "Precautions" and other safety precautions listed in the printed version catalog.

■OPERATE AND RELEASE VOLTAGE VS. AMBIENT TEMPERATURE


This shows a typical change of operate (release) voltage. Maximum value of operate estimated, so it must be applied more than this value for safety operation. In case of "hot start operation", please inquiry for NEC/TOKIN.




Ambient temperature (degree C)

■RUNNING TEST (Nonload)


(Load: None, Driving: 5V.DC, 50 Hz, 50% duty, Ambient temperature: Room temperature, Sample: EB2-5NU 20 pieces)






■RUNNING TEST (Load)

(Load: 50 V.DC 0.1 A resistive, Driving: 5V.DC, 5 Hz, 50% duty, Ambient temperature: 85 degree C, Sample: EB2-5NU 10 pieces)








- •All specifications in this catalog and production status of products are subject to change without notice. Prior to the purchase, please contact NEC Tokin for updated product data.
- Please request for a specification sheet for detailed product data prior to the purchase.
- •Before using the product in this catalog, please read "Precautions" and other safety precautions listed in the printed version catalog.

■BREAKDOWN VOLTAGE


Sample: EB2-5NU 10 pieces










■ALTERNATION OF VOLTAGE AT DENSELY MOUNTING (Magnet interference)










- •All specifications in this catalog and production status of products are subject to change without notice. Prior to the purchase, please contact NEC Tokin for updated product data.
- ●Please request for a specification sheet for detailed product data prior to the purchase.
- Before using the product in this catalog, please read "Precautions" and other safety precautions listed in the printed version catalog.

SOLDERING CONDITION





Note:

- The strength of the stren


TUBE PACKAGE

Dimension of Package (Unit: mm)





Outline of Package




- All specifications in this catalog and production status of products are subject to change without notice. Prior to the purchase, please contact NEC Tokin for updated product data.
- ●Please request for a specification sheet for detailed product data prior to the purchase.
- ●Before using the product in this catalog, please read "Precautions" and other safety precautions listed in the printed version catalog.




TAPE PACKAGE

Appearance Reel Top cover tape Embossed carrying tape 750 Relays/Reel (Standard)

Tape Dimensions Unit: mm (inch)



Relay orientation mark and tape carrying direction.





- •All specifications in this catalog and production status of products are subject to change without notice. Prior to the purchase, please contact NEC Tokin for updated product data.
- Please request for a specification sheet for detailed product data prior to the purchase.
- Before using the product in this catalog, please read "Precautions" and other safety precautions listed in the printed version catalog.

Notes on Correct Use


1. Notes on contact load

Make sure that the contact load is within the specified range; otherwise, the lifetime of the contacts will be shortened considerably. Note that the running performance shown is an example, and that it varies depending on parameters such as the type of load, switching frequency, driver circuit, and ambient temperature under the actual operating conditions. Evaluate the performance by using the actual circuit before using the relay.

2. Driving relays

- If the internal connection diagram of a relay shows + and symbols on the coil, apply the rated voltage to the relay in the specified direction. If a rippled DC current source is used, abnormalities such
- as beat at the coil may occur.


 The maximum voltage that can be applied to the coil of the relay varies depending on the ambient temperature. Generally, the higher the voltage applied to the coil, the shorter the operating time. Note. however, that a high voltage also increases the bounce of the contacts and the contact opening and closing frequency, which may shorten the lifetime of the contacts
- If the driving voltage waveform of the relay coil rises and falls gradually, the inherent performance of the relay may not be fully realized. Make sure that the voltage waveform instantaneously rises and falls as a pulse



- For a latching relay, apply a voltage to the coil according to the polarity specified in the internal connection diagram of the relay
- If a current is applied to the coil over a long period of time, the coil temperature rises, promoting generation of organic gas inside the relay, which may result in faulty contacts. In this case, use of a latching relay is recommended.
- The operating time and release time indicate the time required for each contact to close after the voltage has been applied to or removed from the coil. However, because the relay has a mechanical structure, a bounce state exists at the end of the operating and release times. Furthermore, because additional time is required until the contact stabilizes after being in a high-resistance state, care must be taken when using the relay at high speeds.
- Pins 5 and 6 of the non-latching and single-coil latching types of the EB2 relay are not used. However, do not connect an external circuit

3. Operating environment

- Make sure that the relay mounted in the application set is used within the specified temperature range. Use of a relay at a temperature outside this range may adversely affect insulation or contact performance
- If the relay is used for a long period of time in highly humid (RH 85% or higher) environment, moisture may be absorbed into the



- relay. This moisture may react with the NOx and SOx generated by glow discharges that occur when the contacts are opened or closed, producing nitric or sulfuric acid. If this happens, the acid produced may corrode the metallic parts of the relay, causing operational malfunction.
- Because the operating temperature range varies depending on the humidity, use the relay in the temperature range illustrated in the figure below. Prevent the relay from being frozen and avoid the generation of condensation.
- The relay maintains constant sealability under normal atmospheric pressure (810 to 1,200 hpa). Its sealability may be degraded or the relay may be deformed and malfunction if it is used under barometric conditions exceeding the specified range.
- The same applies when the relay is stored or transported.

 Keep the upper-limit value of the temperature to which the relay is exposed after it is removed from the carton box to within 50°C
- If excessive vibration or shock is applied to the relay, it may malfunction and the contacts remain closed. Vibration or shock applied to the relay during operation may cause considerable damage to or wearing of the contacts. Note that operation of a snap switch mounted close to the relay or shock due to the operation of magnetic solenoid may also cause malfunctioning.

4. Notes on mounting relays

- When mounting a relay onto a PC board using an automatic chip mounter, if excessive force is applied to the cover of the relay when the relay is chucked or inserted, the cover may be damaged or the characteristics of the relay degraded. Keep the force applied to the relay to within 1 kg.
- Avoid bending the pins to temporarily secure the relay to the PC board. Bending the pins may degrade sealability or adversely affect the internal mechanism.
- It is recommended to solder the relay onto a PC board under the following conditions:
- <1> Reflow soldering

Refer to the recommended soldering temperature profile.

<2> Flow soldering

Solder temperature: 260°C max., Time: 5 seconds max. Preheating: 100°C max./1 minute max.

<3> Manual soldering

Solder temperature: 350°C. Time: 2 to 3 seconds

- Ventilation immediately after soldering is recommended
- Avoid immersing the relay in cleaning solvent immediately after soldering due to the danger of thermal shock being applied to the relay.
- Use an alcohol-based or water-based cleaning solvent. Never use thinner and benzene because they may damage the relay housing.
- Do not use ultrasonic cleaning because the vibration energy generated by the ultrasonic waves may cause the contacts to remain closed

5. Handling

- Relays are packaged in magazine cases for shipment. If a space is created in the case after some relays have been removed, be sure to insert a stopper to secure the remaining relays in the case. If relays are not well secured, vibration during transportation may cause malfunctioning of the contacts.
- Exercise care in handling the relay so as to avoid dropping it or allowing it to fall. Do not use a relay that has been dropped.

 If a relay drops from a workbench to the floor, a shock of 9,800 m/s2
- (1,000 G) or more is applied to the relay, possibly damaging its functions. Even if a light shock has been applied to the relay, thoroughly evaluate its operation before using it.
- Latching relays are factory-set to the reset state for shipment.
 A latching relay may be set, however, by vibration or shock applied while being transported. Be sure to forcibly reset the relay before using it in the application set. Also note that the relay may be set by unexpected vibration or shock when it is used in a portable set.
- The sealability of a surface-mount relay may be lost if the relay absorbs moisture and is then heated during soldering. When storing relays, therefore, observe the following points:
- <1> Please use relays within 12 months after delivery. (Storage conditions: 30 degrees C / 60% RH)
 <2> For MBB packing, Please use relays within 2 years after
- delivery

(Stronge conditions: 30 degrees C / 60% RH)

After opening MBB packing, Please use within 3 months. (Storage conditions: 30 degrees C/ 60% RH)

- All specifications in this catalog and production status of products are subject to change without notice. Prior to the purchase, please contact NEC Tokin for updated product data.
- Please request for a specification sheet for detailed product data prior to the purchase
- •Before using the product in this catalog, please read "Precautions" and other safety precautions listed in the printed version catalog.

No part of this document may be copied or reproduced in any form or by any means without the prior written consent of NEC/TOKIN Corporation. NEC/TOKIN Corporation assumes no responsibility for any errors which may appear in this document.

NEC/TOKIN Corporation does not assume any liability for infringement of patents, copyrights or other intellectual property rights of third parties by or arising from use of a device described herein or any other liability arising from use of such device. No license, either express, implied or otherwise, is granted under any patents, copyrights or other intellectual property rights of NEC/TOKIN Corporation or others. While NEC/TOKIN Corporation has been making continuous effort to enhance the reliability of its electronic components, the possibility of defects cannot be eliminated entirely. To minimize risks of damage or injury to persons or property arising from a defect in an NEC/TOKIN electronic component, customers must incorporate sufficient safety measures in its design, such as redundancy, fire-containment, and anti-failure features. NEC/TOKIN devices are classified into the following three quality grades: "Standard", "Special", and "Specific". The Specific quality grade applies only to devices developed based on a

customer designated "quality assurance program" for a specific application. The recommended applications of a device depend on its quality grade, as indicated below. Customers must check the quality grade of each device before using it in a particular application.

Standard. Computers, office equipment, communications equipment, test and measurement equipment, audio and visual equipment, home electronic appliances, machine tools, personal electronic equipment and industrial robots

Special: Transportation equipment (automobiles, trains, ships, etc.), traffic control systems, anti-disaster systems, anti-crime systems, safety equipment and medical equipment (not specifically designed for life support)

Specific: Aircrafts, aerospace equipment, submersible repeaters, nuclear reactor control systems, life

support systems or medical equipment for life support, etc.

The quality grade of NEC/TOKIN devices is "Standard" unless otherwise specified in NEC/TOKIN's Data Sheets or Data Books. If customers intend to use NEC/TOKIN devices for applications other than those specified for Standard quality grade, they should contact an NEC/TOKIN sales representative in advance.

- (1) "NEC/TOKIN" as used in this statement means NEC/TOKIN Corporation and also includes its majorityowned subsidiaries.
- "NÉC/TOKIN electronic component products" means any electronic component product developed or manufactured by or for NEC/TOKIN (as defined above).

DE0202

- All specifications in this catalog and production status of products are subject to change without notice. Prior to the purchase, please contact NEC Tokin for updated product data.
- Please request for a specification sheet for detailed product data prior to the purchase.
- •Before using the product in this catalog, please read "Precautions" and other safety precautions listed in the printed version catalog.