







-  PRODUCTS ▾
-  DISTRIBUTOR INVENTORY
-  INDUSTRIES ▾
-  SUPPORT ▾
-  NEWS & EVENTS ▾
-  ABOUT US ▾









64AT315-1

[Products](#) > [Switches](#) > [Toggle Switches](#) > [AT Series](#) > [64AT315-1](#)

Overview

MICRO SWITCH AT Series Toggle Switch, 4 pole, 3 position, Solder T2 type terminal, Standard Lever.
 MICRO SWITCH AT toggle switches provide a compact [View More](#)



-  [view all 64AT315-1 literature](#)
-  [view distributor inventory](#)
-  [sample request](#)
-  [email support](#)
-  [get support](#)
-  [email sales](#)
-  [find a distributor](#)
-  [email this page](#)





Technical Specifications

Product Type	MICRO SWITCH Toggle	Ampere/Voltage Range (Resistive Load)	0.1 A to 1.0 A at 0.5 Vac to 115 Vac 0.1 A to 1.0 A at 0.5 Vdc to 28 Vdc												
Circuitry	4PDT	Action	3 position												
Circuitry/Operating action	<table border="0" style="font-size: small;"> <tr> <td></td> <td style="text-align: center;">Keyway Position</td> <td style="text-align: center;">Center Position</td> <td style="text-align: center;">Opposite Position</td> </tr> <tr> <td style="text-align: center;">Pole 1&2</td> <td style="text-align: center;">C-NC</td> <td style="text-align: center;">C-NC</td> <td style="text-align: center;">C-NO</td> </tr> <tr> <td style="text-align: center;">Pole 3&4</td> <td style="text-align: center;">C-NO</td> <td style="text-align: center;">C-NC</td> <td style="text-align: center;">C-NC</td> </tr> </table>		Keyway Position	Center Position	Opposite Position	Pole 1&2	C-NC	C-NC	C-NO	Pole 3&4	C-NO	C-NC	C-NC	Mounting	Bushing 15/32 in
	Keyway Position	Center Position	Opposite Position												
Pole 1&2	C-NC	C-NC	C-NO												
Pole 3&4	C-NO	C-NC	C-NC												
Termination	Solder T2 type	Comment	Gold Contacts												
Availability	Global	UNSPSC Code	39122211												

[View More](#)

View documents in:

Documents

TITLE	DOCUMENT TYPE	LANGUAGE	SIZE
 64AT315-1 highres photo	Photo	English	704KB
 AT Series Toggle Switch Assemblies	Catalog Information	English	427KB
 64AT315-1 lowres photo	Photo	English	102KB
 Sensors and Switches in Oil Rig Applications	Application Note	English	7MB

[View More](#)

Product Features

- Gold or silver contacts
- Choice of sealed bushing
- Standard or pull to unlock toggle lever
- Short behind-panel depth
- Solder or quick connect termination
- 2,4, 6, or 8 SPDT precision basic switches
- 2 or 3 position, momentary or maintained action

Applications

- Industrial machinery and equipment
- Military and commercial aviation

- Construction equipment
- Test instruments
- Agricultural machinery
- Process control
- Medical instrumentation

NAVIGATION LINKS

[HOME PAGE](#)

[PRODUCTS](#)

[DISTRIBUTOR INVENTORY](#)

[INDUSTRIES](#)

[SUPPORT](#)

[NEWS & EVENTS](#)

[ABOUT US](#)

DISTRIBUTOR LINKS

[ECOM LOGIN](#)

[LEARN CENTER](#)

[REQUEST ACCESS TO ECOM](#)

[SALES/AD PORTAL LOGIN](#)

[SALES/AD PORTAL ACCESS REQUEST](#)

[SAMPLE REQUEST](#)

[SUPPLIER MICROSITE](#)

LANGUAGE

English 

SOCIAL MEDIA



SITE INFORMATION

[PRIVACY STATEMENT](#)

[SITEMAP](#)

[TERMS & CONDITIONS](#)

COPYRIGHT © 2018 HONEYWELL
INTERNATIONAL INC.