



NADB9MF-B

9 pole D-SUB feedthrough, male to female, black D-shape housing

Features & Benefits

- Ideal for audio networking and integration of equipment into video systems
- Universally accepted standard D-shape housing

Technical Information**Product**

| | |
|---------------|-----------|
| Title | NADB9MF-B |
| Gender | male |

Electrical

| | |
|--------------------------------------|------------|
| Contact resistance | 30 mΩ |
| Insulation resistance | > 5 GΩ |
| Number of electrical contacts | 9 |
| Rated current per contact | 3 A |
| Rated voltage | 50 V ac |
| Dielectric strength | > 0.5 kVac |

Mechanical

| | |
|---------------------------|----------------|
| Panel thickness | 4 mm |
| Wiresize | |
| Wiring | Feedthrough |
| Mounting direction | Front mounting |
| Chassis shape | D |

Material

| | |
|------------------------|-------------------------|
| Contact plating | Au |
| Contacts | Brass (CuZn39Pb3) |
| Insert | Steel , tin plated, PBT |
| Shell | Zinc diecast (ZnAl4Cu1) |
| Shell plating | Black chromium |

Environmental

| | |
|--------------------------|------------------|
| Flammability | UL 94-V0 |
| Temperature range | -25 °C to +85 °C |