

MICRO SWITCH
a Honeywell Division

FED. MFG. CODE 91929

SWITCH-BASIC

CATALOG LISTING
V7-1A37D8-000-3



CW-B0088

CATALOG LISTING
V7-1A37D8-000-3
REPLACES
RELEASE NO. PR-19025
ISSUE
M
4

REVISIONS

A	PR-19025 J A P 11 MAR 91	30 JAN 12
B	CO-76108 L J F 20 OCT 93	CMH
C	0085964 SBH 30 JAN 12	CMH


CHECK
30 JAN 12
CHECK
CMH
CHECK
27 DEC 89
CHECK
J A P
CHECK
27 DEC 89
CHECK
J A P
CHECK
19 DEC 89
DRAWN
T J A



NOTE
1 - SWITCH WILL OPERATE AND RELEASE WITHIN FULL EXCURSION OF THE PLUNGER

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.

THIRD ANGLE PROJECTION



CHARACTERISTICS	ELECTRICAL DATA	SCALE	NONE	DO NOT SCALE PRINT
OPERATING FORCE — — — 150 GRAM MAX	CONTACT ARRANGEMENT S P N C	UNLESS OTHERWISE SPECIFIED TOLERANCES ARE		
RELEASE TRAVEL — — — — .010 MIN	L162 5A 125, 250, 277 VAC 1/10HP 250 VAC			
RELEASE FORCE — — — 25 GRAM MIN		TWO PLACE (.00)	±.015	
DIFFERENTIAL TRAVEL — — .002-.010	RL	THREE PLACE (.000)	±.005	
OVERTRAVEL — — — — .050 MIN		ANGLES	±	
FREE POSITION — — — — .625 MAX		WEIGHT		

RASTER
DRAWN