



## NBNC75BZV14

The rearTWIST HD BNC cable connector offers a true 75  $\Omega$  design and is perfectly suitable for HD applications. The patented rearTWIST boot guarantees easy access even in high density applications and offers color coding.

Suitable cable:  
Belden 1794A

Crimp size:  
Pin: 1.6 mm (square) or 1.75 mm (hex)  
Shield: 8.23 mm (hex)

### Features & Benefits

- "rearTWIST Principle" locking/unlocking using the easily accessible soft touch boot (Patent DE 100 48507)
- True 75  $\Omega$  design meets the stringent HDTV / DVD requirements
- Snug-fit center pin insert provides tactile feedback
- Excellent cable protection and retention
- Accessories include color coded boots in 10 standard colors, crimp tool and dies
- Ideal for recessed bulkheads where access to the "head" of the connector might be an issue. These connectors turn from the back and not the front.
- Leading area: Avoids tilting due to side forces to protect contacts from deformation. Guarantees a lifetime of min. 1000 mating cycles!
- Shield and jacket crimp technology prevents the problem of an exposed grounding braid on cable assemblies
- Precise Swiss machined brass parts for outstanding durability

**Technical Information**

Product	
<b>Title</b>	NBNC75BZV14
<b>Connection Type</b>	BNC 75 Ω
<b>Gender</b>	male

Electrical	
<b>Contact resistance</b>	≤ 3 mΩ (inner)
<b>Contact resistance</b>	≤ 2 mΩ (outer)
<b>Dielectric strength</b>	1.5 kVdc
<b>Insulation resistance</b>	> 5 GΩ
<b>Rated voltage</b>	<50 V
<b>VSWR</b>	≤1.050/>32 dB up to 1 GHz ≤1.065/>30 dB up to 2 GHz ≤1.100/>26 dB up to 3 GHz

Mechanical	
<b>Cable O.D.</b>	< 8.0 mm
<b>Cable retention</b>	> 30 N (center)
<b>Crimp size</b>	1,6 Square crimp (pin) acc. IEC 60803 (die designation 2) or 1,75 Hex crimp acc. IEC 60803 (die desi
<b>Insertion force</b>	< 25 N
<b>Lifetime</b>	> 1000 mating cycles
<b>Wiresize</b>	
<b>Locking device</b>	Bayonett
<b>Cable anchoring</b>	Jacket crimping

Material	
<b>Contacts</b>	Brass (CuZn35Pb2) , 0.2 μm AuCo (Center contact)
<b>Insert</b>	PTFE
<b>Shell</b>	Brass (CuZn39Pb3)
<b>Shell plating</b>	Optalloy®

**Environmental**

<b>Temperature range</b>	-30 °C to +85 °C
<b>Contact crimpability</b>	Complies with IEC 60803 and IEC 60352-2