



NBTB75IF14

BNC cable jack for panel mount, isolated

Neutrik's BNC cable jacks for panel mount offer a true 75 Ω design for serial and digital (HD) signals. The machined brass connector body provides an extremely rugged and non-abrasive connection over long term use.

Suitable cables:

Belden 1520A, Belden 1521A, Belden 1522A, Belden 179DT, Draka 0.31/1.45 AF, Draka 753-1304(2), Draka 755-1302, Suhner G02233, ZNK CM14B

Crimp size:

Pin: 1.6 mm (square)

Shield: 4.06 mm (hex)

Features & Benefits

- Gold plated center contact
- True 75 Ω design meets the stringent HD requirements
- Isolated panel mount (solves potential grounding problems and prevents common-mode influence with other connections conducted over the same panel ground potential)

Technical Information

Product	
Title	NBTB75IFI4
Connection Type	BNC 75 Ω
Gender	female

Electrical	
Contact resistance	≤ 3 mΩ (inner)
Contact resistance	≤ 2 mΩ (outer)
Dielectric strength	0,75 kVdc
Impedance	75 Ω
Insulation resistance	> 5 GΩ
Rated voltage	<50 V
VSWR	≤1.050/>32 dB up to 1 GHz ≤1.065/>30 dB up to 2 GHz ≤1.100/>26 dB up to 3 Ghz

Mechanical	
Cable O.D.	4.0 - 7.7 mm
Cable retention	> 30 N (Center)
Crimp size	4,06 Hex crimp (shield) acc. MIL22520/5-39(B)
Crimp size (pin)	1,6 Square crimp (pin) acc. IEC 60803 (die designation 2)
Insertion force	< 25 N
Lifetime	> 1000 mating cycles
Wiresize	
Locking device	Bayonett
Cable anchoring	Jacket crimping

Material	
Contacts	Brass (CuZn35Pb2), 0.2 µm AuCo (Center contact)
Insert	PTFE
Shell	Brass (CuZn39Pb3)
Shell plating	Optalloy®

Environmental	
Temperature range	-30 °C to +85 °C
Contact crimpability	Complies with IEC 60803 and IEC 60352-2