



NBTC75BVV5

The rearTWIST HD Tiny BNC cable connector is optimized for small cable diameters. The additional leading ferrule eases the critical assembly of multicore or tiny cables.

Like all Neutrik BNCs it offers a true 75 Ω design and is perfectly suitable for HD applications.

The patented rearTWIST boot guarantees easy access even in high density applications and offers color coding.

Suitable cables:

Belden 1406B, 1407B, 1417B

Crimp size:

Pin: 1.6 mm (square)

Shield: 5.0 mm (hex)

Features & Benefits

- "rearTWIST Principle" locking/unlocking using the easily accessible soft touch boot (Patent DE 100 48507)
- Ideal for recessed bulkheads where access to the "head" of the connector might be an issue. These connectors turn from the back and not the front.
- Optimized assembly for multicore or tiny cables
- True 75 Ω design meets the stringent HDTV / DVD requirements
- Leading area: Avoids tilting due to side forces to protect contacts from deformation. Guarantees a lifetime of min. 1000 mating cycles!
- Snug-fit center pin insert provides tactile feedback
- Shield and jacket crimp technology prevents the problem of an exposed grounding braid on cable assemblies
- Excellent cable protection and retention
- Precise Swiss machined brass parts for outstanding durability
- Accessories include color coded boots in 10 standard colors, crimp tool and dies

Technical Information

Product	
Title	NBTC75BWW5
Connection Type	BNC 75 Ω
Gender	male

Electrical	
Contact resistance	≤ 3 m Ω (inner)
Contact resistance	≤ 2 m Ω (outer)
Dielectric strength	0,75 kVdc
Impedance	75 Ω
Insulation resistance	> 5 G Ω
Rated voltage	< 50 V
VSWR	$\leq 1.10 / > 26$ dB up to 1 GHz $\leq 1.14 / > 24$ dB up to 2 GHz $\leq 1.22 / > 20$ dB up to 3 GHz

Mechanical	
Cable O.D.	3.8 mm
Cable retention	> 30 N (Center)
Crimp size	5 Hex crimp (shield) acc. MIL22520/5-43(B)
Crimp size (pin)	1,6 Square crimp (pin) acc. IEC 60803 (die designation 2)
Insertion force	< 25 N
Lifetime	> 1000 mating cycles
Wiresize	
Locking device	Bayonett
Cable anchoring	Jacket crimping

Material	
Contacts	Brass (CuZn35Pb2), 0.2 µm AuCo (Center contact)
Insert	PTFE
Shell	Brass (CuZn39Pb3)
Shell plating	Optalloy®

Environmental	
Temperature range	-30 °C to +85 °C
Contact crimpability	Complies with IEC 60803 and IEC 60352-2