

MICRO SWITCH

FREERPORT ILLINOIS, U.S.A.
A DIVISION OF HONEYWELL
FED. MFG. CODE 91929

SWITCH-BASIC

CATALOG LISTING

V7-2B37D8

CW-B3225

V7-2B37D8

M

DRAWING
NUMBER

X

ISSUE
3

REPLACES

RELEASE NO. PR-16293

REVISIONS

A	C066350	J A P	14 SEPT 89
B	CO-176106	K D R	07 OCT 93

CHECK



II MAX

J A P

CHECK


88

FO-52848-A



THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.

THIRD ANGLE PROJECTION



CHARACTERISTICS

OPERATING FORCE	-----	75 GRAM MAX
RELEASE TRAVEL	-----	.010 MIN
RELEASE FORCE	-----	10 GRAM MIN
DIFFERENTIAL TRAVEL	-----	.002-.010
OVERTRAVEL	-----	.050 MIN
FREE POSITION	-----	.625 MAX

ELECTRICAL DATA

CONTACT ARRANGEMENT
S P N C

L 156

11A 1/3 HP 125, 250, 277 VAC
1/2A 125 VDC, 1/4A 250 VDC
4A 125 VAC "L"



SCALE FULL

DO NOT SCALE PRINT

TOLERANCES

APPLY TO DESIGN UNITS. CONVERSIONS ARE ONLY FOR REFERENCE. UNLESS NOTED, TOLERANCES ARE ±

	DIM.	TOL.	DIM.	TOL.
	mm	mm/in	in	mm/in
NO PLACES	X	17.04	X	0.87/03
ONE PLACE	X,X	0.41/016	X,X	0.387/015
TWO PLACES	X,XX	0.157/006	X,XX	0.137/005
THREE PLACES	X,XXX		X,XXX	
ANGLES				

SI METRIC

US CUSTOMARY

DESIGN UNITS



WEIGHT