



REV	DOCUMENT	CHANGED BY	CHECK
3	207458	TSM 19FEB03	SAV



CHARACTERISTICS	
OPERATING FORCE	---- 77 GRAMS MAX
RELEASE FORCE	----- 6 GRAM MIN
RELEASE TRAVEL	----- .009 MIN
DIFFERENTIAL TRAVEL	----- .015 MAX
OVERTRAVEL	----- .038 MIN

ELECTRICAL DATA	
CONTACT ARRANGEMENT	
S P D T	
L216	
10A 1/3HP 125, 250 OR 277 VAC	
1/2A 125 VDC	
1/4A 250 VDC; 4A 125 VAC "L"	

UNLESS OTHERWISE SPECIFIED TOLERANCES ARE:			
	<input checked="" type="checkbox"/> US (inch) CUSTOMARY	<input type="checkbox"/> SI (mm) METRIC	
NO PLACE	X	±.040	±1
ONE PLACE	.X	±.030	±0,4
TWO PLACE	.XX	±.015	±0,15
THREE PLACE	.XXX	±.005	±
ANGLES		±	±
RAW MATERIAL-COMMERCIAL STANDARD			
THIRD ANGLE PROJECTION			

DRAWN	TSM	19FEB03
CHECK	SAV	19FEB03
THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE PERMISSION OF HONEYWELL.		
DIMENSIONS ARE TO BE MET BEFORE PROTECTIVE COATINGS ARE APPLIED		
PTC 2D	ASME Y14.5M-1994	

<b>Honeywell</b>			
TITLE <b>SWITCH, BASIC</b>			
SIZE	DWG TYPE	DRAWING NAME	REV
<b>B</b>	<b>I</b>	<b>V7-2E17E9-420</b>	<b>3</b>
SCALE 2 : 1		WEIGHT	SHEET 1 OF 1