



NE8FBH-C5-LED

Horizontal PCB mount RJ45 receptacle, CAT5e, two light pipes for through hole LEDs, B-Series cutout with latch lock, max. panel thickness 3 mm

The etherCON Series is a ruggedized and lockable RJ45 connector system, optimized for pro audio, video and lightning network applications. The chassis connectors are shaped to fit into standardized panels out of the entertainment industry.

The B-Series offers a space saving design and a rugged metal front plate.

Attention! Does not intermate with CAT6 cable connector NE8MC6-MO and NKE6S* cables.

Features & Benefits

- Accommodates rugged etherCON NE8MC* or any standard RJ45 plug
- Ground panel connection
- CAT5e performance according to ISO/IEC 11801 and TIA/EIA 568-C.2
- Approved latch lock system
- PoE+ compliant according to 802.3at Type2

Technical Information

Product	
Title	NE8FBH-C5-LED
Gender	female

Electrical	
Contact resistance	< 10 mΩ
Dielectric strength	1 kVdc
Frequencyrange	1 - 100 MHz
Insulation resistance	> 0.5 GΩ
Rated current per contact	1.5 A
Rated voltage	< 50 V
Transmission performance	CAT5e, acc. TIA/EIA 586C.2, IEC11801
Power over Ethernet	PoE+ acc. IEEE 802.3at

Mechanical	
Insertion force	≤ 20 N
Withdrawal force	≤ 20 N
Lifetime	> 1000 mating cycles
Panel thickness	max. 3 mm (0.12")
Wiresize	
Wiring	Horizontal PCB mount
Locking device	Latch lock
Mounting direction	Rear mounting
Chassis shape	A
Recommended LED-height	5.6 mm (2.2") The final LED brightness depends on the actual LED height and the angel of radiation. Subject to be tested!

Material

Contact plating	0.2 µm Au over Ni plating
Contacts	Bronze (CuSn8)
Locking element	Ck 67 steel, treated
Shell	PBT D202G30

Environmental

Flammability	UL 94 V-0
Solderability	Complies with IEC 68-2-20
Temperature range	-30 °C to +80 °C